ABB BALDOR RELIANCE

Customer information packet

VEWDM3611T

3HP, 1764RPM, 3PH, 60HZ, 3630M, TEFC, F1, N
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 11:11:54 AM

Specifications

Enclosure	TEFC
Frame	182TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CURUSEEV
	NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.160 A @ 460.0 V
	8.320 A @ 230.0 V
	8.800 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	4.2 a

Part Detail

Revision	B
Type	AC
Mech. spec.	36K187
Base	
Status	PRD/A
Elec. spec.	36WGZ650
Layout	36LYK187
Eff. date	09-11-2026
CD Diagram	CD0005
Poles	04
Leads	9#16
Proprietary	False
Created date	11-05-2025

Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3630M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	16.54 IN
Power Factor	74
Product Family	Wash Down
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1764 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L								
CAT.NO.	VEWDM3611T							
SPEC.	36K187Z650							
HP	3							
VOLTS	230/460							
AMP	8.4/4.2							
RPM	1765							
FRAME	182TC	**HZ**	60			**PH**	3	
SER.F.	1.15	**CODE**	K	**DES**	B	**CLASS**	F	
NEMA-NOM-EFF	89.5	**PF**	74					
RATING	40C AMB-CONT							
CC	010A							
DE	6206	**ODE**	6205					
ENCL	TEFC	**SN**						
BLANK	SFA 9.28/4.64							

AC Induction Motor Performance Data
Record # 115759
Typical performance - not guaranteed values

Winding: 36WGZ650-R001	**Type:** 3630M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			3	**Full Load Torque**	8.942 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			8.4/4.2	**Breakdown Torque**	38.2 LB-FT
R.P.M.			1765	**Pull-up Torque**	19.1 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	22.4 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	32.2 A
Service Factor (S.F.)			1.15	**No-load Current**	2.38 A
NEMA Nom. Eff.	89.5	**Power Factor**	74	**Line-line Res. @ 25ºC**	3.8717 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	46°C
S.F. Amps			9.4/4.7	**Temp. Rise @ S.F. Load**	56°C
				Locked-rotor Power Factor	42.6
				Rotor inertia	0.279 lb-ft²

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	33	54	67	74	79	81	77
Efficiency	82.2	88.4	89.8	89.8	89	87.9	89.3
Speed	1790.7	1781.4	1771.4	1761.2	1749.9	1738.7	1754
Line amperes	2.54	2.94	3.51	4.2	4.99	5.87	4.67


ABB Motors and Mechanical Inc.


WINDING # 36WGZ650

3 HP 3 PH 60 HZ 1765 RPM 460 V 3630M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=38.2 PU=19.1 LR=22.4 LRA=32.2




36LYK187
614-623 = 15.17
624-634 = 16.54
635-646 = 18.04
(635-646 ONLY)
2.75
.25
2.62
.25 KEY
1.75 LONG
Ø8.60
NAMEPLATE
8.82
1.1250
1.1245
Ø8.500
8.497
FORSHEDA
SLINGER
4 HOLES
3 W/PLUGS
(EA. END)
4.27
Ø7.86
6.80
45°
45°
6.36
LEAD HOLE
.75 NPT
4 HOLES
.50-13 TAP
Ø7.25 B.C.
5.76
APPLY SEALER TO
RETAINER SCREW HEADS
BEFORE INSTALLING
APPLY COAT OF
SEALER TO HOUSING
BEFORE PRESSING
SEAL IN
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: HA1005A03 WAS HW4600B32
REV: E
VERSION: 05
REVISED: 12:58:40 01/09/2025
TDR: 000001247953
MODEL NO. 36LYK187
REF: -
BY: USMAHAD
B
BALDOR - RELIANCE®
VER 182-4TC TEFC 36M WD
36LYK187

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS