Customer information packet

RL1304A

.5HP, 1725RPM, 1PH, 60HZ, 56, 3418L, OPEN, F1, N
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 3:07:47 PM

Specifications

Enclosure	OPEN
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	UR
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Resilient
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.200 A @ 230.0 V
	4.800 A @ 208.0 V
	8.400 A @ 115.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	62.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Resilient Mount
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	N
Type	AC
Mech. spec.	34G036
Base	
Status	PRD/A
Elec. spec.	34WG5595
Layout	34LYG036
Eff. date	08-18-2026
CD Diagram	CD0052
Poles	04
Leads	6#18,1#16 #1TH
Proprietary	False
Created date	03-12-2013

High Voltage Full Load Amps	4.2 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Terminal Panel Or Lead Hole
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	None
Motor Standards	NEMA
Motor Type	3418L
Mounting Arrangement	F1
Number of Poles	4
Overall Length	11.59 IN
Power Factor	62
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Resilient Mount
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible: Connected Standard
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload

Winding Thermal 1 Location	SB
Winding Thermal 2	None

Nameplate

NP1257L											
CAT.NO.	RL1304A										
SPEC.	34G036-5595G1										
HP	.5										
VOLTS	115/230										
AMP	8.4/4.2										
RPM	1725										
FRAME	56		**HZ**	60		**PH**	1				
SER.F.	1.25	**CODE**	K	**DES**	N	**CL**	B				
NEMA-NOM-EFF	62	**PF**	62								
RATING	40C AMB-CONT										
CC											
DE	6203	**ODE**	6203								
ENCL	OPEN	**SN**									
	SFA 9.2/4.6										

AC Induction Motor Performance Data
Record # 6782
Typical performance - not guaranteed values

Winding: 34WG5595-R001 **Type:** 3418L **Enclosure:** OPEN

Nameplate Data			
Rated Output (HP)			.5
Volts			115/230
Full Load Amps			8.4/4.2
R.P.M.			1725
Hz	60	**Phase**	1
NEMA Design Code	N	**KVA Code**	K
Service Factor (S.F.)			1.25
NEMA Nom. Eff.	62	**Power Factor**	62
Rating - Duty			40C AMB-CONT
S.F. Amps			9.2/4.6

230 V, 60 Hz: High Voltage Connection	
Full Load Torque	1.5 LB-FT
Start Configuration	direct on line
Breakdown Torque	4.35 LB-FT
Pull-up Torque	3.75 LB-FT
Locked-rotor Torque	5.03 LB-FT
Starting Current	18 A
No-load Current	3.4 A
Line-line Res. @ 25ºC	4.24 Ω A Ph 3.24 Ω B Ph
Temp. Rise @ Rated Load	66°C
Temp. Rise @ S.F. Load	78°C

Load Characteristics 230 V, 60 Hz, 0.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	30	42	53	62	69	77	69
Efficiency	36	52	60	64	65	65	65
Speed	1780	1765	1750	1730	1711	1685	1711
Line amperes	3.45	3.6	3.85	4.2	4.6	5.2	4.6


ABB Motors and Mechanical Inc.

WINDING # 34WG5595


Typical performance - not guaranteed values.

0.5 HP 1 PH 60 HZ 1725 RPM 230 V 3418L


TORQUES(LB-FT): PO=4.35 PU=3.75 LR=5.03 LRA=18



11/5/2026 ACPERF, record # 6782


34LYG036
5.84
3.72
GROUND SCREW
1.48
6.34
3.50 +.00 -.06
THERMAL (WHEN REQ'D)
6 SLOTS .34 WIDE
2.44
2.44
3.25
6.50
408-421 = 11.59
422-428 = 12.44
429-432 = 12.94
2.22
1.88
LEAD HOLE Ø .88 (W/PLUG)
NAMEPLATE
.19 KEY 1.38 LONG
.6250 .6245
GREEN GROUND LEAD
CORD SLOT
2.00
3.00
2.75
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CHANGE CLAMP SCREW TO CORRECT WAY
REV: D
VERSION: 03
REVISED: 08:22:57 06/21/2023
TDR: 000001211422
MODEL NO. 34LYG036
REF: -
BY: ENFRAJ0
B
BALDOR - RELIANCE®
STD RESIL. MTD OPEN 34L NEMA 56/56H TERM. PLATE
SH 1 of 1
34LYG036

CD0052



NOTES:

1. CONNECT LINE LEADS TO L1 AND L2.
   LOW VOLTAGE: CONNECT AS SHOWN.
   HIGH VOLTAGE: MOVE LEAD J TO TERM. 3.
   MOVE LEAD 2 TO TERM. 4.
2. CONNECTIONS ARE SHOWN FOR STANDARD ROTATION (CCW FACING END OPPOSITE SHAFT EXTENSION). INTERCHANGE LEADS 5 AND 8 TO REVERSE ROTATION.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0052

REV. DESC: REMOVE OPTIONAL THERMAL CONNECTION			BALDOR ELECTRIC Co.
REV. LTR: H	VERSION: 01	TDR: 000000373039	
CD0052	FILE: \AAA\00007\100	REVISED: 10:20:46 08/11/2005	TYPE L, DV, REV, THERMAL, TERMINAL PLATE
	MTL: –	BY: ENJOEP0	