



TEGERA® 882

Learn more

FULLY DIPPED, SMART ELASTIC WRISTLET

Glove for allround light weight work with great resistance against water and grease thanks to the full nitrile foam dipping. The smart elastic wristlet makes it easy to put on and take off the glove. Withstands contact heat up to 100°C/212°F. Synthetic glove made of nylon with 15 gg knitting.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Durable
- Good grip

FUNCTIONS

- Withstands contact heat up to 100°C
- Water and oil repellent

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Scratches, lacerations, Contact with dirt, Contact with moisture, Contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Moist environments, Oily and greasy environments, Dirty environments

PRIMARY AREAS OF USE

Assembly, Building and construction, Carpentry, Construction, Inspection work, Installation work, Soil preparation, Tiling

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Electricity and gas supply, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Transport equipment manufacturing, Transportation and logistics

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE All-round work gloves, Heat protection gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 15
LINING MATERIAL Nylon
LENGTH 230-260 mm
DEXTERITY 5
GRIP DESIGN Micro foam grip pattern
COLOUR Black
PAIRS PER: BUNDLE/CARTON 12/60
DISPLAY TYPE Bag with euro slot
DIPPING Fully dipped
DIPPING MATERIAL Nitrile foam
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level A
INNER MATERIAL SPECIFICATION Nylon
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 4121A

EN 407:2020 (No flame protection) X1XXXX

ANSI 6 ABR

Contact heat rating valid for palm area only

FEATURES

Water repellent

SIZE		ARTICLE NUMBER	EAN
7	S	882-7	7392626040199
8	M	882-8	7392626040205
9	L	882-9	7392626040212
10	XL	882-10	7392626040229
11	XXL	882-11	7392626040236

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.