



**SECTION 1 – CHEMICAL PRODUCT & COMPANY IDENTIFICATION**

GHS Product Identifier: **Oil Eater® Parts Washing Fluid – Heavy Duty Neutral**

Other Identification means: Formula# CH12288

Uses: General Purpose Cleaning

Manufacturer Name: Kafko International. Ltd.

Address: 3555 W Howard St. Skokie, IL. 60076-4012

Phone: (847) 763-0333 Fax: (847) 763-0334

Emergency Contact: Chemtrec (800) 424-9300

**SECTION 2 – HAZARDS IDENTIFICATION**

GHS Classification: Eye Irritant Category 2B

Labeling Pictogram: None Required

Signal Word: WARNING:

Hazard Statement: Causes Eye Irritation.

Precautionary Statement: Avoid contact with eyes. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

**SECTION 3 - INGREDIENTS**

<u>MATERIAL</u>	<u>CAS #</u>	<u>% by WT.</u>
Water	7732-18-5	Q.S.
Linear Alcohol Ethoxylate Blend	Proprietary	< 6 %
Sodium Xylene Sulphonate	1300-72-7	< 3%
2,2',2"-Nitrilotri(ethan-1-ol)[1]	102-71-6	< 1%
Potassium dihydrogenphosphate	7778-77-0	< 0.5%
Potassium Nitrate	7757-79-1	< 0.5%

**SECTION 4 – FIRST AID MEASURES**

Skin Contact: Remove contaminated clothing. Rinse skin with warm water for 15 minutes. If irritation occurs seek medical attention.

Eye Contact: Flush with water for 15 minutes. If irritation persists seek medical attention.

Ingestion: Drink large quantities of water. Call physician immediately.

Inhalation: Remove to fresh air immediately. If irritation persists, call doctor.

**SECTION 5 - FIRE AND EXPLOSION HAZARD DATA**

Flammability of the product: Non Flammable

Flash Point: N/A

Extinguishing Media: Dry Chemical, Water Fog, Co2, Sand

Fire Fighting Procedures: Wear Self Contained Breathing



Products of combustion:	Apparatus
Fire Hazards in the presence of other chemicals:	Carbon oxides
Unusual Fire Hazards:	No specific information is available None Expected

**SECTION 6 – ACCIDENTAL RELEASE MEASURES**

Small Spill:  
Absorb with industrial absorbent. Dispose of in accordance with local, state & federal regulations. Rinse residue to avoid slippery conditions.

Large Spill:  
Non-flammable material. Wear chemical resistant gloves, boots and goggles. Stop the source of the spill. Collect the spill using mechanical means. Waste disposal method: Fully water-soluble. Follow all local, state and federal regulations.

**SECTION 7 – HANDLING & STORAGE**

Precautions:	Store containers upright in cool dry place
Storage:	Store product in original containers. Do not store in metal vessels
Other precautions:	Keep out of reach of children

**SECTION 8 – EXPOSURE CONTRIOLS & PERSONAL PROTECTION**

Engineering Controls:	No control measures are required under normal conditions. If large quantities are involved use NIOSH or MSHA approved respirator Limited personal exposures exist with this product. As always keep airborne vapors below TLV limits. Ensure that proper work-station safety mechanisms are operative and tested including showers and eyewash stations.
Personal Protection:	Safety glasses are recommended, chemical resistant gloves aprons and suits are optional for those with dermatological sensitivity.

**SECTION 9 - PHYSICAL DATA**

Boiling point:	~ 220° F
Voc content:	Less Than 0.4% by weight
Solubility in water:	COMPLETE
Appearance and odor:	Clear Solution With A Characteristic Odor
Specific gravity:	1.00 - 1.02 (ASTM 112H @ 20° C)
Evaporation rate:	1.2 (water=1.0)
pH:	6.5 – 8.9



**SECTION 10 - REACTIVITY DATA**

Conditions To Avoid:	Extreme Heat
Stability:	Stable
Incompatibility:	Acids, Strong Oxidizers
Hazardous Polymerization:	Will Not Occur
Corrosivity:	Non-corrosive

**SECTION 11 - TOXICOLOGICAL DATA**

Routes of Entry: Eyes, skin, ingestion.  
 Toxicity to animals: **Non-Toxic** per Consumer Product Safety Commission and FHSA standards. Acute oral LD50 greater than 5 g/kg  
 Chronic Effect on Humans: None known  
 Special Remarks: None

**SECTION 12 - Ecological Data**

Ecotoxicity: Non-toxic to Aquatic Organisms  
 Fathead Minnow (*Pimephales promelas*) LC<sub>50</sub> > 200mg/L at 96 hours  
 Chemical Fate: This product is expected to be readily biodegradable per EPA guidelines

**SECTION 13 – DISPOSAL CONSIDERATIONS**

Waste Disposal: Dispose of in accordance with local, state & federal regulations. Rinse residue to avoid slippery conditions.

**SECTION 14 – TRANSPORT INFORMATION**

DOT CLASSIFICATION: Not Applicable - Non-regulated; Non-hazardous

**SECTION 15 – REGULATORY INFORMATION**

All components used in this compound appear on the TSCA Inventory Federal/National:  
None

HMIS (USA)

HEALTH 0	FIRE 0	REACTIVITY 0	PERSONAL PROTECTION 0
----------	--------	--------------	-----------------------

**SECTION 16 – OTHER INFORMATION**

The Information Herein Is Based On Data Considered To Be Accurate As Of The Date Of The Presentation Of This Safety Data Sheet. No Warranty Or Representation, Expressed Or Implied, Is Made As To The Accuracy Or Completeness Of The Foregoing Data And Safety Information. The User Assumes All Liability For Any Damage Or Injury Resulting From Abnormal Uses, For Any Failure To Adhere To Recommended Practices, Or For Any Hazards Inherent In The Nature Of The Product.