ABB BALDOR RELIANCE

Customer information packet

EM3313T-5

10HP, 1770RPM, 3PH, 60HZ, 215T, 3740M, OPSB, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 3:15:09 PM

Specifications

Enclosure	OPSB
Frame	215T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM CURUSEEV NEMA PREMIUM (OLD LOGO)
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	10.000 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	10.0 a
Insulation Class	F

Part Detail

Revision	Z
Type	AC
Mech. spec.	37F614
Base	
Status	PRD/A
Elec. spec.	37WGT932
Layout	37LYF614
Eff. date	01-22-2026
CD Diagram	CD0006
Poles	04
Leads	3#14
Proprietary	False
Created date	03-19-2009

Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3740M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	17.45 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553L											
CAT.NO.	EM3313T-5										
SPEC	37F614T932										
HP	10										
VOLTS	575										
AMPS	10										
RPM	1770										
FRAME	215T		**HZ**	60			**PH**	3			
SF	1.15	**CODE**	H	**DES**	B	**CLASS**	F				
NEMA NOM. EFF	91.7	**PF**	82								
RATING	40C AMB-CONT										
CC	010A										
ENCL	OPSB	**SER**									
DE	6307		**ODE**	6206							
VPWM INVERTER READY		SFA 11.3									
CT30-60(2:1) VT3-60(20:1)											

Accessories

Part number	Description	Multiplier
37-1404	C FACE KIT	A8

AC Induction Motor Performance Data
Record # 28137
Typical performance - not guaranteed values

Winding: 37WGT932-R003	**Type:** 3740M	**Enclosure:** OPSB

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			10	**Full Load Torque**	29.68 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			10	**Breakdown Torque**	87.58 LB-FT
R.P.M.			1770	**Pull-up Torque**	46.92 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	52.43 LB-FT
NEMA Design Code	B	**KVA Code**	H	**Starting Current**	71.77 A
Service Factor (S.F.)			1.15	**No-load Current**	4.43 A
NEMA Nom. Eff.	91.7	**Power Factor**	82	**Line-line Res. @ 25ºC**	1.71 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	34°C
S.F. Amps				**Temp. Rise @ S.F. Load**	41°C
				Locked-rotor Power Factor	37.7
				Rotor inertia	0.984 lb-ft²

Load Characteristics 575 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	43	66	77	82	85	85	84
Efficiency	87	91.7	92.2	91.7	90.9	89.8	91.2
Speed	1793	1785	1777	1770	1760	1750	1763
Line amperes	4.94	6.26	7.96	10	12.18	14.77	11.3


ABB Motors and Mechanical Inc.

WINDING # 37WGT932

Typical performance - not guaranteed values.

10 HP 3 PH 60 HZ 1770 RPM 575 V 3740M

TORQUES(LB-FT): PO=87.58 PU=46.92 LR=52.43 LRA=71.77



11/5/2026 ACPERF, record # 28137

AC Induction Motor Performance Data
Record # 30180
Typical performance - not guaranteed values

Winding: 37WGT932-R001	**Type:** 3740M	**Enclosure:** OPSB

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			10	**Full Load Torque**	29.68 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			10	**Breakdown Torque**	87.58 LB-FT
R.P.M.			1770	**Pull-up Torque**	46.92 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	52.43 LB-FT
NEMA Design Code	B	**KVA Code**	H	**Starting Current**	71.77 A
Service Factor (S.F.)			1.15	**No-load Current**	4.43 A
NEMA Nom. Eff.	91.7	**Power Factor**	82	**Line-line Res. @ 25ºC**	1.71 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	34°C
S.F. Amps				**Temp. Rise @ S.F. Load**	41°C
				Locked-rotor Power Factor	37.7
				Rotor inertia	0.984 LB-FT2

Load Characteristics 575 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	43	66	77	82	85	85	84
Efficiency	87	91.7	92.2	91.7	90.9	89.8	91.2
Speed	1793	1785	1777	1770	1760	1750	1763
Line amperes	4.94	6.26	7.96	10	12.18	14.77	11.3


ABB Motors and Mechanical Inc.


WINDING # 37WGT932

10 HP 3 PH 60 HZ 1770 RPM 575 V 3740M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=87.58 PU=46.92 LR=52.43 LRA=71.77





37LYF614
(717-735) = 16.32
(736-744) = 17.45
(745-750) = 18.20
(751-756) = 18.95
3.44
3.88
3.38
GREASE FITTING
(EA. END)
NAMEPLATE
.31 KEY
2.38 LONG
Ø 1.3750
1.3745
6 HOLES
Ø.43
5.50
.50
7.00
3.50
8.00
Ø9.57
7.90
LIFTING LUG
(1 EA. END)
10.04
5.25
5.19
LEAD
HOLE
Ø1.38
4.25
4.25
6.73
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: UPDATE THRU-BOLT GRAPHICS
REV: K
VERSION: 05
REVISED: 11:30:38 01/03/2024
TDR: 000001221774
MODEL NO. 37LYF614
REF: -
BY: USFRHAR
B
BALDOR - RELIANCE®
STD HORZ 213-5T OPSB 37M (SUPER-E)
37LYF614


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1