



**Airflow  
You  
Trust**

Confined Space Ventilators • Dehumidification



The Americ<sup>®</sup> dehumidifier offers all of the tools necessary to manage ambient humidity and moisture mitigation concerns with ease. The unit features intuitive and at the ready controls that allow the user to set, track, and service the unit seamlessly.

- **Oversized, heavy-duty wheels** make transporting the unit up and down stairs smooth and effortless
- **Rugged rotomolded construction** resists dents, chips, and corrosion for long-lasting durability
- **Intuitive control interface** delivers only the essential information you need—nothing more, nothing less
- **Heavy-duty retractable handle** folds away neatly when not in use
- **Large-capacity basin and pump** ensure reliable, hassle-free operation
- **Thoughtful access points** simplify maintenance and routine cleaning
- **High-airflow, easy-clean filters** maximize efficiency with minimal upkeep

Model	AMD-100A-115
Dimensions (L x W x H)	18.5" x 17.5" x 30"
Tested Water Removal AHAM (80 degrees F, 60% Relative Humidity)	100 Pints/Day
Tested full saturation conditions (90 degrees F, 60% Relative Humidity)	219 Pints/Day
Process Air Rating	380 CFM
Handle	Steel, Retractable Handle
Power 115 Volt	6.37 Amp
Defrost Type	Fan Defrost
Controls	Electronic Touch Pad
Noise Level	≤ 58 dB

Contact your Sales Rep for more details and timing on availability.



www.pinnacleclimate.com • 1.800.779.3267