



## TEGERA® 987

Learn more

## VERY HIGH CUT AND HEAT PROTECTION

Glove with a very high level of both cut and heat protection. It can withstand contact heat up to 250°C/482°F and provides resistance to contact cold. The nitrile-coated palm features a sandy finish for an excellent grip. Additionally, it has a water and oil-repellent palm and an extended cuff. This glove is made of 7 gg para-aramid and stainless-steel fiber yarn.

### CHARACTERISTICS

- Highest level of protection
- Very durable
- Good grip

### FUNCTIONS

- Withstands contact heat up to 250°C
- Extra long
- Water and oil repellent palm



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*

## PREVENTS RISK OF

Cut injuries, Puncturing, Abrasion injuries, Blisters, Contact with dirt, Contact with moisture

## PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Warm environments, Moist environments, Dirty environments, Harsh environments

## PRIMARY AREAS OF USE

Sheet-metal work, Metalwork, Glass industry work, Repair work

## PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Basic metals manufacturing, Electrical equipment manufacturing, Glass, ceramics and construction materials, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Transport equipment manufacturing

## TYPE OF WORK

Heavy weight

## SPECIFICATION

**TYPE** Cold insulation gloves, Cut resistant gloves, Heat protection gloves
**CATEGORY** Cat. II
**KNITTING GAUGE (GG)** 7
**LINING MATERIAL** Acrylic, Para-aramid, Stainless steel fibre yarn
**LENGTH** 250-290 mm
**DEXTERITY** 2
**GRIP DESIGN** Sandy finish
**COLOUR** Black
**PAIRS PER: BUNDLE/CARTON** 6/60
**DISPLAY TYPE** Bulk pack
**DIPPING** Palm-dipped
**DIPPING MATERIAL** Nitrile
**CUFF STYLE** Extended knitwrist cuff
**CUFF MATERIAL** Textile
**CUT RESISTANCE (EN ISO 13997)** Cut resistance level F
**CUT RESISTANCE (EN ISO 13997) TDM:** 30.3 N
**INNER MATERIAL SPECIFICATION** Acrylic, Para-aramid, Stainless steel fibre yarn, Polyester
**OUTER MATERIAL SPECIFICATION** Nitrile

## COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018 4X42F

EN 407:2020 (No flame protection) X2XXXX

EN 511:2006 X1X

ANSI A5 CUT

ANSI 6 ABR

**Contact heat rating valid for palm area only**

## FEATURES

Cut protection

| SIZE | | ARTICLE NUMBER | EAN |
|---|---|---|---|
| 7 | S | 987-7 | 7340118340289 |
| 8 | M | 987-8 | 7340118340371 |
| 9 | L | 987-9 | 7340118340463 |
| 10 | XL | 987-10 | 7340118340555 |
| 11 | XXL | 987-11 | 7340118340647 |

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*