

LOW PROFILE CARTON SEALER

MODEL CS-5050AS

sealersales



Conveyors and Casters
Included

Low Profile - Seals Cartons as Low as 3.5"

- Simple to use
- Ideal for smaller boxes - seals heights as low as 3.5"
- Quick manual adjustment for various box sizes
- Side pressure rollers to close box top
- Two side belts for positive feed
- Plug and Play - Includes conveyors and casters
- Optional 3" tape head available

Unlock seamless carton sealing with our **CS-5050AS** featuring two side belt drive design. The operator simply folds the top flaps of the corrugated carton and feeds it into the machine. The CS-5050AS applies a single tape to both the top and bottom of the box simultaneously. The CS-5050AS can easily be adjusted to process a different size carton. Our carton sealers offer reliable, cost-effective solutions that deliver significant savings to your production process.

Built for low profile cartons, the CS-5050AS can seal box heights as low as 3.5" - making it excellent fit for fulfillment centers running flat or slim pack shipments.

Experience thoughtful design with our carton sealers – tailored for your convenience. The sealer comes complete with infeed/exit conveyors, casters, and power cord, providing you a plug and play system. Enjoy flexibility with your box sizes – easily adjust for different box widths in seconds. Elevate your packaging process with the features of our carton sealers, designed to make sealing cartons a breeze.

SPECIFICATIONS

CARTON SIZE (LENGTH)	3.5" TO INFINITE
CARTON SIZE (WIDTH)	3.1" - 19.7" (80MM - 500MM)
CARTON SIZE (HEIGHT)	3.5" - 19.7" (90MM - 500MM)
TABLE HEIGHT	21" - 34" (538-870MM)
MACHINE SIZE	68"L X 37"W X (38"-61")H
MACHINE SPEED	65.6FT/MINUTE - UP TO 15 CARTONS/MIN
ELECTRICAL	110V, 1 PHASE, 10 AMPS, 180W
MAX BOX WEIGHT	66-LBS
TAPE HEAD SPECS	2" (48MM) WIDE - 1,000 OR 1,500 YARD ROLL
WEIGHT	242-LBS (NET) 400-LBS (GROSS)

LOW PROFILE CARTON SEALER

MODEL CS-5050AS

sealersales

