marathon®

Cast Iron Motors

Model No: TCA2P23AE231GAA009
Catalog No: R823

Cast Iron Motor, 3 & 2 HP, 3 Ph, 60 & 50 Hz, 230/460 & 200/400 V, 1200 RPM, 112M Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: TCA2P23AE231GAA009, Catalog No: R823 Cast Iron Motor, 3 & 2 HP, 3 Ph, 60 & 50 Hz, 230/460 & 200/400 V, 1200 RPM, 112M Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**3 & 2 Hp**
Output KW	**2.2 & 1.5 kW**	Voltage	**230/460 & 200/400 V**
Speed	**1170 & 980 r/min**	Synchronous RPM	**1200 & 1000 r/min**
Service Factor	**1.15 & 1.15**	Frame	**112M**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**89.5 & 82.5 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**10.3/5.1 & 8.3/4.2 A**
Power Factor	**70**	Duty	**Continuous**
Insulation Class	**F8**	Design Code	**N (IEC)**
KVA Code	**M**	Drive End Bearing Size	**6306**
Opp Drive End Bearing Size	**6206**	UL	**Recognized**
CSA	**N**	CE	**Y**
IP Code	**55**	Number of Speeds	**1**

Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Line Or Inverter**
Poles	**6**	Rotation	**Reversible**
Resistance Main	**3.31 O**	Mounting	**B3**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Cast Iron**
Shaft Type	**IEC**	Shaft Diameter	**28 in**
Assembly/Box Mounting	**F3**	Inverter Load	**Constant 2:1/Variable 10:1**

Drawings

Connection Drawing	**8442000675**	Outline Drawing	**SS620873**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026

GENERAL TOLERANCE		
LINEAR DIM	>0~6	±0.1
	>6~30	±0.2
	>30~120	±0.3



NOTES:

1. PRESSURE-SENSITIVE ADHESIVE TAPE COATED WITH ANTI-ADHESIVE.
2. YELLOW COLOR BACK GROUND LETTERS WILL BE BLACK.
3. THE TOLERANCE OF THE LINEAR SIZE OF THE TOLERANCE WITHOUT THE TOLERANCE BY THE TABLE.
4. LEAD TERMINAL MARKINGS FONT SIZE : T1-T12 & U1-U4,V1-V4& W1-W4 OF ARIAL WITH 3mm SIZE.
5. OTHER LETTER FONT SIZE SHOULD BE 3.5mm.

DRAWING REVISION	REVISION BY	REV DATE/© DATE
C	SV	05/11/2026
REQUEST NUMBER	APPROVED BY	DATE
CR-0026249	RMS	05/11/2026

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE mm
INCH DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY	DATE
NIV	29/01/2019
APPROVED BY	DATE
JAY	29/01/2019
REFERENCE	

THIRD ANGLE PROJECTION

marathon™

DESCRIPTION
CONNECTION DIAGRAM
9 LEADS- STAR CONNECTON

MATERIAL	PROCESS/FINISH

SIZE	DRAWING NUMBER	SHEET
A	8442000675	1 OF 1