ABB BALDOR RELIANCE

Customer information packet

CFSWDM3713T-E

15HP, 3500RPM, 3PH, 60HZ, 215TC, 3756M, TEFC, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 2:59:42 PM

Specifications

Enclosure	TEFC
Frame	215TC
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	37.000 A @ 208.0 V
	34.000 A @ 230.0 V
	17.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part Detail

Revision	T
Type	AC
Mech. spec.	37Q242
Base	
Status	PRD/A
Elec. spec.	37WGR515
Layout	37LYQ242
Eff. date	01-29-2026
CD Diagram	CD0180
Poles	02
Leads	9#14
Proprietary	False
Created date	08-03-2017

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	17.0 a
Insulation Class	H
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3756M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	22.12 IN
Power Factor	90
Product Family	WD All SS Encapsulated
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4427AAA05												
CAT #	CFSWDM3713T-E			**WGT**		**LBS**						
SPEC	37Q242R515G1			**ENCL**	TEFC							
SER #				**CC**	010A	**IP**	69					
HP	15			**MAG CUR**	11/5.5							
VOLTS	230/460					**NEMA NOM. EFF**	91.7					
AMPS	34/17					**PF**	90					
RATING	40C AMB-CONT											
RPM	3500					**MAX RPM**	5400					
FRAME	215TC	**HZ**	60	**CODE**	L	**CLASS**	H					
SER.F.	1.15	**SF AMP**	38/19			**PH**	3	**DES**	A			
DE	6307			**ODE**	6307							
LUBRICATION	POLYREX EM											
ID LOGO	**INV TYPE:**		**VPWM**	**CHP**	60	**TO**	90		1.5:1			
ID LOGO	**WK2**	0.512	**CT**	15	**TO**	60		4:1				
ID LOGO	**SL HZ**	1.7	**VT**	6	**TO**	60		10:1				
										QR		
YR												

AC Induction Motor Performance Data
Record # 43026
Typical performance - not guaranteed values

Winding: 37WGR515-R001	**Type:** 3756M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			15	**Full Load Torque**	22.4 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			34/17	**Breakdown Torque**	129 LB-FT
R.P.M.			3500	**Pull-up Torque**	62.1 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	81.4 LB-FT
NEMA Design Code	A	**KVA Code**	L	**Starting Current**	187 A
Service Factor (S.F.)			1.15	**No-load Current**	5.43 A
NEMA Nom. Eff.	91.7	**Power Factor**	90	**Line-line Res. @ 25ºC**	0.42167 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	78°C
S.F. Amps				**Temp. Rise @ S.F. Load**	96°C
				Locked-rotor Power Factor	30
				Rotor inertia	0.512 LB-FT2

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	59	82	87	90	92	93	91
Efficiency	88.1	92	92.4	91.9	91.1	89.9	91.4
Speed	3575.6	3551.4	3525.1	3498.7	3469.7	3437.4	3481
Line amperes	6.71	9.36	13.1	16.9	20.8	25.3	19.2


ABB Motors and Mechanical Inc.


WINDING # 37WGR515

15 HP 3 PH 60 HZ 3500 RPM 460 V 3756M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=129 PU=62.1 LR=81.4 LRA=187





37LYQ242
717-735 = 19.49
736-744 = 20.68
745-750 = 21.37
751-756 = 22.12
LASER ETCHED WARNING LABEL
LASER ETCHED NAMEPLATE
6.03
.26
3.12
.31 KEY 2.38 LONG
10.18
Ø8.500 8.497
Ø8.97
Ø1.3750 1.3745
6 HOLES Ø.41
.50
5.50
4.50
7.00
8.000
4 DRAIN HOLES W/PLUGS 90° APART (EACH END)
9.24
Ø9.51
45°
45°
TOP OF WARNING LABEL
TOP OF NAMEPLATE
2.00
9.98
5.25
5.19
LEAD HOLE 1.00 N.P.T.
4 HOLES .50-13 UNC ↧1.00 Ø7.25 B.C.
4.25
4.25
7.38
4.75
9.50
.177±.020 (EA. END)
6307
FRONT END DETAIL
SNAP RING BRG. RETAINER
LIP SEAL (EA. END)
AXIAL FACE SEAL (EA. END)
6307
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD DIM TO AXIAL SEAL LOCATION
REV: C
VERSION: 03
REVISED: 07:28:51 07/28/2026
TDR: 000001276312
MODEL NO. 37LYQ242
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
STD HORZ 213-5TC TEFC M WD11/12
37LYQ242

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1