

Master MH-220T-SDR SilentDrive® Kerosene/Diesel Forced Air Heater w/ Thermostat—220,000 BTU



- Heat up well-ventilated construction sites, workshops, farms, or garages
- Made of rugged steel for years of use
- SilentDrive® Technology for half the noise of a comparable heater
- Runs on efficient, clean-burning K-1 Kerosene and CSA certified to run on #1 Diesel, Jet A Fuel and #1 Fuel Oil
- 1-year limited warranty

Product Description

Level up with Master's 220,000 BTU SilentDrive® Kerosene/Diesel Forced Air Torpedo Heater. Despite its powerful, high-BTU output, it's the quietest forced air heating solution for spaces up to 5,500 square feet. In fact, heaters with SilentDrive® technology are 50% quieter and 46% more energy efficient than equivalent conventional forced air heaters. An added bonus for your busy schedule: this durable, multi-fuel heater requires no routine maintenance to keep it running smoothly. Master – built for power.



Features and Benefits

- Operates up to 10 hours on a full tank of fuel
- Steel construction
- Heats up to 5,500 square feet
- Built-in air pressure gauge
- Easy-lift handle
- Automatic safety shutoff system
- Built-in fuel gauge
- Easy-grip fuel cap
- Built-in thermostat
- Solid wheels
- LED digital readout
- Power on/off switch
- Integrated diagnostics
- Half the noise of a comparable heater
- 1-year limited warranty

Key Specs

| | | | |
|-----------------------------------|---|---|--------------|
| Model Number | MH-220T-SDR | Fuel Tank Capacity (gal.) | 13 |
| Brand | Master | Max. Operating Hours | 7.7 |
| Warranty | 1-year limited warranty | Heating Area (sq. ft.) | 5,500 |
| Net Weight (lb.) | 62 | Max. Outlet Temp (°F / °C) | 1025 / 552 |
| Air Flow (CFM) | 685 | Volts | 120 |
| Fuel Type | K-1 Kerosene, Jet A Fuel, #1 Fuel Oil, # 1 Diesel | Amps | 1.72 |
| Fuel Consumption (gal./hr) | 1.67 | Max. BTU | 220,000 |
| | | Product Dimensions (L x W x H) (in.) | 45 x 24 x 27 |

