

SECTION 1 Identification**1.1. Product identifier**

Product form : Mixture
Trade name : MAG1 5W20 6/1QT
Product code : 26679

1.2. Other means of identification

No additional information available

1.3. Recommended use of the chemical and restrictions on use

Use of the substance/mixture : Engine oil

1.4. Supplier's details**Manufacturer**

Highline Warren LLC
8700 Trail Lake Drive West
Suite 300
Memphis, TN 38125
USA
T +01 (901) 437-8615
sds@highlinewarren.com

1.5. Emergency phone number

Emergency number : CHEMTREC: +1 (800) 424-9300 International: +01 (703) 527-3887
24 hours a day, 7 days a week

SECTION 2 Hazard Identification**2.1. Classification of the substance or mixture****GHS US classification**

Not classified

2.2. Label elements**GHS US labeling**

No labeling applicable

2.3. Hazards associated with known or reasonably anticipated uses

No additional information available

2.4. Hazards not otherwise classified

No additional information available

2.5. Unknown acute toxicity

89.69% of the mixture consists of ingredient(s) of unknown acute toxicity (Oral)
89.69% of the mixture consists of ingredient(s) of unknown acute toxicity (Dermal)
89.69% of the mixture consists of ingredient(s) of unknown acute toxicity (Inhalation (Dust/Mist))

MAG1 5W20 6/1QT

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

SECTION 3 Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	GHS US classification
Distillates, petroleum, hydrotreated heavy paraffinic	CAS-No.: 64742-54-7	80 - 100*	Aquatic Chronic 4, H413

Full text of hazard classes and H-statements : see section 16

SECTION 4 First aid measures

4.1. Description of necessary first-aid measures

First-aid measures general	: If you feel unwell, seek medical advice.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash skin with plenty of water.
First-aid measures after eye contact	: Rinse eyes with water as a precaution.
First-aid measures after ingestion	: Call a poison center/doctor/physician if you feel unwell.
Personal protection for first-aid responders.	: First aid workers will be equipped with suitable personal protective equipment.

4.2. Most important symptoms/effects, acute and delayed

Symptoms/effects after inhalation	: None under normal conditions.
Symptoms/effects after skin contact	: None under normal conditions.
Symptoms/effects after eye contact	: None under normal conditions.
Symptoms/effects after ingestion	: None under normal conditions.

4.3. Indication of immediate medical attention and special treatment needed, if necessary

Other medical advice or treatment	: Treat symptomatically.
-----------------------------------	--------------------------

SECTION 5: Fire-fighting measures

5.1. Suitable (and unsuitable) extinguishing media

Suitable extinguishing media	: Water spray. Dry powder. Foam. Carbon dioxide.
Unsuitable extinguishing media	: Do not use a heavy water stream.

5.2. Specific hazards arising from the chemical

Fire hazard	: No fire hazard.
Explosion hazard	: No direct explosion hazard.
Hazardous decomposition products in case of fire	: Toxic fumes may be released.

5.3. Special protective equipment and precautions for fire-fighters

Firefighting instructions	: Fight fire from safe distance and protected location. Do not enter fire area without proper protective equipment, including respiratory protection.
Protection during firefighting	: Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

MAG1 5W20 6/1QT

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

SECTION 6 Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : Stop leak if safe to do so. Notify authorities if product enters sewers or public waters. Absorb spillage to prevent material-damage.

For non-emergency personnel

Protective equipment : Wear recommended personal protective equipment.
Emergency procedures : Ventilate spillage area.

For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".
Emergency procedures : Evacuate unnecessary personnel. Stop leak if safe to do so.
Environmental precautions : Avoid release to the environment.

6.2. Methods and materials for containment and cleaning up

For containment : Absorb spilled material with sand or earth. Contain any spills with dikes or absorbents to prevent migration and entry into sewers or streams. Stop leak, if possible without risk.
Methods for cleaning up : Take up liquid spill into absorbent material.
Other information : Dispose of materials or solid residues at an authorized site.

For further information refer to section 13.

SECTION 7 Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Wear personal protective equipment.
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.
Additional hazards when processed : Not expected to present a significant hazard under anticipated conditions of normal use.

7.2. Conditions for safe storage, including incompatibilities

Technical measures : Keep in a cool, well-ventilated place away from heat.
Storage conditions : Keep cool. Protect from sunlight.
Packaging materials : Always store product in container of same material as original container.

SECTION 8 Exposure controls/personal protection

8.1. Control parameters

Distillates, petroleum, hydrotreated heavy paraffinic (64742-54-7)	
USA - ACGIH - Occupational Exposure Limits	
Local name	Mineral oil, excluding metal working fluids Pure, highly and severely refined
ACGIH® TLV® TWA	5 mg/m³ (I - Inhalable particulate matter)
Remark (ACGIH®)	TLV® Basis: URT irr. Notations: A4 (Not classifiable as a Human Carcinogen)
Regulatory reference	ACGIH 2025

MAG1 5W20 6/1QT

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

Exposure limit values of other components

8.2. Appropriate engineering controls

Appropriate engineering controls : Ensure good ventilation of the work station.
Environmental exposure controls : Avoid release to the environment.

8.3. Individual protection measures, such as personal protective equipment

Personal protective equipment:

Wear recommended personal protective equipment.

Hand protection:
Protective gloves
Eye protection:
Safety glasses
Skin and body protection:
Wear suitable protective clothing
Respiratory protection:
In case of insufficient ventilation, wear suitable respiratory equipment

Personal protective equipment symbol(s):



SECTION 9 Physical and chemical properties

9.1. Basic physical and chemical properties

Physical state	: Liquid
Color	: Amber
Odor	: mild petroleum
Odor threshold	: No data available
pH	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: No data available
Flash point	: 204 °C
Flammability (solid, gas)	: Not applicable.
Vapor pressure	: No data available
Relative vapor density at 20°C	: No data available
Relative density	: ≈ 0.8532
Density	: 0.8551 g/ml
Solubility	: Insoluble.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Viscosity, kinematic	: 49.06 mm²/s
Explosion limits	: No data available
Particle characteristics	: No data available

MAG1 5W20 6/1QT

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

9.2. Data relevant with regard to physical hazard classes (supplemental)

No additional information available

SECTION 10 Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11 Toxicological information

Likely routes of exposure : Inhalation. Ingestion. Skin and eye contact.

11.1. Information on toxicological effects

Acute toxicity (oral) : Not classified
Acute toxicity (dermal) : Not classified
Acute toxicity (inhalation) : Not classified

MAG1 5W20 6/1QT	
Unknown acute toxicity (GHS US)	89.69% of the mixture consists of ingredient(s) of unknown acute toxicity (Oral) 89.69% of the mixture consists of ingredient(s) of unknown acute toxicity (Dermal) 89.69% of the mixture consists of ingredient(s) of unknown acute toxicity (Inhalation (Dust/Mist))

Distillates, petroleum, hydrotreated heavy paraffinic (64742-54-7)	
LD50 oral rat	> 15000 mg/kg Source: IUCLID
LD50 dermal rabbit	> 5000 mg/kg Source: IUCLID

Skin corrosion/irritation : Not classified

Serious eye damage/irritation : Not classified

Respiratory or skin sensitization : Not classified

Germ cell mutagenicity : Not classified

MAG1 5W20 6/1QT

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

Carcinogenicity : Not classified (Note L:
The classification as a carcinogen need not apply if it can be shown that the substance contains less than 3 % DMSO extract as measured by IP 346. This note applies only to certain complex oil-derived substances in Annex I.).

Reproductive toxicity : Not classified

STOT-single exposure : Not classified

STOT-repeated exposure : Not classified

Distillates, petroleum, hydrotreated heavy paraffinic (64742-54-7)

LOAEL (oral, rat, 90 days)	125 mg/kg body weight Animal: rat, Animal sex: male, Guideline: OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity Study in Rodents)
NOAEC (inhalation, rat, dust/mist/fume, 90 days)	> 0.98 mg/l air Animal: rat, Guideline: OECD Guideline 412 (Subacute Inhalation Toxicity: 28-Day Study)

Aspiration hazard : Not classified

MAG1 5W20 6/1QT

Viscosity, kinematic	49.06 mm ² /s
----------------------	--------------------------

Symptoms/effects after inhalation : None under normal conditions.

Symptoms/effects after skin contact : None under normal conditions.

Symptoms/effects after eye contact : None under normal conditions.

Symptoms/effects after ingestion : None under normal conditions.

SECTION 12 Ecological information

12.1. Ecotoxicity

Ecology - general : The product is not considered harmful to aquatic organisms or to cause long-term adverse effects in the environment.

Hazardous to the aquatic environment, short-term (acute) : Not classified

Hazardous to the aquatic environment, long-term (chronic) : Not classified.

Distillates, petroleum, hydrotreated heavy paraffinic (64742-54-7)

LC50 - Fish [1]	> 5000 mg/l
EC50 - Crustacea [1]	> 1000 mg/l Source: IUCLID
EC50 96h - Algae [1]	> 1000 mg/l Source: IUCLID

12.2. Persistence and degradability

MAG1 5W20 6/1QT

Persistence and degradability	Not rapidly degradable
-------------------------------	------------------------

Distillates, petroleum, hydrotreated heavy paraffinic (64742-54-7)

Persistence and degradability	Not rapidly degradable
-------------------------------	------------------------

12.3. Bioaccumulative potential

Distillates, petroleum, hydrotreated heavy paraffinic (64742-54-7)

Partition coefficient n-octanol/water (Log Pow)	3.9 – 6 Source: IUCLID
---	------------------------

MAG1 5W20 6/1QT

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

12.4. Mobility in soil

No additional information available

12.5. Other adverse effects

Ozone : Not classified
Fluorinated greenhouse gases : No

SECTION 13 Disposal considerations

Regional waste regulation : Disposal must be done according to official regulations.
Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.
Sewage disposal recommendations : Disposal must be done according to official regulations.
Product/Packaging disposal recommendations : Disposal must be done according to official regulations.
Additional information : Do not re-use empty containers.

SECTION 14 Transport information

In accordance with DOT / IMDG / IATA

DOT	IMDG	IATA
14.1. UN number		
Not regulated for transport		
14.2. Proper Shipping Name		
Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)		
Not regulated	Not regulated	Not regulated
14.4. Packing group		
Not regulated	Not regulated	Not regulated
14.5. Environmental hazards		
Not regulated	Not regulated	Not regulated
No supplementary information available		

14.6. Transport in bulk

Not applicable

14.7. Special precautions for user

DOT
Not regulated

IMDG
Not regulated

IATA
Not regulated

MAG1 5W20 6/1QT

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

SECTION 15 Regulatory information

15.1. Federal regulations

Commercial status of components according to the United States Environmental Protection Agency's Toxic Substances Control Act (TSCA):

Name	CAS-No.	Listing	Commercial status	Flags
Distillates, petroleum, hydrotreated heavy paraffinic	64742-54-7	Present	Active	

This product or mixture is not known to contain a toxic chemical or chemicals in excess of the applicable de minimis concentration as specified in 40 CFR §372.38(a) subject to the reporting requirements of section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 and 40 CFR Part 372.

15.2. International regulations

CANADA

Distillates, petroleum, hydrotreated heavy paraffinic (64742-54-7)

Listed on the Canadian DSL (Domestic Substances List)

EU-Regulations

No additional information available

National regulations

Distillates, petroleum, hydrotreated heavy paraffinic (64742-54-7)

Listed on INSQ (Mexican National Inventory of Chemical Substances)

15.3. State regulations



WARNING:

This product can expose you to chemicals including Benzene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

SECTION 16 Other information

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

Revision date : 2/11/2026
Issue date : 1/6/2026

Full text of hazard classes and H-statements

H413	May cause long lasting harmful effects to aquatic life
------	--

Safety Data Sheet (SDS), USA

This safety data sheet and the information it contains is offered to you in good faith as accurate. We have reviewed any information contained in the data sheet which we have received from outside sources and we believe the information to be correct, but cannot guarantee its accuracy or completeness. Health and safety precautions in this data sheet may not be adequate for all individuals and/or situations. It is the user's obligation to evaluate and use this product in a safe manner and to comply with all applicable laws and regulations. No statement made in this data sheet shall be construed as permission or recommendation for the use of any product in a manner that might infringe existing patents. No warranty is made, either expressed or implied.