

PowerQUAD™

PNEUMATIC VACUUM
 GENERATING HEAD KITS



About PowerQUAD

PowerQUAD vacuums are the most exciting advancement in pneumatic vacuum technology in over 75 years! Featuring a patent-pending, dual-stage vacuum, multi-venturi generating engine. PowerQUAD vacuums save energy, and can be configured to match your compressed air supply while optimizing vacuum performance.

Why Choose Pneumatic over Electric?

NO ELECTRIC MOTORS TO SPARK, BURNOUT, WEAR OUT, OR OVERHEAT.



Savings

PowerQUAD's FOREVER WARRANTY means lower Total Cost of Ownership.

**Save Up To 71%
 Compressed Air.**



Performance

Customer configurable nozzles provide superior vacuum performance.

**Up to 35% Higher Vac Head.
 Up to 67% More Vac Flow.**



Safety

Pneumatic vacuums are inherently safe in hazardous or wet environments.

**No Dangerous Electric
 Cords on the Shop Floor.**



Quiet

PowerQUAD is the quietest pneumatic vacuum on the market period!




**Ultra Quiet Operation.
 Less Than 88 dB.**

PowerQUAD PERFORMANCE & MODELS

CUSTOMER CONFIGURABLE PERFORMANCE

Easy to change color-coded injector nozzle sets are included with all vacuums.



INJECTOR NOZZLE SET	COMPRESSED AIR	VAC FLOW UP TO	VAC HEAD UP TO	ADVANTAGE
	20 cfm	110 cfm	122 inches H ₂ O	Maximum Compressed Air Savings.
	40 cfm	139 cfm	225 inches H ₂ O	Compressed Air Savings AND Higher Vacuum Performance.
	60 cfm	149 cfm	251 inches H ₂ O	Maximum Vacuum Performance.



20-55 Gallon

ALL POWERQUAD Vacuum GENERATING HEAD KITS

- ▶ Ideal for vacuuming up chips, dust, debris, liquids, or sludge in **industrial and commercial applications**.
- ▶ **COMPATIBLE:** fits all existing Guardair vacuum accessories and attachments.
- ▶ **FOREVER WARRANTY**



10 - Gallon



5 - Gallon

Part No.	Gallon Capacity	Vac Hose Size	Sugg. Air Line	Air Flow Requ. (cfm)	Vacuum Lift (in H ₂ O)	Vacuum Flow (cfm)	Noise (dBA)	Dimensions (L" x W" x H")	Weight (lbs)
PQ55H200K	55	2" ID x 10'	1/2"	20-60	122-250	110-149	85-88	28x28x23	33
PQ55H150K	55	1.5" ID x 10'	1/2"	20-60	126-251	92-129	82-85	28x28x23	33
PQ30H200K	20/30	2" ID x 10'	1/2"	20-60	122-250	110-149	85-88	24x24x23	28
PQ30H150K	20/30	1.5" ID x 10'	1/2"	20-60	126-251	92-129	82-85	24x24x23	28
PQ10H150K	10	1.5" ID x 10'	1/2"	20-60	126-251	92-129	82-85	19.75x19.75x19.13	16
PQ05H125K	5	1.5" ID x 10'	3/8"	20-45	118-213	75-97	81-86	19.75x19.75x19.13	16

 FOREVER WARRANTY [DETAILS HERE](#)

ALL VACUUM GENERATING HEADS ARE NON-RETURNABLE ITEMS.