



P65

Technical Data



Color	Gray
Sizes Available	OS
Packaging	Bagged Each
Packed	40 Pair/Case
Case Dimensions (in)	18.11 x 9.06 x 3.94
Case Weight (lbs)	11.02
Country of Origin	Malaysia
Ventilation	Indirect
Headband	Elastic
Lens Color	Clear
Frame Material	Synthetic Rubber
Lens	Clear
Lens Coating	Anti-Scratch, Anti-Fog
Base Curve	5
Certifications	ANSI Z87.1

Bouton® Optical Fortis™ II

Indirect Vent Goggle with Light Gray Body, Clear Lens and Anti-Scratch / Anti-Fog Coating - Non-Latex Strap

- Offers indirect ventilation for liquid splash protection
- Wide facial flange for a secure seal
- Flexible, soft rubber/polyester body for optimal comfort and fit
- Fits comfortably over most prescription glasses
- Nose area split to fit the vast majority of users
- Wide adjustable (non-latex) headband strap
- Headband strap attaches to frame with a swivel clip to ensure a comfortable fit
- Antifog lens coating
- Comes individually boxed
- 5.25 Base curve lens
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Protection from Liquid Splash, Dust and Light Impacts

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS COATING	UPC	UPC (INNER)	UPC (CASE)
251-80-0020	Gray	Clear	Clear	AS/AF	616314164033	01616314164032	02616314164031
251-80-0020-RHB	Gray	Clear	Clear	AS/AF	616314164026	01616314164025	02616314164024

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated