ABB BALDOR RELIANCE

Customer information packet

EM3157T-5

2HP, 1765RPM, 3PH, 60HZ, 145T, 3528M, OPSB, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 3:42:49 PM

Specifications

Enclosure	OPSB
Frame	145T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CURUSEEV
	NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.200 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.2 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	L

Part Detail

Revision	G
Type	AC
Mech. spec.	35BB101
Base	
Status	PRD/A
Elec. spec.	35WGG113
Layout	35LYBB101
Eff. date	12-29-2025
CD Diagram	CD0006
Poles	04
Leads	3#18
Proprietary	False
Created date	03-11-2022

Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3528M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.12 IN
Power Factor	80
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553L											
CAT.NO.	EM3157T-5										
SPEC	35BB101G113G1										
HP	2										
VOLTS	575										
AMPS	2.2										
RPM	1765										
FRAME	145T		**HZ**	60			**PH**	3			
SF	1.15	**CODE**	L	**DES**	B	**CLASS**	F				
NEMA NOM. EFF	86.5	**PF**	80								
RATING	40C AMB-CONT										
CC	010A										
ENCL	OPSB	**SER**									
DE	6205		**ODE**	6203							
VPWM INVERTER READY		SFA 2.56									
CT30-60(2:1) VT3-60(20:1)											

Accessories

Part number	Description	Multiplier
35-8764	C FACE KIT	A8
35EP1604A01SP	D-FLANGE KIT	

AC Induction Motor Performance Data
Record # 87424
Typical performance - not guaranteed values

Winding: 35WGG113-R003	**Type:** 3528M	**Enclosure:** OPEN

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			2	**Full Load Torque**	5.95 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			2.2	**Breakdown Torque**	23.7 LB-FT
R.P.M.			1765	**Pull-up Torque**	14.43 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	17.45 LB-FT
NEMA Design Code	B	**KVA Code**	L	**Starting Current**	19.89 A
Service Factor (S.F.)			1.15	**No-load Current**	1.39 A
NEMA Nom. Eff.	86.5	**Power Factor**	80	**Line-line Res. @ 25ºC**	15 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	58°C
S.F. Amps				**Temp. Rise @ S.F. Load**	70°C
				Locked-rotor Power Factor	57
				Rotor inertia	0.188 lb-ft²

Load Characteristics 575 V, 60 Hz, 2 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	34	54	68	76	81	84	79
Efficiency	77	84.7	86.6	86.3	85.3	83.7	85.7
Speed	1791	1783	1775	1766	1757	1745	1761
Line amperes	1.45	1.64	1.93	2.29	2.74	3.19	2.56


ABB Motors and Mechanical Inc.


WINDING # 35WGG113

2 HP 3 PH 60 HZ 1765 RPM 575 V 3528M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=23.7 PU=14.43 LR=17.45 LRA=19.89





35LYBB101
510-520 = 11.13
521-524 = 11.62
525-528 = 12.12
529-535 = 13.00
536-546 = 14.38
2.50
2.25
GREASE FITTING
(EACH END)
NAMEPLATE
.19 KEY
1.38 LONG
Ø.8750
Ø.8745
6 HOLES
.34 DIA.
4.00
2.25
5.00
.50
5.94
6.61
5.61
6.78
3.50
3.44
LEAD HOLE
Ø1.09
2.75
2.75
4.56
3.25
6.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: UPDATE 3D MODEL BOM PER REV D, NO CHG TO 2D PRINT
REV: E
VERSION: 05
REVISED: 02:33:05 03/22/2022
TDR: 000001187751
MODEL NO. 35LYBB101
REF: -
BY: USBUFRA
Material: -
B
BALDOR - RELIANCE®
STD HORZ 143-5T OPSB 35M W/1.09 LEAD HOLE
SH 1 of 1
35LYBB101


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1