



OxiClean Versatile Stain Remover

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations
Revision Date: 03/26/2015 Issue Date: 03/13/2015

Version: 1.0

SECTION 1: IDENTIFICATION

Product Identifier

Product Form: Mixture

Product Name: OxiClean Versatile Stain Remover

Intended Use of the Product

Laundry Booster, Carpet Spot Remover, Hard Surface Cleaner. For professional use only.

Name, Address, and Telephone of the Responsible Party

Company

Church & Dwight
500 Charles Ewing Blvd
Ewing Township, NJ 08628
T 1-800-524-1328
www.churchdwight.com

Emergency Telephone Number

Emergency Number : For Medical Emergency: 1-888-234-1828, For Chemical Emergency: 1-800-424-9300 (CHEMTREC)

SECTION 2: HAZARDS IDENTIFICATION

This product is labeled in accordance with regulations administered by the Consumer Product Safety Commission (CPSC). The use pattern and exposure in the workplace are generally not consistent with those experienced by consumers. The requirements of the Occupational Safety and Health Administration applicable to this SDS differ from the labeling requirements of the CPSC and, as a result, this SDS may contain additional health hazard information not pertinent to consumer use and not found on the product label.

Classification of the Substance or Mixture

Classification (GHS-US)

Skin Irrit. 2 H315
Eye Dam. 1 H318
Aquatic Acute 2 H401

Label Elements

GHS-US Labeling

Hazard Pictograms (GHS-US)

:



Signal Word (GHS-US)

: Danger

Hazard Statements (GHS-US)

: H315 - Causes skin irritation.
H318 - Causes serious eye damage.
H401 - Toxic to aquatic life.

Precautionary Statements (GHS-US)

: P264 - Wash hands, forearms, and other exposed areas thoroughly after handling.
P273 - Avoid release to the environment.
P280 - Wear protective gloves, protective clothing, eye protection, face protection, respiratory protection.
P302+P352 - If on skin: Wash with plenty of water.
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310 - Immediately call a poison center/doctor.
P321 - Specific treatment (see section 4).
P332+P313 - If skin irritation occurs: Get medical advice/attention.
P362 - Take off contaminated clothing and wash before reuse.

OxiClean Versatile Stain Remover

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations

P501 - Dispose of contents/container in accordance with local, regional, national, territorial, provincial, and international regulations.

Other Hazards

Exposure may aggravate those with pre-existing eye, skin, or respiratory conditions. Contains an oxidizing material which may accelerate fire. May react with metals, and alkaline materials upon prolonged contact. When heated to decomposition may emit toxic and irritating fumes. Material may decompose exothermically at elevated temperatures, or when damp.

Unknown Acute Toxicity (GHS-US) Not available

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

Mixture

Name	Product Identifier	% (w/w)	Classification (GHS-US)
Sodium carbonate	(CAS No) 497-19-8	60 - 100	Eye Irrit. 2A, H319
Sodium percarbonate	(CAS No) 15630-89-4	30 - 60	Ox. Sol. 2, H272 Acute Tox. 4 (Oral), H302 Eye Dam. 1, H318 Aquatic Acute 2, H401
Alcohols, C12-15, ethoxylated	(CAS No) 68131-39-5	1 - 5	Acute Tox. 4 (Oral), H302 Eye Dam. 1, H318 Aquatic Acute 1, H400 Aquatic Chronic 3, H412
Sodium metasilicate	(CAS No) 6834-92-0	0.1 - 1	Met. Corr. 1, H290 Acute Tox. 4 (Oral), H302 Skin Corr. 1B, H314 Eye Dam. 1, H318 STOT SE 3, H335

The specific chemical identity and/or exact percentage of composition have been withheld as a trade secret [29 CFR 1910.1200].

A range of concentration as prescribed by the Controlled Products Regulations has been used where necessary, due to varying composition.

Full text of H-phrases: see section 16

SECTION 4: FIRST AID MEASURES

Description of First Aid Measures

General: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).

Inhalation: When symptoms occur: go into open air and ventilate suspected area. Obtain medical attention if breathing difficulty persists.

Skin Contact: Remove contaminated clothing. Drench affected area with water for at least 15 minutes. Wash contaminated clothing before reuse. If skin irritation occurs: Get medical advice/attention.

Eye Contact: Rinse cautiously with water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Obtain medical attention.

Ingestion: Rinse mouth. Do NOT induce vomiting. Seek medical attention immediately.

Most Important Symptoms and Effects Both Acute and Delayed

General: Causes skin irritation. Causes serious eye damage.

Inhalation: May cause respiratory irritation.

Skin Contact: Causes skin irritation.

Eye Contact: May cause severe irritation. Prolonged exposure may cause eye damage.

Ingestion: Ingestion is likely to be harmful or have adverse effects.

Chronic Symptoms: No additional information available.

Indication of Any Immediate Medical Attention and Special Treatment Needed

If exposed or concerned, get medical advice and attention.

SECTION 5: FIRE-FIGHTING MEASURES

Extinguishing Media

Suitable Extinguishing Media: Water spray, dry chemical, foam, carbon dioxide.

OxiClean Versatile Stain Remover

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations

Unsuitable Extinguishing Media: Do not use a heavy water stream. Use of heavy stream of water may spread fire.

Special Hazards Arising From the Substance or Mixture

Fire Hazard: Not flammable.

Explosion Hazard: Product is not explosive.

Reactivity: Contains an oxidizing material which may accelerate fire.

Advice for Firefighters

Precautionary Measures Fire: Exercise caution when fighting any chemical fire.

Firefighting Instructions: Use water spray or fog for cooling exposed containers.

Protection During Firefighting: Do not enter fire area without proper protective equipment, including respiratory protection.

Hazardous Combustion Products: Carbon oxides (CO, CO₂), sodium oxides, oxygen, irritating fumes.

Other Information: Do not allow run-off from fire fighting to enter drains or water courses.

Reference to Other Sections

Refer to section 9 for flammability properties.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Personal Precautions, Protective Equipment and Emergency Procedures

General Measures: Handle in accordance with good industrial hygiene and safety practice. Spilled material may present a slipping hazard. Avoid prolonged contact with eyes, skin and clothing. Avoid breathing (dust).

For Non-Emergency Personnel

Protective Equipment: Use appropriate personal protection equipment (PPE).

Emergency Procedures: Evacuate unnecessary personnel.

For Emergency Personnel

Protective Equipment: Equip cleanup crew with proper protection.

Emergency Procedures: Ventilate area.

Environmental Precautions

Prevent entry to sewers and public waters. Avoid release to the environment.

Methods and Material for Containment and Cleaning Up

For Containment: Sweep or vacuum the product to recover it.

Methods for Cleaning Up: Clean up spills immediately and dispose of waste safely. Recover the product by vacuuming, shovelling or sweeping. Contact competent authorities after a spill.

Reference to Other Sections

See heading 8, Exposure Controls and Personal Protection.

SECTION 7: HANDLING AND STORAGE

Precautions for Safe Handling

Additional Hazards When Processed: When heated, material may emit irritating fumes. May react with metals, and alkaline materials upon prolonged contact. Material may decompose exothermically at elevated temperatures, or when damp. Contains oxidizing material, may accelerate fire. Material will evolve oxygen when contaminated, which can support combustion.

Hygiene Measures: Handle in accordance with good industrial hygiene and safety procedures. Wash hands and other exposed areas with mild soap and water before eating, drinking, or smoking and again when leaving work. Wash hands and forearms thoroughly after handling.

Conditions for Safe Storage, Including Any Incompatibilities

Technical Measures: Comply with applicable regulations.

Storage Conditions: Store in a dry, cool and well-ventilated place. Keep container closed when not in use. Keep/Store away from extremely high or low temperatures, direct sunlight, moisture, heat, incompatible materials.

Incompatible Materials: Strong acids, strong bases, strong oxidizers, powdered metals, moisture, organic materials.

Specific End Use(s)

Laundry Booster, Carpet Spot Remover, Hard Surface Cleaner. For professional use only.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

No Occupational Exposure Limits (OELs) have been established for this product or its chemical components.

OxiClean Versatile Stain Remover

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations

Exposure Controls

Appropriate Engineering Controls: For Occupational workplace settings: Emergency eye wash fountains should be available in the immediate vicinity of any potential exposure. Ensure adequate ventilation, especially in confined areas. Ensure all national/local regulations are observed.

Personal Protective Equipment: For Occupational workplace settings and bulk quantities: Gloves. Protective clothing. Safety glasses.



Materials for Protective Clothing: Chemically resistant materials and fabrics.

Hand Protection: Wear chemically resistant protective gloves.

Eye Protection: In case of splash hazard: safety glasses.

Skin and Body Protection: Wear suitable protective clothing.

Respiratory Protection: Not required for normal conditions of use. Use NIOSH-approved air-purifying or supplied-air respirator where airborne concentrations of particulates are expected to exceed exposure limits.

Other Information: When using, do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Information on Basic Physical and Chemical Properties

Physical State	: Solid
Appearance	: White, off-white powder with blue specks
Odor	: None
Odor Threshold	: Not available
pH	: 10.5
Evaporation Rate	: Not available
Melting Point	: Not available
Freezing Point	: Not available
Boiling Point	: 101.67 °C (215.01 °F)
Flash Point	: Not flammable
Auto-ignition Temperature	: Not available
Decomposition Temperature	: Not available
Flammability (solid, gas)	: Not available
Lower Flammable Limit	: Not available
Upper Flammable Limit	: Not available
Vapor Pressure	: Not available
Relative Vapor Density at 20 °C	: Not available
Relative Density	: Not available
Specific Gravity	: 1.06 g/cc @20°C (68°F)
Solubility	: 140 g/L @20°C (68°F).
Partition Coefficient: N-octanol/water	: Not available
Viscosity	: Not available
Explosion Data – Sensitivity to Mechanical Impact	: Not expected to present an explosion hazard due to mechanical impact.
Explosion Data – Sensitivity to Static Discharge	: Not expected to present an explosion hazard due to static discharge.

SECTION 10: STABILITY AND REACTIVITY

Reactivity: Contains an oxidizing material which may accelerate fire.

Chemical Stability: Stable at standard temperature and pressure.

Possibility of Hazardous Reactions: Hazardous polymerization will not occur.

Conditions to Avoid: Direct sunlight, heat, extremely high or low temperatures, incompatible materials, moisture.

Incompatible Materials: Strong acids, strong bases, strong oxidizers, organic materials, powdered metals.

Hazardous Decomposition Products: Carbon oxides (CO, CO₂), sodium oxides, oxygen, irritating fumes.

OxiClean Versatile Stain Remover

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations

SECTION 11: TOXICOLOGICAL INFORMATION

Information on Toxicological Effects - Product

Acute Toxicity: Not classified

LD50 and LC50 Data: Not available

Skin Corrosion/Irritation: Causes skin irritation.

pH: 10.5

Serious Eye Damage/Irritation: Causes serious eye damage.

pH: 10.5

Respiratory or Skin Sensitization: Not classified

Germ Cell Mutagenicity: Not classified

Teratogenicity: Not classified

Carcinogenicity: Not classified

Specific Target Organ Toxicity (Repeated Exposure): Not classified

Reproductive Toxicity: Not classified

Specific Target Organ Toxicity (Single Exposure): Not classified

Aspiration Hazard: Not classified

Symptoms/Injuries After Inhalation: May cause respiratory irritation.

Symptoms/Injuries After Skin Contact: Causes skin irritation.

Symptoms/Injuries After Eye Contact: May cause severe irritation. Prolonged exposure may cause eye damage.

Symptoms/Injuries After Ingestion: Ingestion is likely to be harmful or have adverse effects.

Chronic Symptoms: No additional information available.

Information on Toxicological Effects - Ingredient(s)

LD50 and LC50 Data:

Alcohols, C12-15, ethoxylated (68131-39-5)	
LD50 Oral Rat	1600 mg/kg
LD50 Dermal Rabbit	2500 mg/kg
Sodium percarbonate (15630-89-4)	
LD50 Oral Rat	1034 mg/kg
Sodium carbonate (497-19-8)	
LD50 Oral Rat	4090 mg/kg
LC50 Inhalation Rat	2300 mg/m ³ (Exposure time: 2 h)
Sodium metasilicate (6834-92-0)	
LD50 Oral Rat	1153

SECTION 12: ECOLOGICAL INFORMATION

Toxicity

Ecology - General: Toxic to aquatic life.

Alcohols, C12-15, ethoxylated (68131-39-5)	
LC50 Fish 1	0.59 mg/l
Sodium percarbonate (15630-89-4)	
LC50 Fish 1	70.7 mg/l (Exposure time: 96 h - Species: Pimephales promelas [static])
EC50 Daphnia 1	4.9 mg/l (Exposure time: 48 h - Species: Daphnia pulex)
Sodium carbonate (497-19-8)	
LC50 Fish 1	300 mg/l (Exposure time: 96 h - Species: Lepomis macrochirus [static])
EC50 Daphnia 1	265 mg/l (Exposure time: 48 h - Species: Daphnia magna)
LC 50 Fish 2	310 - 1220 mg/l (Exposure time: 96 h - Species: Pimephales promelas [static])
Sodium metasilicate (6834-92-0)	
LC50 Fish 1	210 mg/l (Exposure time: 96 h - Species: Brachydanio rerio [semi-static])
LC 50 Fish 2	210 mg/l (Exposure time: 96 h - Species: Brachydanio rerio)

OxiClean Versatile Stain Remover

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations

Persistence and Degradability Not available

Bioaccumulative Potential

OxiClean Versatile Stain Remover	
Bioaccumulative Potential	Not established.
Sodium percarbonate (15630-89-4)	
BCF Fish 1	(no bioaccumulation)
Sodium carbonate (497-19-8)	
BCF Fish 1	(no bioaccumulation)

Mobility in Soil Not available

Other Adverse Effects

Other Information: Avoid release to the environment.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal Recommendations: Dispose of waste material in accordance with all local, regional, national, provincial, territorial and international regulations.

Ecology – Waste Materials: This material is hazardous to the aquatic environment. Keep out of sewers and waterways.

SECTION 14: TRANSPORT INFORMATION

In Accordance with DOT Not regulated for transport

In Accordance with IMDG Not regulated for transport

In Accordance with IATA Not regulated for transport

In Accordance with TDG Not regulated for transport

SECTION 15: REGULATORY INFORMATION

US Federal Regulations

OxiClean Versatile Stain Remover	
SARA Section 311/312 Hazard Classes	Immediate (acute) health hazard
Alcohols, C12-15, ethoxylated (68131-39-5)	
Regional legislation Listed on the EU NLP (No Longer Polymers) inventory Listed on the AICS (Australian Inventory of Chemical Substances) Listed on the Canadian DSL (Domestic Substances List) Listed on IECSC (Inventory of Existing Chemical Substances Produced or Imported in China) Listed on the Japanese ENCS (Existing & New Chemical Substances) inventory Listed on the Korean ECL (Existing Chemicals List) Listed on NZIoC (New Zealand Inventory of Chemicals) Listed on PICCS (Philippines Inventory of Chemicals and Chemical Substances) Listed on the United States TSCA (Toxic Substances Control Act) inventory Japanese Pollutant Release and Transfer Register Law (PRTR Law)	
Sodium percarbonate (15630-89-4)	
Regional legislation Listed on the AICS (Australian Inventory of Chemical Substances) Listed on the Canadian DSL (Domestic Substances List) Listed on IECSC (Inventory of Existing Chemical Substances Produced or Imported in China) Listed on the EEC inventory EINECS (European Inventory of Existing Commercial Chemical Substances) Listed on the Japanese ENCS (Existing & New Chemical Substances) inventory Listed on the Korean ECL (Existing Chemicals List) Listed on NZIoC (New Zealand Inventory of Chemicals) Listed on PICCS (Philippines Inventory of Chemicals and Chemical Substances) Listed on the United States TSCA (Toxic Substances Control Act) inventory	
Sodium carbonate (497-19-8)	

OxiClean Versatile Stain Remover

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations

Regional legislation

Listed on the AICS (Australian Inventory of Chemical Substances)
Listed on the Canadian DSL (Domestic Substances List)
Listed on IECSC (Inventory of Existing Chemical Substances Produced or Imported in China)
Listed on the EEC inventory EINECS (European Inventory of Existing Commercial Chemical Substances)
Listed on the Japanese ENCS (Existing & New Chemical Substances) inventory
Listed on the Japanese ISHL (Industrial Safety and Health Law)
Listed on the Korean ECL (Existing Chemicals List)
Listed on NZIoC (New Zealand Inventory of Chemicals)
Listed on PICCS (Philippines Inventory of Chemicals and Chemical Substances)
Listed on the United States TSCA (Toxic Substances Control Act) inventory
Listed on the Canadian IDL (Ingredient Disclosure List)

Sodium metasilicate (6834-92-0)

Regional legislation

Listed on the AICS (Australian Inventory of Chemical Substances)
Listed on the Canadian DSL (Domestic Substances List)
Listed on IECSC (Inventory of Existing Chemical Substances Produced or Imported in China)
Listed on the EEC inventory EINECS (European Inventory of Existing Commercial Chemical Substances)
Listed on the Japanese ENCS (Existing & New Chemical Substances) inventory
Listed on the Korean ECL (Existing Chemicals List)
Listed on NZIoC (New Zealand Inventory of Chemicals)
Listed on PICCS (Philippines Inventory of Chemicals and Chemical Substances)
Listed on the United States TSCA (Toxic Substances Control Act) inventory
Listed on the Canadian IDL (Ingredient Disclosure List)


US State Regulations

No additional information available

Canadian Regulations

OxiClean Versatile Stain Remover

WHMIS Classification	Class D Division 2 Subdivision B - Toxic material causing other toxic effects
----------------------	---



Alcohols, C12-15, ethoxylated (68131-39-5)

Listed on the Canadian DSL (Domestic Substances List)

WHMIS Classification	Class D Division 2 Subdivision B - Toxic material causing other toxic effects
----------------------	---

Sodium percarbonate (15630-89-4)

Listed on the Canadian DSL (Domestic Substances List)

WHMIS Classification	Class C - Oxidizing Material Class D Division 2 Subdivision B - Toxic material causing other toxic effects
----------------------	---

Sodium carbonate (497-19-8)

Listed on the Canadian DSL (Domestic Substances List)

Listed on the Canadian IDL (Ingredient Disclosure List)

IDL Concentration 1 %

WHMIS Classification	Class D Division 2 Subdivision B - Toxic material causing other toxic effects Class E - Corrosive Material
----------------------	---

Sodium metasilicate (6834-92-0)

Listed on the Canadian DSL (Domestic Substances List)

Listed on the Canadian IDL (Ingredient Disclosure List)

OxiClean Versatile Stain Remover

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations

IDL Concentration 1 %	
WHMIS Classification	Class E - Corrosive Material Class D Division 2 Subdivision B - Toxic material causing other toxic effects

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations (CPR) and the SDS contains all of the information required by CPR.

SECTION 16: OTHER INFORMATION, INCLUDING DATE OF PREPARATION OR LAST REVISION

Revision Date : 03/26/2015

Other Information : This document has been prepared in accordance with the SDS requirements of the OSHA Hazard Communication Standard 29 CFR 1910.1200. This product is labeled in accordance with regulations administered by the Consumer Product Safety Commission (CPSC). The use pattern and exposure in the workplace are generally not consistent with those experienced by consumers. The requirements of the Occupational Safety and Health Administration applicable to this SDS differ from the labeling requirements of the CPSC and, as a result, this SDS may contain additional health hazard information not pertinent to consumer use and not found on the product label.

GHS Full Text Phrases:

Acute Tox. 4 (Oral)	Acute toxicity (oral) Category 4
Aquatic Acute 1	Hazardous to the aquatic environment - Acute Hazard Category 1
Aquatic Acute 2	Hazardous to the aquatic environment - Acute Hazard Category 2
Aquatic Chronic 3	Hazardous to the aquatic environment - Chronic Hazard Category 3
Comb. Dust	Combustible Dust
Eye Dam. 1	Serious eye damage/eye irritation Category 1
Eye Irrit. 2A	Serious eye damage/eye irritation Category 2A
Met. Corr. 1	Corrosive to metals Category 1
Ox. Sol. 2	Oxidizing solids Category 2
Skin Corr. 1B	Skin corrosion/irritation Category 1B
Skin Irrit. 2	Skin corrosion/irritation Category 2
STOT SE 3	Specific target organ toxicity (single exposure) Category 3
	May form combustible dust concentrations in air
H272	May intensify fire; oxidizer
H290	May be corrosive to metals
H302	Harmful if swallowed
H314	Causes severe skin burns and eye damage
H315	Causes skin irritation
H318	Causes serious eye damage
H319	Causes serious eye irritation
H335	May cause respiratory irritation
H400	Very toxic to aquatic life
H401	Toxic to aquatic life
H412	Harmful to aquatic life with long lasting effects

Party Responsible for the Preparation of This Document

Church & Dwight 500
Charles Ewing Blvd
Ewing Township, NJ 08628
T 1-800-524-1328

This Product Safety Data Sheet is offered solely for your information, consideration and investigation. Church & Dwight Co., Inc. provides no warranties; either expressed or implied, and assumes no responsibility for the accuracy or completeness of data contained herein. Church & Dwight Co., Inc. urges persons receiving this information to make their own determination as to the information suitability for their particular application.

North America GHS US 2012 & WHMIS