



# Safety Data Sheet

Applicable Items: AOD3232301

Effective Date:  
April 2025  
CH12323

## 1. Identification

### 1.1. Product identifier

**Product Identity**

CH12323 Oil Stain Remover with Microbes

**Alternate Names**

Oil Eater® Overnight Oil Stain Remover / Microbe enhanced

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

**Intended use**

See Label

### 1.3. Details of the supplier of the safety data sheet

**Company Name**

Kafko International, Ltd.  
3555 Howard St  
Skokie, IL 60076

**Emergency**

**Customer Service: Kafko**

847-763-0333

## 2. Hazard(s) identification

### 2.1. Classification of the substance or mixture

Eye Damage 2B;H320 Causes eye irritation.

### 2.2. Label elements

## Warning

H320 Causes eye irritation.

**[Prevention]**

P264 Wash thoroughly after handling.

**[Response]**

P305+351+338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses if present and easy to do - continue rinsing.

P337+313 If eye irritation persists: Get medical advice or attention.

**[Storage]**

No GHS storage statements

**[Disposal]**

No GHS disposal statements



# Safety Data Sheet

Applicable Items: AOD3232301

Effective Date:  
April 2025  
CH12323

## 3. Composition/information on ingredients

This product contains the following substances that present a hazard within the meaning of the relevant State and Federal Hazardous Substances regulations.

Ingredient/Chemical Designations	Weight %	GHS Classification	Notes
Silica/Surfactant Powder Blend CAS Number: Proprietary	10 - 25	Eye Dam. 2B;H320	----

The specific chemical identity and/or exact percentage (concentration) of composition has been withheld as a trade secret.

\*PBT/vPvB - PBT-substance or vPvB-substance.

The full texts of the phrases are shown in Section 16.

## Section 4. First aid measures

### 4.1. Description of first aid measures

<b>General</b>	In all cases of doubt, or when symptoms persist, seek medical attention. Never give anything by mouth to an unconscious person.
<b>Inhalation</b>	Remove to fresh air, keep patient warm and at rest. If breathing is irregular or stopped, give artificial respiration. If unconscious, place in the recovery position and obtain immediate medical attention. Give nothing by mouth.
<b>Eyes</b>	Irrigate copiously with clean water for at least 15 minutes, holding the eyelids apart and seek medical attention.
<b>Skin</b>	Remove contaminated clothing. Wash skin thoroughly with soap and water or use a recognized skin cleanser.
<b>Ingestion</b>	If swallowed obtain immediate medical attention. Keep at rest. Do NOT induce vomiting.

### 4.2. Most important symptoms and effects, both acute and delayed

<b>Overview</b>	No specific symptom data available. Treat symptomatically. Check section 2.2 (GHS Label Elements) for further details.
<b>Eyes</b>	Causes eye irritation.

## Section 5. Fire-fighting measures

### 5.1. Extinguishing media

Recommended extinguishing media; alcohol resistant foam, CO<sup>2</sup>, powder, water spray.  
Unsuitable extinguishing media: Do not use; water jet.

### 5.2. Special hazards arising from the substance or mixture

Hazardous decomposition: No hazardous decomposition data available.



## Safety Data Sheet

Applicable Items: AOD3232301

Effective Date:  
April 2025  
CH12323

### 5.3. Advice for fire-fighters

As with all fires, wear positive pressure, self-contained breathing apparatus, (SCBA) with a full face piece and protective clothing. Persons without respiratory protection should leave area. Wear SCBA during clean-up immediately after fire. No smoking.

ERG Guide No. ---

## Section 6. Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Put on appropriate personal protective equipment (see section 8).

### 6.2. Environmental precautions

Do not allow spills to enter drains or waterways.

Use good personal hygiene practices. Wash hands before eating, drinking, smoking, or using toilet. Promptly remove soiled clothing and wash thoroughly before reuse.

### 6.3. Methods and material for containment and cleaning up

Ventilate the area and avoid breathing vapors. Take the personal protective measures listed in section 8. Contain and absorb spillage with non-combustible materials e.g. sand, earth, and vermiculite. Place in closed containers outside buildings and dispose of according to the Waste Regulations.

## Section 7. Handling and storage

### 7.1. Precautions for safe handling

Handle containers carefully to prevent damage and spillage.

Check section 2.2 (GHS Label Elements) for further details. - [Prevention]

### 7.2. Conditions for safe storage, including any incompatibilities

Incompatible materials: Any acidic material, ammonia, urea, oxidizable materials and metals such as nickel, copper, tin, aluminum and iron.

Check section 2.2 (GHS Label Elements) for further details. - [Storage]

### 7.3. Specific end use(s)

No data available.



# Safety Data Sheet

Applicable Items: AOD3232301

Effective Date:  
April 2025  
CH12323

## Section 8. Exposure controls / personal protection

### 8.1. Control parameters

CAS No.	Ingredient	Exposure	
		Source	Value
Proprietary	Silica/Surfactant Powder Blend	OSHA	No Established Limit
		ACGIH	No Established Limit
		NIOSH	No Established Limit

### 8.2. Exposure controls

- Respiratory** Use NIOSH/MSHA approved respirator, following manufacturer's recommendations when concentrations exceed permissible exposure limits.
- Eyes** Wear safety glasses with side shields to protect the eyes. An eye wash station is suggested as a good workplace practice.
- Skin** Chemical resistant clothing such as coveralls/apron and boots should be worn. Chemical impervious gloves required.
- Engineering Controls** Provide adequate ventilation. Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction. If these are not sufficient to maintain concentrations of particulates and any vapor below occupational exposure limits suitable respiratory protection must be worn.
- Other Work Practices** Use good personal hygiene practices. Wash hands before eating, drinking, smoking, or using toilet. Promptly remove soiled clothing and wash thoroughly before reuse.

Check section 2.2 (GHS Label Elements) for further details.

## Section 9. Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

<b>Appearance</b>	Color: White, opaque, viscous	Physical State: Liquid
<b>Odor</b>	Characteristic	
<b>Odor threshold</b>	Not determined	
<b>pH</b>	9.0 – 10.0	
<b>Melting point / freezing point</b>	Not Measured	
<b>Initial boiling point and boiling range</b>	Not Measured	
<b>Flash Point</b>	Not Measured	
<b>Evaporation rate (Ether = 1)</b>	Not Measured	
<b>Flammability (solid, gas)</b>	Not Applicable	
<b>Upper/lower flammability or explosive limits</b>	<b>Lower Explosive Limit:</b> Not Measured	<b>Upper Explosive Limit:</b> Not Measured
<b>Vapor pressure (Pa)</b>	Not Measured	



## Safety Data Sheet

Applicable Items: AOD3232301

Effective Date:  
April 2025  
CH12323

Vapor Density	Not Measured
Relative Density	Not Measured
Solubility in Water	Not Measured
Partition coefficient n-octanol/water (Log Kow)	Not Measured
Auto-ignition temperature	Not Measured
Decomposition temperature	Not Measured
Viscosity (cSt)	Not Measured
VOC Content	Not Measured

### 9.2. Other information

No other relevant information.

## Section 10. Stability and reactivity

### 10.1. Reactivity

Hazardous Polymerization will not occur.

### 10.2. Chemical stability

Stable under normal circumstances.

### 10.3. Possibility of hazardous reactions

No data available.

### 10.4. Conditions to avoid

No data available.

### 10.5. Incompatible materials

Any acidic material, ammonia, urea, oxidizable materials and metals such as nickel, copper, tin, aluminum and iron.

### 10.6. Hazardous decomposition products

No hazardous decomposition data available.

## Section 11. Toxicological information

### Acute toxicity

Note: When no route specific LD50 data is available for an acute toxin, the converted acute toxicity point estimate was used in the calculation of the product's ATE (Acute Toxicity Estimate).



# Safety Data Sheet

Applicable Items: AOD3232301

Effective Date:  
April 2025  
CH12323

Ingredient	Oral LD50, mg/kg	Skin LD50, mg/kg	Inhalation Vapor LC50, mg/L/4hr	Inhalation Dust/Mist LC50, mg/L/4hr	Inhalation Gas LC50, ppm
Silica/Surfactant Powder Blend - (Proprietary)	No data available	No data available	No data available	No data available	No data available

## Carcinogen Data

CAS No.	Ingredient	Source	Value
Proprietary	Silica/Surfactant Powder Blend	OSHA	Regulated Carcinogen: No;
		NTP	Known: No; Suspected: No;
		IARC	Group 1: No; Group 2a: No; Group 2b: No; Group 3: No; Group 4: No;
		ACGIH	No Established Limit

Classification	Category	Hazard Description
Acute toxicity (oral)	---	Not Applicable
Acute toxicity (dermal)	---	Not Applicable
Acute toxicity (inhalation)	---	Not Applicable
Skin corrosion/irritation	---	Not Applicable
Serious eye damage/irritation	2B	Causes eye irritation.
Respiratory sensitization	---	Not Applicable
Skin sensitization	---	Not Applicable
Germ cell mutagenicity	---	Not Applicable
Carcinogenicity	---	Not Applicable
Reproductive toxicity	---	Not Applicable
STOT-single exposure	---	Not Applicable
STOT-repeated exposure	---	Not Applicable
Aspiration hazard	---	Not Applicable

## Section 12. Ecological information

### 12.1. Toxicity

No additional information provided for this product. See Section 3 for chemical specific data.

### Aquatic Ecotoxicity

Ingredient	96 hr LC50 fish, mg/L	48 hr EC50 crustacea, mg/L	ErC50 algae, mg/L
Silica/Surfactant Powder Blend - (Proprietary)	Not Available	Not Available	Not Available



# Safety Data Sheet

Applicable Items: AOD3232301

Effective Date:  
April 2025  
CH12323

## 12.2. Persistence and degradability

There is no data available on the preparation itself.

## 12.3. Bioaccumulative potential

Not Measured

## 12.4. Mobility in soil

No data available.

## 12.5. Results of PBT and vPvB assessment

This product contains no PBT/vPvB chemicals.

## 12.6. Other adverse effects

No data available.

## Section 13. Disposal considerations

### 13.1. Waste treatment methods

Observe all federal, state, and local regulations when disposing of this substance.

## Section 14. Transport information

	<b>DOT (Domestic Surface Transportation)</b>	<b>IMO / IMDG (Ocean Transportation)</b>	<b>ICAO/IATA</b>
<b>14.1. UN number</b>	Not Regulated	Not Regulated	Not Regulated
<b>14.2. UN proper shipping name</b>	Not Regulated	Not Regulated	Not Regulated
<b>14.3. Transport hazard class(es)</b>	<b>DOT Hazard Class:</b> Not Applicable <b>Sub Class:</b> Not Applicable	<b>IMDG:</b> Not Applicable <b>Sub Class:</b> Not Applicable	<b>Air Class:</b> Not Applicable <b>Sub Class:</b> Not Applicable
<b>14.4. Packing group</b>	Not Applicable	Not Applicable	Not Applicable
<b>14.5. Environmental hazards</b>			
<b>IMDG</b>	Marine Pollutant: No;		
<b>14.6. Special precautions for user</b>	Not Applicable		

## Section 15. Regulatory information

<b>Regulatory Overview</b>	The regulatory data in Section 15 is not intended to be all-inclusive, only selected regulations are represented.
<b>Toxic Substance Control Act (TSCA)</b>	All components of this material are either listed or exempt from listing on the TSCA Inventory.
<b>EPCRA 302 Extremely Hazardous:</b>	To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.



## Safety Data Sheet

Applicable Items: AOD3232301

Effective Date:  
April 2025  
CH12323

### EPCRA 313 Toxic Chemicals:

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

### Proposition 65 - Carcinogens (>0.0%):

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

### Proposition 65 - Developmental Toxins (>0.0%):

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

### Proposition 65 - Female Repro Toxins (>0.0%):

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

### Proposition 65 - Male Repro Toxins (>0.0%):

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

### Proposition 65 Label Warning:

This product contains no chemicals known to the State of California to cause cancer and birth defects or other reproductive harm.

## Section 16. Other information

**Revision Date** 10/11/2022

The information and recommendations contained herein are based upon data believed to be correct. However, no guarantee or warranty of any kind, expressed or implied, is made with respect to the information contained herein. We accept no responsibility and disclaim all liability for any harmful effects which may be caused by exposure to our products. Customers/users of this product must comply with all applicable health and safety laws, regulations, and orders.

The full text of the phrases appearing in section 3 is:

H320 Causes eye irritation.

The information contained herein is furnished without warranty of any kind. The above information is believed to be correct but does not purport to be all inclusive and should be used only as a guide. Users should make independent determinations of the suitability and completeness of information from all sources to assure proper use and disposal of these materials and the safety and health of employees and customers.

End of Document