




# Mini Catalog USA • Canada

UNITED STATES  
CANADA

# History of Henco


## An introduction

Henco's success story began in 1992 when entrepreneur Louis Hendrickx developed the idea for a high quality **multilayer pipe**.

Today, our **300 employees** ensure an annual production and sales of over **450 million feet of pipe** and more than **11 million fittings**.



Since 2008, Henco is a part of the **Aalberts group**, a key innovator in the field of ground-breaking technologies for the industry and everyday life, giving us a competitive edge. The connection and shared knowledge between Henco and Aalberts facilitate great achievements. **By staying focused and true to our values**, we will achieve our objectives together.



**1993**

Production  
multilayer pipe



**2003**

Start of  
Henco Floor



**2019**

Building of new  
distribution centre



**1992**

Start of Henco



**1999**

Production  
PVDF press  
fittings



**2007**

Production Vision  
push fittings



**2024**

Production  
foam line

# What we do

## Applications



Sanitary



Heating



Underfloor Heating



Gas




Sprinkler



Compressed Air

## Henco in numbers



**+ 450 million**  
feet / year

4 x around  
the world



**± 11 million**  
fittings / year

Belgium  
± 11 million  
inhabitants




**± 300**  
employees

### Quality

Our pipes and fittings are being tested in our lab in multiple ways, to guarantee their quality. The high quality of our products is being stated by our certificates.



**1.000.000 sqft**  
surface area



**+ 10.000.000 sqft**  
underfloor heating  
/ year



**± 80**  
countries active

### Complete solution

Multilayer pipes, fittings, underfloor heating, manifolds and user-friendly tools to install each project quickly, problemfree and efficiently. Henco has always the right solution for you!

Henco Industries is an organization that delivers **worldwide** from her home base in Herentals, Belgium.




# Multilayer Pipe

**Our multilayer pipe is undoubtedly at the heart of our extensive range.** The Henco multilayer pipe has been designed for the most demanding and diverse applications, based on the principle that only the best quality is good enough.

The result is the leading, **most reliable multifunctional pipe on the international market.** The Henco multilayer pipe combines all of the advantages of synthetic materials and metal pipes. Our comprehensive range also includes pre-insulated pipes, protection hoses and gas pipes.

## These are the key properties:

- ✓ Butt-welded aluminium
- ✓ 100% oxygen-tight
- ✓ Low coefficient of linear expansion, like metal pipe
- ✓ Resistant to corrosion, chemical and electrochemical impacts
- ✓ Maximum working pressure 145 psi and maximum operating temperature 203°F
- ✓ PE-Xc electron beam crosslinked inner and outer pipe
- ✓ High resistance to pressure and temperature
- ✓ Smooth surface - low loss of pressure
- ✓ As lightweight as a synthetic pipe
- ✓ Flexible, easy to bend even at low temperatures, retains shape after bending



**A Crosslinked Polyethylene (PE-Xc)**  
Physical crosslinking C (Xc)

**B Adhesive layer**

**C Aluminium (AL)**  
Butt welded

# Underfloor Heating

---



Are you looking for a **discrete heating system** that provides pleasant, comfortable heat? Underfloor heating is the right choice.

Henco underfloor heating has a lot of advantages and possibilities. We are delighted to list them for you.

Henco Floor offers a comprehensive range of high-quality mounting system, manifolds and control units, spearheaded by the Henco multilayer pipe. The installation of a **long-lasting high-quality pipe** is of utmost importance for an underfloor heating system. After all, it is expensive to replace the piping system.

- ✓ Healthy air
- ✓ No invasion of space
- ✓ Energy efficient & economical
- ✓ Unlimited choice of floor coverings
- ✓ Compatible with any source of energy
- ✓ No fire hazard

In addition to this range of top-class products, Henco boasts **experienced** and **customer friendly employees**, guaranteeing the necessary **support** on all levels.





### Henco Multilayer pipe RIXc (Coil)

| Article           | Type        |           |
|-------------------|-------------|-----------|
| 1000ft-R160212-US | 16X2 / ½"   | 1000 feet |
| 250ft-R160212-US  | 16X2 / ½"   | 250 feet  |
| 300ft-R160212-US  | 16X2 / ½"   | 300 feet  |
| 450ft-R200216-US  | 20X2 / ¾"   | 450 feet  |
| 400ft-R200216-US  | 20X2 / ¾"   | 400 feet  |
| 500ft-R200216-US  | 20X2 / ¾"   | 500 feet  |
| 500ft-R252520-US  | 25X2,5 / ¾" | 500 feet  |
| 100ft-320326-US   | 32X3 / 1"   | 100 feet  |
| 300ft-320326-US   | 32X3 / 1"   | 300 feet  |



### Nickel plated eurocone (3/4"F)

| Article | Type   |
|---------|--------|
| EK16-2  | Ø½"x¾" |
| EK20-2  | Ø¾"x¾" |



### Composite manifold, adjustable with flow meter, fill and drain valve and manual air vents

| Article                | Type |
|------------------------|------|
| UFH-0605MDK02-1.25G    | 2 x  |
| UFH-0605MDK03-US-1.25G | 3 x  |
| UFH-0605MDK04-US-1.25G | 4 x  |
| UFH-0605MDK05-US-1.25G | 5 x  |
| UFH-0605MDK06-US-1.25G | 6 x  |
| UFH-0605MDK07-US-1.25G | 7 x  |
| UFH-0605MDK08-US-1.25G | 8 x  |
| UFH-0605MDK09-US-1.25G | 9 x  |
| UFH-0605MDK10-US-1.25G | 10 x |
| UFH-0605MDK11-US-1.25G | 11 x |
| UFH-0605MDK12-US-1.25G | 12 x |



### Composite connector for MDK Manifold

| Article     |
|-------------|
| UFH-MDK-CON |



### Automatic air vent in composite for MDK manifold

| Article    | Type |
|------------|------|
| UFH-MDK-AO | ¾"   |




### Stainless steel manifold, adjustable with flow meter, fill and drain valve and manual air vents

| Article                 | Type |
|-------------------------|------|
| UFH-0605MDSS02-US-1.25G | 2 x  |
| UFH-0605MDSS03-US-1.25G | 3 x  |
| UFH-0605MDSS04-US-1.25G | 4 x  |
| UFH-0605MDSS05-US-1.25G | 5 x  |
| UFH-0605MDSS06-US-1.25G | 6 x  |
| UFH-0605MDSS07-US-1.25G | 7 x  |
| UFH-0605MDSS08-US-1.25G | 8 x  |
| UFH-0605MDSS09-US-1.25G | 9 x  |
| UFH-0605MDSS10-US-1.25G | 10 x |
| UFH-0605MDSS11-US-1.25G | 11 x |
| UFH-0605MDSS12-US-1.25G | 12 x |
| UFH-0605MDSS13-US-1.25G | 13 x |
| UFH-0605MDSS14-US-1.25G | 14 x |
| UFH-0605MDSS15-US-1.25G | 15 x |




### Ball valve with gasket, nickel-plated

| Article            | Type  |
|--------------------|-------|
| UFH-BM0606-VN-NPT  | 1"x1" |
| UFH-BM0606T-VN-NPT | 1"x1" |



### Composite manifold set, adjustable with flow meter, fill and drain valve and manual air vents. Ball valves UFH-BM0606-VN-NPT are included

| Article             | Type |
|---------------------|------|
| UFH-0605MDK02-US-BV | 2 x  |
| UFH-0605MDK03-US-BV | 3 x  |
| UFH-0605MDK04-US-BV | 4 x  |
| UFH-0605MDK05-US-BV | 5 x  |
| UFH-0605MDK06-US-BV | 6 x  |
| UFH-0605MDK07-US-BV | 7 x  |
| UFH-0605MDK08-US-BV | 8 x  |
| UFH-0605MDK09-US-BV | 9 x  |
| UFH-0605MDK10-US-BV | 10 x |
| UFH-0605MDK11-US-BV | 11 x |
| UFH-0605MDK12-US-BV | 12 x |



### Stainless steel manifold set, adjustable with flow meter, fill and drain valve and manual air vents. Ball valves UFH-BM0606T-VN-NPT are included

| Article              | Type |
|----------------------|------|
| UFH-0605MDSS02-US-BV | 2 x  |
| UFH-0605MDSS03-US-BV | 3 x  |
| UFH-0605MDSS04-US-BV | 4 x  |
| UFH-0605MDSS05-US-BV | 5 x  |
| UFH-0605MDSS06-US-BV | 6 x  |
| UFH-0605MDSS07-US-BV | 7 x  |
| UFH-0605MDSS08-US-BV | 8 x  |
| UFH-0605MDSS09-US-BV | 9 x  |
| UFH-0605MDSS10-US-BV | 10 x |
| UFH-0605MDSS11-US-BV | 11 x |
| UFH-0605MDSS12-US-BV | 12 x |
| UFH-0605MDSS13-US-BV | 13 x |
| UFH-0605MDSS14-US-BV | 14 x |
| UFH-0605MDSS15-US-BV | 15 x |





#### Straight coupling

| Article  | Type        |
|----------|-------------|
| 2-1616-S | 1/2" x 1/2" |
| 2-2020-S | 3/4" x 3/4" |



#### Decoiler, standard model

| Article | Type             |
|---------|------------------|
| UFH-VLA | 82 ft - 1,968 ft |



#### Protection sleeve for expansion joint

| Article  | Type       |
|----------|------------|
| UFH-DH40 | 15.75 inch |



#### Braid hook

| Article     | Type |
|-------------|------|
| UFH-RAS-VLE |      |



#### Kalispeed for Ø16, 20 and 26

| Article    | Type                 |
|------------|----------------------|
| KS-P162026 | Ø1/2", 5/8" and 3/4" |



#### Set with KS-K and KS-M for Ø16, 20, 26 and 32

| Article  | Type                     |
|----------|--------------------------|
| KS-MSET4 | Ø1/2", Ø5/8", Ø3/4", Ø1" |



#### Set with KS-K and KS-M for Ø16, 20 and 26

| Article  | Type                |
|----------|---------------------|
| KS-MSET1 | Ø1/2", Ø5/8", Ø3/4" |



#### Guillotine cutter

| Article     | Type           |
|-------------|----------------|
| IM1426PRESS | 1/2" till 3/4" |



#### Wheel cutter

| Article | Type         |
|---------|--------------|
| IM63    | 1/2" till 1" |



#### Cutter to open the packing paper

| Article | Type |
|---------|------|
| SAFECUT |      |



#### Endcap with washer

| Article    | Type |
|------------|------|
| UFH-BS05-M | 3/4" |



#### Steel strand, plasticized, to connect pipe on steel mesh

| Article         | Bag      |
|-----------------|----------|
| UFH-RAS-BIND15A | 250 pc.  |
| UFH-RAS-BIND15B | 2500 pc. |



#### Testcap red for Henco Pipe

| Article       | Bag   |
|---------------|-------|
| TESTPLUG16-RO | Ø1/2" |
| TESTPLUG20-RO | Ø3/4" |

# The MyHenco platform is the perfect fit.

MyHenco, a digital assistant that is always within reach & available 24/7. More than just an online catalogue. Designed with a dynamic and user-friendly platform. MyHenco allows a personalised dashboard, features support articles and video's and helps to answer any queries our professionals may have.

Sign up to MyHenco at [myhenco.com](https://myhenco.com)

