



SAFETY DATA SHEET

Supersedes Date: 11 Feb 2022

Revision Date: 13 Feb 2023

Version: 2.0

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Label Name Encapuclean Green DS

Other means of identification

UPC Code(s) Not applicable

Product code CC15

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Carpet cleaning solution

Uses advised against Follow label instructions. Not recommended for any use except intended use.

Supplier's details

Supplier Address

AramSCO Inc.
4282 South 590 West
Salt Lake City, UT 84123
USA

Manufacturer Address

AramSCO Inc.
4282 South 590 West
Salt Lake City, UT 84123
USA

Emergency telephone number

Company Phone Number 1-800-658-5314

Company Emergency Phone Number United States: 1-800-535-5053 (INFOTRAC – 24 hours, 7 days a week)

Emergency telephone International: 1-352-323-3500 (INFOTRAC – 24 hours, 7 days a week)

Poison Control 1-800-222-1222 (24 hour)

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin corrosion/irritation	Category 2
Serious eye damage/eye irritation	Category 2

GHS Label elements, including precautionary statements

Emergency Overview

Warning

Hazard Statements

Causes skin irritation

Causes serious eye irritation

**Appearance** Clear Liquid**Physical state** liquid**Odor** Sweet Floral**Precautionary Statements - Prevention**

Wash face, hands and any exposed skin thoroughly after handling
 Wear protective gloves/protective clothing/eye protection/face protection

Precautionary Statements - Response

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 If eye irritation persists: Get medical advice/attention
 IF ON SKIN: Wash with plenty of soap and water
 If skin irritation occurs: Get medical advice/attention
 Take off contaminated clothing and wash before reuse

Hazards not otherwise classified (HNOC)**Other information**

- Causes mild skin irritation
- Harmful to aquatic life

General Hazards

Keep out of reach of children

Please see Section 11. Toxicological Information for further information

9.2311% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS-No	Weight %	Trade Secret
Proprietary Polymer	Proprietary	5 - 10	*
Proprietary Surfactant	Proprietary	1 - 5	*
Proprietary Surfactant	Proprietary	1 - 5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret

4. FIRST AID MEASURES

First aid measures for different exposure routes**General advice**

If symptoms persist, call a physician.

Eye contact

Immediately flush with plenty of water. After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes. Keep eye wide open while rinsing. If symptoms persist, call a physician.

Skin contact

Remove and wash contaminated clothing before re-use. Wash off immediately with plenty of water. If skin irritation persists, call a physician. Immediate medical attention is not required. Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes.

Toxic - Inhalation

Immediate medical attention is not required. Move to fresh air in case of accidental inhalation of vapors. If symptoms persist, call a physician.

Ingestion Clean mouth with water and drink afterwards plenty of water. Never give anything by mouth to an unconscious person. Consult a physician. Do NOT induce vomiting.

Protection of First-aiders Use personal protective equipment.

Most important symptoms/effects, acute and delayed

Main Symptoms No information available.

Indication of immediate medical attention and special treatment needed, if necessary

Notes to physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable Extinguishing Media CAUTION: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

No information available.

Hazardous Combustion Products No information available.

Explosion Data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective Equipment and Precautions for Firefighters

Wear self contained breathing apparatus for fire fighting if necessary.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Use personal protective equipment. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak.

Advice for emergency responders For personal protection see section 8.

Environmental precautions

Environmental precautions See Section 12 for additional Ecological Information. Do not flush into surface water or sanitary sewer system. Prevent further leakage or spillage if safe to do so. Prevent product from entering drains.

Methods and materials for containment and cleaning up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Use personal protective equipment. Dam up. Cover liquid spill with sand, earth or other noncombustible absorbent material. Take up mechanically, placing in appropriate containers for disposal. Clean contaminated surface thoroughly. Soak up with inert absorbent material. Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Use only in area provided with appropriate exhaust ventilation. Wear personal protective equipment. Do not breathe vapors or spray mist.

Conditions for safe storage, including any incompatibilities

Technical measures/Storage conditions Keep containers tightly closed in a cool, well-ventilated place. Keep in properly labeled containers.

Packaging material Keep product in packaging product is initially sold in.

Incompatible products None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines This product does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

Appropriate engineering controls

Engineering Measures Showers
Eyewash stations
Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/Face Protection Tightly fitting safety goggles. Face-shield.

Skin and body protection No special protective equipment required.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

Hygiene measures When using, do not eat, drink or smoke. Provide regular cleaning of equipment, work area and clothing.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical and chemical properties

Physical state	liquid	Odor	Added: Sweet Floral
Appearance	Clear Liquid		Fragrance
Color	Light Amber	Odor threshold	No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	8	
pH RTU	7.5	
Melting point	No information available	
Boiling point/boiling range	No information available	
Flash Point	> 100 °C / > 212 °F	
Evaporation rate	= 1	
Flammability (solid, gas)	No information available	
Flammability Limits in Air		
Upper Flammability Limit	No information available	

Lower Flammability Limit	No information available	
Vapor pressure	No information available	
Vapor density	No information available	
Specific Gravity	1.021	
Water solubility	Soluble in water	
Solubility in other solvents	No information available	
Partition coefficient: n-octanol/water	No information available	
Autoignition temperature	No information available	
Decomposition temperature	No information available	
Viscosity, kinematic	No information available	200 cps
Viscosity, dynamic	No information available	
Explosive properties	No information available	
Oxidizing Properties	No information available	

Other information

Softening point	No information available
Molecular weight	No information available
VOC Content(%)	No information available
Density VALUE	No information available
Bulk Density VALUE	No information available
Fragrance	Sweet Floral Fragrance

10. STABILITY AND REACTIVITY

Reactivity**Chemical stability**

Stable under recommended storage conditions.

Possibility of hazardous reactions

None under normal processing.

Hazardous Polymerization	None under normal processing.
---------------------------------	-------------------------------

Conditions to Avoid

Extremes of temperature and direct sunlight.

Incompatible Materials

None known based on information supplied.

Hazardous Decomposition Products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure**Product Information**

Toxic - Inhalation	Avoid breathing vapors or mists. May cause irritation of respiratory tract.
Eye contact	Avoid contact with eyes. Irritating to eyes.
Skin contact	Avoid contact with skin. Irritating to skin.
Ingestion	Do not taste or swallow. Ingestion may cause stomach discomfort. May cause irritation.

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation	No information available.
Eye damage/irritation	No information available.
Sensitization	No information available.
Germ Cell Mutagenicity	No information available.
Carcinogenicity	No information available.
Reproductive toxicity	No information available.
Developmental Toxicity	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Chronic toxicity	Avoid repeated exposure.
Aspiration hazard	No information available.

Numerical measures of toxicity - Product Information

Unknown acute toxicity 9.2311% of the mixture consists of ingredient(s) of unknown toxicity
The following values are calculated based on chapter 3.1 of the GHS document .
ATEmix (oral) 11572

12. ECOLOGICAL INFORMATION

Ecotoxicity

9.3307% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Other adverse effects

No information available

13. DISPOSAL CONSIDERATIONS

Waste treatment

Waste Disposal Methods

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Do not re-use empty containers.

14. TRANSPORT INFORMATION

DOT

Not regulated

IMDG

Not regulated

IATA

Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA

Complies

DSL/NDSL Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

SARA 311/312 Hazard Categories

Acute Health Hazard	Yes
Chronic Health Hazard	No
Fire Hazard	No
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

Clean Water Act

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

US State Regulations

California Proposition 65

This product can expose you to chemicals including 1,4-Dioxane, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

U.S. State Right-to-Know Regulations

This product does not contain any substances regulated by state right-to-know regulations

U.S. EPA Label information

EPA Pesticide Registration Number Not applicable

16. OTHER INFORMATION

<u>NFPA</u>	Health hazard 1	Flammability 1	Instability 0	Physical and chemical hazards -
<u>HMIS</u>	Health hazard 1	Flammability 1	Physical Hazard 0	Personal protection X

Prepared By Aramsco
 Environmental Health & Safety
Revision Date 13 Feb 2023

Revision Note
 13 Feb 2023 – Update Prop 65 Warning
 11 Feb 2022 – Review, no changes made

Disclaimer

The (M)SDS is intended to provide a brief summary of our knowledge and guidance regarding the use of this material. The information contained here has been compiled from sources considered by Bridgewater LLC to be dependable and is accurate to the best of the Company's knowledge. It is not meant to be an all-inclusive document on worldwide hazard communication regulations.

This information is offered in good faith. Each user of this material needs to evaluate the conditions of use and design the appropriate protective mechanisms to prevent employee exposures, property damage or release to the environment. Bridgewater LLC assumes no responsibility for injury to the recipient of third persons, or for any damage to any property resulting from misuse of the product.

End of Material Safety Data Sheet