



Earththerapy™ - Conditioner

Safety Data Sheet

SDS No.: SHG2026021003
Issue Date: Feb. 10th, 2026
Revision Date: Feb. 10th, 2026
Version No.: 1.0

According to US HazCom 2012

Section 1 Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier:

Identification on the label/Trade Name: EARTHERAPY CONDITIONER

Additional identification: Not available

1.2 Relevant identified uses of the substance and uses advised against:

Relevant Identified uses: Hair Care

Uses advised against: Not Applicable

1.3 Details of the supplier of the safety data sheet:

Supplier: World Amenities, Inc.

Address: 8960 Carroll Way, Suite E, San Diego, CA 92121

Telephone: 1-858-880-SOAP

Fax: 858-428-3330

Email: sales@worldamenities.com

1.4 Emergency telephone Number:

Association/Organization: World Amenities, Inc.

Emergency Tel No.: 1-858-880-SOAP

Section 2 Hazards Identification

2.1 Classification of the substance/mixture:

Considered NOT a Hazardous mixture according to GHS US HazCom 2012.

Classified NOT as Dangerous Goods for transport purposes.

2.2 Label elements:

Hazard Pictograms: Not Applicable

Signal Words: Not Applicable

Hazard Statements: Not Applicable

Supplementary statement: Not Applicable

Precautionary statements Prevention: Not Applicable

Precautionary statements Response: Not Applicable

Precautionary statements Storage: Not Applicable

Precautionary statements Disposal: Not Applicable

2.3 Other hazards:

Not Applicable

Section 3 Composition/information on ingredients

3.1 Substance/Mixture:

See "Composition on ingredients" in Section 3.2

3.2 Mixtures of Ingredient(s):

INCI Name	CAS No.	%	Function
Aqua(Water)	7732-18-5	88.77147000	Solvent
Cetearyl Alcohol	67762-27-0	5.00	Emulsifying
Cetrimonium Chloride	112-02-7	2.50	Antistatic
Glycerin	56-81-5	1.00	Humectant
Glyceryl Stearate	31566-31-1	0.80	Skin Conditioning
Phenoxyethanol	122-99-6	0.60	Preservative
Caprylic/Capric Triglyceride	73398-61-5	0.50	Skin Conditioning
Ethylhexyl Palmitate	29806-73-3	0.50	Skin Conditioning
Fragrance	N/A	0.30	Perfuming
Methylchloroisothiazolinone	26172-55-4	0.00101250	Preservative
Methylisothiazolinone	2682-20-4	0.00033750	Preservative
Limonene	138-86-3	allergen	allergen-perfuming
Citrus Aurantium Peel Oil	68916-04-1	allergen	allergen-perfuming
Linalyl Acetate	115-95-7	allergen	allergen-perfuming
Terpineol	138-87-4	allergen	allergen-perfuming
FD&C Yellow No. 5	1934-21-0	0.011360	Colorant
FD&C Yellow No. 6	2783-94-0	0.015820	Colorant

Section 4 First aid measures**4.1 Description of first aid measures:**

Inhalation:	If fumes, aerosols or combustion products are inhaled, removed from contaminated area. Other measures are usually unnecessary.
Skin contact:	If skin or hair contact occurs, flush skin and hair with running water (and soap if available). Seek medical attention in event of irritation.
Eyes contact:	If this product comes in contact with eyes, wash out immediately with water. If irritation continues, seek medical attention. Removal of contact lenses after eye injury should only be undertaken by skilled personnel.
Ingestion:	Immediately give a glass of water. First aid is not generally required. If in doubt, contact a poisons information center or a doctor.

4.2 Most important symptoms and effects, both acute and delayed:

See Section 11

4.3 Indication of any immediate medical attention and special treatment needed:

Treat symptomatically

Section 5 Fire-Fighting measures**5.1 Extinguishing media:**

Foam
Dry chemical powder

5.2 Special hazards arising from the substance or mixture**5.3 Advice for fire-fighters:**

Product Name: EARTHERAPY CONDITIONER
Version #: 1.0

Revision date: 10-02-2026

MSDS US
2 / 7

Fire Incompatibility: None known.

Wear breathing apparatus plus protective gloves in the event of a fire.

Fire/Explosion Hazard: Noncombustible. Not considered a significant, however containers may burn.

Fire-fighting: Alert fire brigade and tell them location and nature of hazard.

Section 6 Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures:

See Section 8

6.2 Environmental Precautions:

See Section 12

6.3 Methods and material for Containment and Cleaning up:

Minor spills: Clean up all spills immediately. Avoid breathing vapors and contact with skin and eyes.

Major spills: Clear area of personnel and move upwind.

6.4 Reference to other sections:

Personal Protection Equipment advice is contained in Section 8 of the SDS.

6.5 Additional information:

Not applicable.

Section 7 Handling and storage

7.1 Precautions for safe handling:

7.11 Safe Handling:

Limit all unnecessary personal contact. Wear protective clothing when risk of exposure occurs.

7.12 Fire and explosion protection:

See Section 5.

7.13 Other information:

Store in original containers. Keep the containers sealed.

7.2 Conditions for safe storage, including any incompatibilities

7.21 Suitable container:

Tube, bottle or sachet

7.22 Storage Incompatibility:

None known

7.3 Specific end uses

See Section 1.2

Section 8 Exposure Controls/Personal Protection

8.1 Control parameters:

DERIVED NO EFFECT LEVEL(DNEL):
PREDICTED NO EFFECT LEVEL(PNEC):
OCCUPATIONAL EXPOSURE LIMITS(OEL):
INGREDIENT DATA

Not Available
Not Available

Source	Ingredient	Material Name	TWA	STEL	PEAK	NOTES
UK Workplace Exposure Limits (WELs)	Glycerin	Glycerol, mist	10 mg/m ³	Not Available	Not Available	Not Available

8.2 Exposure controls:

8.2.1 Appropriate engineering controls:

Engineering controls are used to remove a hazard or place a barrier between the worker and the hazard. Well-designed engineering controls can be highly effective in protecting workers and will typically be independent of worker interactions to provide this level of protection.

8.2.2 Individual protection measures, such as personal protective equipment:



Eye/face protection:

Safety glasses with side shields; chemical goggles.

Hands/feet protection:

Wear chemical protective gloves, e.g. PVC. Wear safety footwear or safety gumboots, e.g. Rubber.

NOTE: The material may product skin sensitization in predisposed individuals. Care must be taken, when removing gloves and protective equipment, to avoid all possible skin contact.

Body protection:

See other protection below

Other protection:

Overalls. P.V.C.

8.2.3 Environmental exposure controls:

See Section 12.

Section 9 Physical and chemical properties

9.1 Information on basic physical and chemical properties:

Appearance:	Cream
Physical state:	Cream
Odor:	Pleasant smell
Odor threshold:	Not available
PH(20°C):	4.0 – 6.0
Melting point/range (°C):	Not available
Freezing point/range (°C):	Not available
Boiling point/range (°C):	Not available
Flash point (°C):	Not applicable
Evaporation rate:	Not available
Flammability:	Not flammable
Upper/lower/explosive limits:	Not available
Vapor pressure (kPa):	Not available
Vapor density (Air=1):	Not available
Water solubility (g/l):	Not available
Relative Density (Water=1):	Not available
Partition coefficient n-octanol/water:	Not available
Auto-ignition temperature:	Not available
Decomposition temperature:	Not available
Viscosity (mPa.s):	8000 - 30000
Explosive properties:	Not available
Molecular Weight(g/mol):	Not available
Taste:	Not applicable
Explosive properties:	Not available
Oxidizing properties:	Not available
Surface Tension(Dyn/cm or mN/m):	Not available
Volatile Component(% vol):	Not available
Gas group:	Not available
PH as a solution(1%):	Not available
VOC g/L:	Not applicable

9.2. Other information:

Not available

Section 10 Stability and reactivity

10.1 Reactivity:	Product is non-reactive under normal conditions of use, storage and transport.
10.2 Chemical stability:	Product is considered stable and hazardous polymerization will not occur.
10.3 Possibility of hazardous reactions:	No dangerous reactions known under normal conditions of use.
10.4 Conditions to avoid:	None
10.5 Incompatible materials:	No additional information available.
10.6 Hazardous decomposition products:	See section 5.3

Section 11 Toxicological information

11.1 Information on toxicological effects

Acute toxicity:

Cetearyl Alcohol (CAS No.: 67762-27-0):

Dermal (rabbit) LD50:	> 10000 mg/kg ^[1]
Oral (rabbit) LD50:	> 10000 mg/kg ^[1]

Cetrimonium Chloride (CAS No.: 112-02-7):

Oral (rat) LD50:	1300 mg/kg** ^[2]
------------------	-----------------------------

Glycerin (CAS No.: 56-81-5):

Oral (guinea pig) LD50:	7750 mg/kg ^[2]
Oral (mouse) LD50:	4940 mg/kg ^[2]
Oral (rat) LD50:	12600 mg/kg ^[2]

Glyceryl Stearate (CAS No.: 31566-31-1):

Dermal (rat) LD50:	> 2000 mg/kg ^[1]
Oral (mouse) LD50:	> 5000 mg/kg ^[1]

Phenoxyethanol (CAS No.: 122-99-6)

Dermal (rat) LD50:	2300-3800 mg/kg ^[1]
Oral (rat) LD50:	1260 mg/kg ^[1]

Caprylic/Capric Triglyceride (CAS No.: 73398-61-5)

Oral (rat) LD50:	> 5000 mg/kg ^[2]
------------------	-----------------------------

Ethylhexyl Palmitate (CAS No.: 29806-73-3)

Dermal (rat) LD50:	> 2000 mg/kg ^[2]
Oral (rat) LD50:	> 5000 mg/kg ^[2]

Methylchloroisothiazolinone&Methylisothiazolinone(CAS No. 26172-55-4& 2682-20-4)

Oral (rat) LD50:	4467 mg/kg ^[2]
Dermal (rabbit) LD50:	> 5000 mg/kg ^[2]

FD&C Yellow No. 6 (CAS No.: 2783-94-0)

Oral (rat) LD50:	> 2000 mg/kg ^[1]
------------------	-----------------------------

FD&C Yellow No. 5 (CAS No.: 1934-21-0)

Oral (rat) LD50:	> 2000 mg/kg ^[2]
------------------	-----------------------------

Skin corrosion/Irritation:

Causes skin irritation.

Serious eye damage/irritation:

Causes serious eye damage.

Respiratory or skin sensitization:

May cause an allergic skin reaction.

Germ cell mutagenicity:

No data available.

Carcinogenicity:

No data available

Reproductive toxicity:

No data available.

STOT- single exposure:

No data available.

STOT-repeated exposure:

No data available.

Aspiration hazard:

No data available.

Legend:

1. Value obtained from Europe ECHA and US CIR – Acute toxicity.
2. Value obtained from the SDS from raw material suppliers. Unless otherwise specified data extracted from RTECS – Register of Toxic Effect of chemical Substance.

Section 12 Ecological information

12.1 Toxicity:

Conditioner:

No data available for the mixture.

12.2 Persistence and degradability:

Ingredient	Persistence: Water/Soil	Persistence: Air	Biodegradation: Water/Soil
Cetearyl Alcohol	Low	Low	Readily biodegradable (100%) in Water
Cetrimonium Chloride	Low	Low	Readily biodegradable (100%) in Water Half-life in soil: 17.1 days @ 12 °C
Glycerin	Low	Low	Readily biodegradable (100%) in Water
Caprylic/Capric Triglyceride	Low	Low	Readily biodegradable in Water
Ethylhexyl Palmitate	Low	Low	Readily biodegradable (80.8%) in Water, 28d
Glyceryl Stearate	Low	Low	Readily biodegradable (100%) in Water

12.3 Bio-accumulative potential

Ingredient	Bioaccumulation
Cetearyl Alcohol	HIGH (LogKOW)= 6.7342)
Glycerin	LOW (LogKOW)= - 1.76)
Caprylic/Capric Triglyceride	LogPow> 5
Glyceryl Stearate	HIGH (LogKOW)= 6.6162)

12.4 Mobility in soil

Ingredient	Bioaccumulation
Cetearyl Alcohol	LOW (KOC=3786)
Glycerin	HIGH (KOC=1)
Glyceryl Stearate	LOW (KOC=486.6)

12.5 Results of PBT and vPvB assessment

	P	B	T
Relevant available data	Not Applicable	Not Applicable	Not Applicable
PBT Criteria fulfilled	Not Applicable	Not Applicable	Not Applicable

12.6 Other adverse effects

No data available

Section 13 Disposal considerations

13.1 Waste treatment methods:

Dispose of contents/container in accordance with licensed collector's sorting instructions.

Section 14 Transport information

In accordance with DOT/IMDG/IATA

DOT	IMDG	IATA
14.1 UN No.		
Not Regulated	Not Regulated	Not Regulated
14.2 Proper Ship Name		
Not Applicable	Not Applicable	Not Applicable
14.3 Transport Hazard Class(es)		
Not Applicable	Not Applicable	Not Applicable
14.4 Packing Group		
Not Applicable	Not Applicable	Not Applicable
14.5 Environmental Hazards		
Not Applicable	Not Applicable	Not Applicable
No supplementary information available		

14.6 Special precautions for users

Not regulated for DOT/IMDG/IATA

14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not Applicable

The product is not classified as dangerous and is safe for all the means of transportation based on the Certification for Safe Transport of Chemical Goods by Shanghai Institute of Chemical Industry Testing Co., Ltd.

Section 15 Regulation information

15.1 US Federal regulations

All components of this product are present and listed as Active on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory.

This product or mixture is not known to contain a toxic chemical or chemicals in excess of the applicable de minimis concentration as specified in 40CFR S372.38/a) subject to the reporting requirements of section 313 of Title II of the Superfund Amendments and Reauthorization Act of 1986 and 4CFR Part 372.

15.2 US State regulations

California Proposition 65 - This product does not contain any substances known to the state of California to cause cancer, developmental and/or reproductive harm.

Section 16 Other information

The health and safety information contained in this MSDS is believed to be true and correct. However, because Jiangsu SOHO International Group Yangzhou Co., Ltd. has no control over the method of use of this product, all statements or suggestions are made without warranty, expressed or implied, regarding the reliability of the information, or the hazards resulting from the use of the material. Every user should consider the information given in this MSDS in the context of how this product will be used in the user's workplace, including the effects of other products on the premises.