# 5” Diameter Stock Motors

## Refrigeration – Unit Heaters – Space Heaters, GE 21/29 Frame Replacements – Mechanically Reversible


9666



604

### Features:

- Air Conditioners
- Base Mounting Available
- Commercial Condenser Units
- Continuous Duty, Air Over
- Designed for Easy Mechanical Reversing
- Drain Holes
- Extra Long 30” Leads
- Fits G.E. Base
- Mounting Rings Included
- Lead Exit on Shaft End
- For 1/2” Shaft Applications use Stock No 1306 Shaft Bushing
- Holes Provided for Conduit Connector
- Refrigeration Cabinets
- Replaces Most G.E. 21/29 Frame Motors
- Replaces Universal Stock 401-406
- Shaded Pole
- Sleeve Bearing
- Thermally Protected
- Unit Cooler Fans & Blowers
- Unit Heaters
- 2-1/4” Mounting Rings Included
- 4 Tapped 10-32 Holes for Shaft End Mounting
- 60 Hz



**STOCK N0. 2087A**
**MOUNTING STUDS**
10-32 X 1”
4 per set
(available separately)




| HP | RPM | Speeds | Volts | Amps | Stock Number | Shaft Dia. & Length | Rotation | “A” Dim. | Cross Reference | Base Number | Notes |
|---|---|---|---|---|---|---|---|---|---|---|---|
| **1/20** | 1050 | 1 | 115/230 | 2.8/1.4 | **604** | 3/8 x 3-1/4 | CWSE | 4-1/4 | 2321 & 2322 | 1207 | 103 |
| **1/20** | 1550 | 1 | 115/230 | 2.4/1.2 | **610** | 3/8 x 3-1/4 | CWSE | 4-1/4 | 2341 & 2342 | 1207 | 103 |
| **1/20** | 1550 | 1 | 115/230 | 2.4/1.2 | **611** | 3/8 x 3-1/4 | CCWSE | 4-1/4 | 2331 & 2332 | 1207 | 103 |
| **1/15** | 1050 | 1 | 115/230 | 3.8/1.9 | **606** | 3/8 x 3-1/4 | CWSE | 4-1/2 | 2223 | | 103 |
| **1/15** | 1550 | 1 | 115/208-230 | 2.8/1.4 | **612A** | 3/8 x 3-1/4 | CWSE | 4-1/2 | 2241 & 2242 | | 103 |
| **1/15** | 1550 | 1 | 115/208-230 | 2.8/1.4 | **613A** | 3/8 x 3-1/4 | CCWSE | 4-1/2 | 2231 & 2232 | | 103 |
| **1/12** | 1050 | 1 | 115 | 1.8 | **9667** | 3/8 x 2 | Rev. | 5-3/4 | 2928 | | 6,70,118 |
| **1/12** | 1050 | 1 | 208-230 | 0.61 | **9669** | 3/8 x 2 | Rev. | 5-3/4 | 2954 | | 6,70,118 |
| **1/12** | 1550 | 1 | 115 | 1.6 | **9666** | 3/8 x 2 | Rev. | 5-3/4 | 2927 | | 6,70,118 |
| **1/12** | 1550 | 1 | 208-230 | 0.65 | **9668** | 3/8 x 2 | Rev. | 5-3/4 | 2953 | | 6,70,118 |
| **1/10** | 1050 | 1 | 115/230 | 4.6/2.3 | **608** | 3/8 x 3-1/4 | CWSE | 4-3/4 | 2121 & 2122 | 2089 | 103 |
| **1/10** | 1050 | 1 | 115/230 | 4.6/2.3 | **609** | 3/8 x 3-1/4 | CCWSE | 4-3/4 | 2113 | 2089 | 103 |
| **1/10** | 1550 | 1 | 115/230 | 4.4/2.2 | **614** | 3/8 x 3-1/4 | CWSE | 4-3/4 | 2141 & 2142 | 2089 | 103 |
| **1/10** | 1550 | 1 | 115/230 | 4.4/2.2 | **615** | 3/8 x 3-1/4 | CCWSE | 4-3/4 | 2131 & 2132 | 2089 | 103 |


Used on many popular commercial condensing units (Copeland, Tecumseh, Hussmann, Tyler, etc.) as well as unit cooler fans and blowers, refrigeration cabinets; also used on unit heaters, space heaters, remote air conditioners, blower units and other air moving applications. 4 ratings replace 21 of G.E.’s 21/29 frame designs.


RF4400

### Features:

- All angle sleeve bearings
- Auto protector
- Base and mounting clamps included
- Grommeted lead exit
- Mounting rings included
- Mechanically reversible in the field
- Open enclosure
- Shaded pole
- UL and C.S.A. approved
- Lead exit on shaft end
- 3/8” shaft diameter,1/2” adapter
- 2-1/4” rubber rings; base mounting
- 30” color coded leads
- 42 Frame (5.0” Dia.)
- 60 HZ

| HP | RPM | Voltage | Amps | Frame | Stock Number | Rotation | Notes |
|---|---|---|---|---|---|---|---|
| **1/10** | 1050 | 115/208-230 | 4.0/2.0 | 42Y | **RF6402** | CWSE | 6,154 |
| **1/10** | 1050 | 115/208-230 | 4.0/2.0 | 42Y | **RF6403** | CCWSE | 6,154 |
| **1/10** | 1550 | 115/208-230 | 4.0/2.0 | 42Y | **RF4400** | CWSE | 6,154 |
| **1/10** | 1550 | 115/208-230 | 4.0/2.0 | 42Y | **RF4401** | CCWSE | 6,154 |




4 mounting bolts 3-1/2 dia. B.C.
*(Mounting Washers and Nuts Included)*

**Notes:**

6. 60/50 HZ
70. Permanent Split Capacitor
103. When using U.E. Base, add (2) 1221A Adapter Rings to EACH Mounting Ring
118. TEAO
154. Previous stock numbers with “X” suffix are as current models

Also see page 35 for G.E. 11 Frame Replacements