ABB BALDOR RELIANCE

Customer information packet

EL11203M

.25HP, 1725RPM, 1PH, 60HZ, 48, 3411LC, OPEN, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 2:24:44 PM

Specifications

Enclosure	OPEN
Frame	48
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	.250 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	115.0 V @ 60 HZ
Agency Approvals	CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.600 A @ 115.0 V
	1.900 A @ 208.0 V
	1.300 A @ 230.0 V
Design Code	-
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	68.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.3 a

Part Detail

Revision	N
Type	AC
Mech. spec.	34F351
Base	
Status	PRD/A
Elec. spec.	34WGR218
Layout	34LYF351
Eff. date	12-31-2024
CD Diagram	CD0320
Poles	04
Leads	7#18
Proprietary	False
Created date	10-03-2014

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	7 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3411LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	9.76 IN
Power Factor	89
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.35
Shaft Diameter	0.500 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Manual Thermal Overload
Winding Thermal 1 Location	SB

Winding Thermal 2	None

Nameplate

NP3273L								
CAT.NO.	EL11203M							
SPEC.	34F351R218G1							
HP	.25							
VOLTS	115/230							
AMP	2.6/1.3							
RPM	1725							
FRAME	48	**HZ**	60		**PH**	1		
SER.F.	1.35	**CODE**	L	**DES**	-	**CL**	F	
F.L. AVG. EFF.	68.5	**PF**	89					
RATING	40C AMB-CONT							
CC								
DE	6203	**ODE**	6203					
ENCL	OPEN	**SN**						
	SFA 3.4/1.7							

AC Induction Motor Performance Data
Record # 62090
Typical performance - not guaranteed values

Winding: 34WGR218-R002	**Type:** 3411LC	**Enclosure:** OPEN

Nameplate Data				**115 V, 60 Hz: Low Voltage Connection**	
Rated Output (HP)			.25	**Full Load Torque**	0.754 LB-FT
Volts			115/230	**Start Configuration**	direct on line
Full Load Amps			2.6/1.3	**Breakdown Torque**	1.86 LB-FT
R.P.M.			1725	**Pull-up Torque**	1.57 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	2.48 LB-FT
NEMA Design Code	-	**KVA Code**	L	**Starting Current**	20.3 A
Service Factor (S.F.)			1.35	**No-load Current**	1.53 A
NEMA Nom. Eff.	68.5	**Power Factor**	89	**Line-line Res. @ 25ºC**	3.4881 Ω A Ph 6.3165 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	27°C
S.F. Amps			3.4/1.7	**Temp. Rise @ S.F. Load**	34°C

Load Characteristics 115 V, 60 Hz, 0.25 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	67	79	85	90	92	94	93
Efficiency	37.2	55.5	65.1	69.7	71.4	71.1	71.3
Speed	1783.6	1770.8	1755.8	1739.1	1717.7	1691.5	1707
Line amperes	1.63	1.85	2.18	2.59	3.1	3.69	3.34


ABB Motors and Mechanical Inc.


WINDING # 34WGR218

0.25 HP 1 PH 60 HZ 1725 RPM 115 V 3411LC


Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=1.86 PU=1.57 LR=2.48 LRA=20.3




34LYF351
408-421 = 9.76
422-428 = 10.63
429-432 = 11.13
1.75
1.50
1.12
FLAT
NAMEPLATE
.453
.433
Ø .5000
.4995
1.82
.63
4 SLOTS
.34 WIDE
2.75
2.50
4.00
Ø5.68
5.07
4.03
2.28
5.80
3.00
2.94
THERMAL
(WHEN
REQ'D)
LEAD HOLE
Ø .88
2.13
2.13
3.54
2.88
5.75
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CLEAN UP DIMENSIONING
REV: E
VERSION: 04
REVISED: 10:32:08 10/02/2025
TDR: 000001264465
MODEL NO. 34LYF351
REF: -
BY: ENJEFD0
B
BALDOR - RELIANCE®
STD HOR 34LC NEMA 48 OPEN
34LYF351

CD0320



	LINE A	LINE B	JOIN	JOIN
HIGH STD	1,8	4	2,3,5	J
HIGH OPP	1,5	4	2,3,8	J
LOW STD	1,3,8	4	–	2,J,5
LOW OPP	1,3,5	4	–	2,J,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0320

REV. DESC: ADD INTERNAL CONNECTION TO HELP MANUFACTURING		
REV. LTR: G	VERSION: 01	TDR: 000000941594
FILE: \AAA\00007\422	REVISED: 02:21:00 08/28/2015	BY: ENALEMO
MTL: –		

BALDOR

TYPE LC, DV, REV, THERMAL, B PH AMPS THRU HTR HVC, 7 LEAD

SH 1 of 1