



Revision Number: 007.0

Issue date: 11/07/2022

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE AA H3300 B known as SPEEDBONDER H3300 50 ML PART B	IDH number:	702108
Product type/use:	Acrylics	Item number:	83020_AB0330
Restriction of Use:	None identified	Region:	United States
Company address:	Contact information:		
Henkel Corporation	Telephone: +1 (860) 571-5100		
One Henkel Way	MEDICAL EMERGENCY Phone: Poison Control Center		
Rocky Hill, Connecticut 06067	1-877-671-4608 (toll free) or 1-303-592-1711		
	TRANSPORT EMERGENCY Phone: CHEMTREC		
	1-800-424-9300 (toll free) or 1-703-527-3887		
	Internet: www.henkelna.com		

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW	
DANGER:	HIGHLY FLAMMABLE LIQUID AND VAPOUR. CAUSES SKIN IRRITATION. MAY CAUSE AN ALLERGIC SKIN REACTION. MAY CAUSE RESPIRATORY IRRITATION. SUSPECTED OF DAMAGING FERTILITY OR THE UNBORN CHILD.

HAZARD CLASS	HAZARD CATEGORY
FLAMMABLE LIQUID	2
SKIN IRRITATION	2
SKIN SENSITIZATION	1
REPRODUCTIVE TOXICITY	2
SPECIFIC TARGET ORGAN TOXICITY - SINGLE EXPOSURE	3

PICTOGRAM(S)

Precautionary Statements

Prevention:	Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Keep away from heat, sparks, open flames, hot surfaces - no smoking. Keep container tightly closed. No release into water. Use explosion-proof equipment. Use non-sparking tools. Take action to prevent static discharges. Avoid breathing vapors, mist, or spray. Wash affected area thoroughly after handling. Use only outdoors or in a well-ventilated area. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves, clothing, eye and face protection.
Response:	If on skin (or hair): Take off immediately all contaminated clothing. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or physician if you feel unwell. IF exposed or concerned: Get medical attention. If skin irritation or rash occurs: Get medical attention. Take off contaminated clothing. In case of fire: Use foam, dry chemical or carbon dioxide to extinguish.
Storage:	Store in a well-ventilated place. Keep container tightly closed. Store in a well-ventilated place. Keep cool. Store locked up.
Disposal:	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Methyl methacrylate	80-62-6	30 - 60
Aldehyde-amine condensate	34562-31-7	1 - 5
Toluene	108-88-3	0.1 - 1

* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. If symptoms develop and persist, get medical attention.
Skin contact:	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. If symptoms develop and persist, get medical attention. Wash clothing before reuse. Thoroughly clean shoes before reuse.
Eye contact:	Immediately flush eyes with plenty of water for at least 15 minutes. If symptoms develop and persist, get medical attention.
Ingestion:	DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.
Unusual fire or explosion hazards:	Vapors may accumulate in low or confined areas, travel considerable distance to source of ignition, and flash back. Closed containers may rupture (due to build up of pressure) when exposed to extreme heat.
Hazardous combustion products:	Oxides of carbon. Oxides of nitrogen. Acrylic monomers. Toxic fumes. Irritating vapors.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Remove all sources of ignition. Ensure adequate ventilation. Wear appropriate personal protective equipment. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Scrape up spilled material and place in a closed container for disposal.

7. HANDLING AND STORAGE

Handling:	Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Keep container closed. During use and until all vapors are gone: Keep area ventilated - do not smoke; extinguish all flames, pilot lights, and heaters; turn off stoves, electrical tools and appliances, and any other sources of ignition. Make sure containers are properly grounded before use or transfer of material.
Storage:	For safe storage, store at or below 32 °C (89.6 °F) Keep container tightly closed and in a cool, well-ventilated place away from incompatible materials. Keep away from heat, spark and flame. Keep out of direct sunlight. Maintain head space in storage containers to support oxygen requirements of the inhibitor(s).

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Methyl methacrylate	50 ppm TWA 100 ppm STEL (Dermal sensitization)	100 ppm (410 mg/m ³) PEL	None	50 ppm
Aldehyde-amine condensate	None	None	None	None
Toluene	20 ppm TWA	200 ppm TWA 300 ppm Ceiling 500 ppm MAX. CONC 10 minutes	None	None

Engineering controls:	Use local ventilation if general ventilation is insufficient to maintain vapor concentration below established exposure limits.
Respiratory protection:	Use NIOSH approved respirator if there is potential to exceed exposure limit(s).
Eye/face protection:	Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists.
Skin protection:	Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Liquid, Paste
Color:	Tan, Yellow
Odor:	Sharp
Odor threshold:	Not available.
pH:	Not applicable, Product is non-polar/aprotic.
Vapor pressure:	Not available.
Boiling point/range:	> 212 °F (> 100°C)
Melting point/ range:	Not available.
Specific gravity:	1.03
Vapor density:	> 1
Flash point:	14 °C (57.2 °F) Setflash Closed Cup
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Flammability:	Not applicable
Evaporation rate:	Faster than ether.
Solubility in water:	low solubility
Partition coefficient (n-octanol/water):	Not available.
VOC content:	0.98 %; 9.8 g/l (Adhesive and Activator mixed)
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	Polymerization may occur at elevated temperatures or upon depletion of inhibitor.
Hazardous decomposition products:	Oxides of carbon. Oxides of nitrogen. Acrylic monomers. Toxic fumes. Irritating vapors.
Incompatible materials:	Oxidizing agents. Reducing agents.
Reactivity:	Not available.
Conditions to avoid:	Keep away from heat, ignition sources and incompatible materials. Do not mix in batches greater than 100 grams (0.22 pounds) unless you plan to use immediately. Protect from direct sunlight. Loss of polymerization inhibitor. Loss of dissolved air.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects/Symptoms

Inhalation:	May cause respiratory tract irritation. Drowsiness. Dizziness.
Skin contact:	Causes skin irritation. May cause allergic skin reaction.
Eye contact:	May cause eye irritation.
Ingestion:	May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Methyl methacrylate	Oral LD50 (Rat) = 7,800 mg/kg Oral LD50 (Rabbit) = 6,000 mg/kg Oral LD50 (Rat) = 9,400 mg/kg	Allergen, Irritant, Kidney, Liver, Mutagen, Nervous System, Respiratory
Aldehyde-amine condensate	None	No Records
Toluene	Oral LD50 (Rat) = 2.6 g/kg Dermal LD50 (Rabbit) = 12,124 mg/kg Inhalation LC50 (Rat, 4 h) = 12.5 - 28.8 mg/l Inhalation LC50 (Rat, 4 h) = 25.7 mg/l Inhalation LC50 (Rat, 4 h) = 28.1 mg/l Inhalation LC50 (Rat, 4 h) = 30 mg/l	Behavioral, Cardiac, Central nervous system, Developmental, Ear, Irritant

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Methyl methacrylate	No	No	No
Aldehyde-amine condensate	No	No	No
Toluene	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Dispose of according to Federal, State and local governmental regulations.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Adhesives
Hazard class or division: 3
Identification number: UN 1133
Packing group: II
DOT Hazardous Substance(s): Methyl methacrylate

International Air Transportation (ICAO/IATA)

Proper shipping name: Adhesives
Hazard class or division: 3
Identification number: UN 1133
Packing group: II

Water Transportation (IMO/IMDG)

Proper shipping name: ADHESIVES (Diethyl-phenyl-propyl-dihydropyridine~)
Hazard class or division: 3
Identification number: UN 1133
Packing group: II
Marine pollutant: Diethyl-phenyl-propyl-dihydropyridine~

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed as active or are exempt from listing on the Toxic Substances Control Act (TSCA) inventory.

TSCA 12 (b) Export Notification: None above reporting de minimis

CERCLA/SARA Section 302 EHS: None above reporting de minimis.
CERCLA/SARA Section 311/312: Fire, Immediate Health, Delayed Health
CERCLA/SARA Section 313: This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Methyl methacrylate (CAS# 80-62-6).
CERCLA Reportable quantity: Methyl methacrylate (CAS# 80-62-6) 1,000 lbs. (454 kg)

California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDSL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: 9, 11, 13, 14, 15

Prepared by: Product Safety and Regulatory Affairs

Issue date: 11/07/2022

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.

This Safety Data Sheet has been generated based on OSHA Hazard Communication Standard (29 CFR 1910.1200) and provides information in accordance with U.S. federal law only. No warranty or representation of any kind is given with respect to the substantive or export laws of any other jurisdiction or country. Please confirm that the information provided herein conforms to the substantive export or other law of any other jurisdiction prior to export. Please contact Henkel Product Safety and Regulatory Affairs for additional assistance.