

## Marine 4T Motor Oil SAE 25W-40

### Description

High performance motor oil formulated with specific synthetic marine additives. Provides a stable lubricating film and best wear protection in the most extreme conditions. Maintains engine rubber seals for lowest possible oil consumption.

### Properties

- ideal with catalytic converters
- outstanding corrosion protection
- outstanding oil film strength
- stable to aging and stable viscosity
- optimum oil pressure under all operating conditions

### Specifications / Approvals

API SM • NMMA FC-W Catalyst Compatible®

**LIQUI MOLY recommends this product for vehicles or assemblies for which the following specifications or original spare part numbers are required:**

Honda Marine • Mercury Marine • NMMA FC-W • Selva • Suzuki Marine • Tohatsu • Volvo Penta • Yamaha

### Technical data

|                          |                                            |
|--------------------------|--------------------------------------------|
| SAE class (engine oils)  | 25W-40<br>SAE J300                         |
| Density at 59 °F         | 0,875 g/cm <sup>3</sup><br>DIN 51757       |
| Viscosity at 104 °F      | 120,0 mm <sup>2</sup> /s<br>ASTM D 7042-04 |
| Viscosity at 212°F       | 13,5 mm <sup>2</sup> /s<br>ASTM D 7042-04  |
| Viscosity at 14 °F (CCS) | <= 13000 mPas<br>ASTM D 5293               |
| Viscosity index          | 110<br>DIN ISO 2909                        |
| HTHS at 302 °F           | >= 3,7 mPas<br>ASTM D 5481                 |
| Pour point               | -16 °F<br>DIN ISO 3016                     |
| Evaporation loss (Noack) | 6 %<br>CEC-L-40-A-93                       |
| Flash point              | 446 °F<br>DIN ISO 2592                     |
| Total base number        | 7,0 mg KOH/g<br>DIN ISO 3771               |
| Sulfate ash              | 0,8 g/100g<br>DIN 51575                    |



### Technical data

Color number (ASTM) L 2,0  
DIN ISO 2049

### Areas of application

For 4-stroke gasoline engines, where an oil according to current product specifications is required or recommended. Safe with catalytic converters and turbochargers.

### Application

Observe the manufacturers instructions!

### Available pack sizes

|                          |                            |
|--------------------------|----------------------------|
| 1 l Canister plastic     | 20546<br>CAEN-CAFR-USEN    |
| 4 l Canister plastic     | 20548<br>CAEN-CAFR-USEN    |
| 20 l Canister plastic    | 20499<br>CAEN-CAFR-USEN    |
| 60 l Black plate barrel  | 25029<br>DE-EN-ES-FR-IT-PT |
| 205 l Black plate barrel | 25057<br>DE-EN-ES-FR-IT-PT |

**Our information is based on thorough research and may be considered reliable, although not legally binding.**