

User Manual

Instruction manual



Dander Capture




Pet & Children Friendly



Air Quality Light



Eco, Sleep & Turbo



Enjoy it.

Enjoy it.

Manufacture: Guangdong MAK Electrical Technology Co., Ltd.
ADD: Dongfu Garden, No.8 Shangyi Road, Nantou, Zhongshan City, Guangdong
Email: terhomelife@outlook.com

FC **ETL**
C LISTED US
Intertek
5030376
MADE IN CHINA

Air Purifier for Pets
MK-AP02

DIRECTORY

IMPORTANT SAFEGUARDS	01-03
ATTENTION	04-05
PRODUCT APPEARANCE DIAGRAM	06-07
USE AND OPERATION	08-10
INSTRUCTIONS FOR USE	11-14
CLEANING AND CARE/FAQ	15

IMPORTANT SAFEGUARDS

In order to prevent harm or damage happened to users or others, be sure to comply with the requirement as below:

WARNING/ATTENTION



WARNING

It reminds that misusing or mishandling may cause death.



ATTENTION

It reminds that misusing or mishandling may cause hurt.



FORBID




FORCE

Unplug or disconnect the appliance from the power supply before servicing.
WARNING: To Reduce The Risk Of Fire Or Electric Shock, Do Not Use This Fan With Any Solid-State Speed Control Device.

WARNING: To Reduce The Risk Of Fire, Electric Shock Or Injury To Persons, Do Not Use Replacement Parts That Have Not Been Recommended By The Manufacturer (e.g. Parts Made At Home Using A 3D Printer)

IMPORTANT SAFEGUARDS

WARNING



Please supervise your children and avoid them from touching or using machine.



AVOID WET

Do not connect or disconnect the power with wet hand.
It may cause electrical shocking.



NO DISASSEMBLE

Do not disassemble, repair or reconstruct.
It may cause fire or damage.
Please contact the seller for replacement.



FORBID

Do not use over-limit sockets or wiring connectors. Please use the rated voltage.
It may cause a fire.



Do plug the power into the socket completely.
It may cause fire because of heating or electrical shocking.
Do not use the damaged plug or loose socket.

IMPORTANT SAFEGUARDS




AVOID WET

Avoid any water on the surface of the unit.
It may cause short circuit or electrical shocking.



DISCONNECT POWER

The appliance must be disconnected from the supply mains before cleaning or other maintenance.
Otherwise the unit may start working in a sudden which may cause electrical shocking or hurt.



Do not insert any metal objects into the unit.
It may cause hurt or electric shocking.




FORBID

Do not repair it when the cord or plug is damaged.
It may cause short circuit, electric shocking or fire. Please contact the retailer for replacement.



If there is dust on the plug, it may weaken the insulation and even cause a fire.
Take out the plug and clean it with dry cloth.
Please remove the plug from the socket if not using for a long period.


! ATTENTION




Do not use in the room with a gas stove.
It may cause hurt because the machine is not a ventilator.




Do not place the unit near fires.
It may cause fire.




Do not use in the watery or high temperature room such as the bathroom etc.
Otherwise it may cause creepage, electric shocking or fire.



Please hold the plug instead of the cord when unplug the power.
Otherwise it may cause short circuit, breaking of the cord, electric shocking or fire.



Keep away from alcohol, organic impregnant.
It may cause cracking, short circuit, electric shock, injury or fire.



Please ventilate timely when used with fire in the room.


Please remove the plug from the socket if any conditions as below:

- If all switches do not work
- If the power cord or plug hot singularly
- If any peculiar smell, exceptional noise or vibration
- Any other abnormality or failure

If the power cord is damaged, please send it to the retailer or service center or technician for repairing. Do not change or repair it by yourself.

The multi-functional filter is composed of pre-filter, HEPA layer and activated carbon layer.

DIAGRAM OF PURIFICATION



DECOMPOSITION DIAGRAM





DIAGRAM OF CONTROL PANEL



PLACEMENT

- ◆ Make sure the appliance is placed at least 30cm away from any wall or piece of furniture. Do not position the appliance directly under furniture or objects that may obstruct the exhaust air flow.
- ◆ Do not use the appliance near any source of heat.

REPLACE THE FILTER

- ◆ Replace the filter and reset.

The filter replacement indicator will light up when cumulative running time reaches 2160hrs. Please replace the filter with a new one. Then, press and hold the reset button for approximately 3 seconds to reset the filter's lifetime counter, and the filter replacement indicator will turn off.

REMOVE THE FILTER


1. Switch the appliance off and unplug it.
2. Remove the inlet grille.
3. Grab the top rope of the filter and pull it out.
4. Take out the filter and close the inlet grille.

PARAMETERS OF THE UNIT

Model	MK-AP02
CADR	230m ³ /h
Usage Area	30m ²
Size	411x315x166mm.
Rated Input	DC 24V 2A
Rated Power	35W


INSTALL THE FILTER

1. Please remove the new filter protective film before installation.
2. Please fasten the inlet grille correctly until the filter is firmly installed.



EXTERNAL POWER SOURCE


Suitable Voltage: 24V




24V DC power adapter inlet




Power adapter





Press the lid to open the aromatherapy box.

Add the appropriate amount of aroma essence to the sponge tablet.



Press and close the lid, finish!
Enjoy the aroma in the Air.

POWER SETTING

- ♦ All the indicator lights will be on for 3 second for self-checking after connecting power, then enter standby mode. The pictures below are for reference.
- ♦ To turn on or switch off the appliance, press the power button while in standby mode.

FAN SPEED SETTING


Press the fan speed button to select the fan speed: Auto, low, medium, high




When in Auto mode, the machine will automatically regulate the purify power speed according to the real-time air quality index.

TIMER SETTING


- ◆ Press the timer button to set the working time.



- ◆ Use the control lock to temporarily lock the control panel and deactivate the function buttons. To turn on or deactivate the child lock, press and hold the child button on the top control panel for approx. 3 seconds. Child lock indicator light on the display will light up or be switched off accordingly.




- ◆ The filter replacement indicator will light up when the cumulative running time reaches 4800 hours. Please replace the filter with a new one. Then, press and hold the reset button for approximately 3 seconds to reset the filter's lifetime counter, and the filter replacement indicator will turn off.




SLEEPING MODE

- ◆ To turn on or deactivate sleep mode by pressing sleep button. Sleep mode sets the appliance to the lowest speed setting with fan speed indicator light switched off and Sleep mode indicator half lit.




ECO MODE

- ◆ To turn on or deactivate eco mode by pressing mode button. In eco mode, the highest working function of the machine will be limited to 2nd speed.



USE AMBIENT LIGHT FUNCTION


- ◆ Press Indicator light button to turn on or switch off the Indicator light



Switch off /Turn on Indicator light

TURBO&PET BUTTON

- ◆ Pet mode: Press this button once to set the wind speed to the maximum rapid speed.



Turn on Auto mode

Note: Auto's specific working gears should be made to correspond to the change of PM2.5 values.

Three colors, corresponding to three gears.


Air Quality Indicator light	AQI
Green	0~75
Yellow	76~150
Red	151~999

MAINTENANCE AND CLEANING METHODS



Please remove plug from the socket before cleaning and maintenance .

- ◆ Cleaning the body for this device by damp cloth, then wipe it dry.
- ◆ If the machine is too dirty, neutral detergent can be used for cleaning, but please dilute the detergent before use.
- ◆ Do not clean the unit with the solvent listed on the right which may cause distortion or discolour.



If the machine can't work properly, please kindly check as below before you send it out for repair

Problem	Checking methods	Possible solution
Do not work	• Please check if the plug is disconnected from the socket.	➡ Power plug should be plugged properly
Odor can not be removed	• Is there a very strong odor in the using environment? (Notes: air should be purified continuously) • Does the using life time for filters come to the end?	➡ It is recommended to ventilate first and then turn on the machine ➡ Please replace the used filter with a new one.
High noise	• Is the PE bag for filter removed? • Does the using life time for filter come to the end?	➡ Please take out filter and tear off PE bag. ➡ Please replace the used filter with a new one.
E1	• The front cover is not properly installed.	➡ Reinstall the front cover securely.
999 (Persistent Display)	• The PM2.5 sensor has not been cleaned for an extended period.	➡ 1.Power off the machine. 2.Open the cover located at the lower-right corner on the back of the unit. 3.Gently clean the sensor area using a cotton swab or soft cloth. 4.Close the cover and power the machine back on.

If the problem is still existed after above inspections,please disconnect the power and it for repair