



SAFETY DATA SHEET

1. Identification

Important information

*** This Safety Data Sheet is only authorised for use by HP for HP Original products. Any unauthorised use of this Safety Data Sheet is strictly prohibited and may result in legal action being taken by HP. ***

Product identifier

HP Color LaserJet W2001A-X-XC Cyan Print Cartridge

Other means of identification

None.

Recommended use

This product is a cyan toner preparation that is used in HP Color LaserJet Enterprise M750n, M750dn, M750xh series printers.

Recommended restrictions

None known.

Manufacturer/Importer/Supplier/Distributor information

HP Inc.
1501 Page Mill Road
Palo Alto, CA 94304-1112
United States
650-857-5020

Telephone

HP Inc. health effects line

(Toll-free within the US)

1-800-457-4209

(Direct)

1-760-710-0048

HP Inc. Customer Care Line

(Toll-free within the US)

1-800-474-6836

(Direct)

1-208-323-2551

Email:

hpcustomer.inquiries@hp.com

2. Hazard(s) identification

Physical hazards

Not classified.

Health hazards

Not classified.

Environmental hazards

Not classified.

OSHA defined hazards

Not classified.

Label elements

Hazard symbol

None.

Signal word

None.

Hazard statement

Not available.

Precautionary statement

Prevention

Not available.

Response

Not available.

Storage

Not available.

Disposal

Not available.

Hazard(s) not otherwise classified (HNOC)

None of the other ingredients in this preparation are classified as carcinogens according to ACGIH, EU, IARC, MAK, NTP or OSHA.

GHS Supplemental information

This product is not classified as hazardous according to OSHA CFR 1910.1200 (HazCom 2012).

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Styrene acrylate copolymer		Trade Secret	<85
Wax	Wax	Trade Secret	<10

Chemical name	Common name and synonyms	CAS number	%
Pigment	Pigment	Trade Secret	<5
Amorphous silica	Amorphous silica	7631-86-9	<3

4. First-aid measures

Inhalation	Move person to fresh air immediately. If irritation persists, consult a physician.
Skin contact	Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.
Eye contact	Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists, consult a physician.
Ingestion	Rinse mouth out with water. Drink one to two glasses of water. If symptoms occur, consult a physician.
Most important symptoms/effects, acute and delayed	Not available.

5. Fire-fighting measures

Suitable extinguishing media	CO2, water, or dry chemical
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	Like most organic material in powder form, toner can form explosive dust-air mixtures when finely dispersed in air.
Special protective equipment and precautions for firefighters	Not available.
Fire fighting equipment/instructions	If fire occurs in the printer, treat as an electrical fire.
Specific methods	None established.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Minimize dust generation and accumulation.
Methods and materials for containment and cleaning up	Slowly vacuum or sweep the material into a bag or other sealed container. Clean remainder with a damp cloth or vacuum cleaner. If a vacuum is used, the motor must be rated as dust explosion-proof. Fine powder can form explosive dust-air mixtures. Dispose of in compliance with federal, state, and local regulations.
Environmental precautions	Do not flush into surface water or sanitary sewer system. See also section 13 Disposal considerations.

7. Handling and storage

Precautions for safe handling	Keep out of the reach of children. Avoid inhalation of dust and contact with skin and eyes. Use with adequate ventilation. Keep away from excessive heat, sparks, and open flames.
Conditions for safe storage, including any incompatibilities	Keep out of the reach of children. Keep tightly closed and dry. Store at room temperature. Store away from strong oxidizers.

8. Exposure controls/personal protection

Occupational exposure limits

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Amorphous silica (CAS 7631-86-9)	TWA	6 mg/m3

Biological limit values	No biological exposure limits noted for the ingredient(s).
Exposure guidelines	USA OSHA (TWA/PEL): 15 mg/m3 (Total Dust), 5 mg/m3 (Respirable Fraction) ACGIH (TWA/TLV): 10 mg/m3 (Inhalable Particulate), 3 mg/m3 (Respirable Particulate) Amorphous silica: USA OSHA (TWA/PEL): 20 mppcf 80 (mg/m3)/%SiO2, ACGIH (TWA/TLV): 10 mg/m3 TRGS 900 (Luftgrenzwert) - 10 mg/m3 (Einatembare partikel), 3 mg/m3 (Alveolengängige fraktion)

Appropriate engineering controls Use in a well ventilated area.

Individual protection measures, such as personal protective equipment

Eye/face protection Not available.
Skin protection
Hand protection Not available.
Other Not available.
Respiratory protection Not available.
Thermal hazards Not available.

9. Physical and chemical properties

Appearance Fine powder
Physical state Solid.
Form solid
Color Cyan
Odor Slight plastic odor
Odor threshold Not available.
pH Not applicable
Melting point/freezing point Not available.
Initial boiling point and boiling range Not applicable
Flash point Not applicable
Evaporation rate Not applicable
Flammability (solid, gas) Not available.
Upper/lower flammability or explosive limits
Flammability limit - lower (%) Not flammable
Flammability limit - upper (%) Not available.
Explosive limit - lower (%) Not available.
Explosive limit - upper (%) Not available.
Vapor pressure Not applicable
Vapor density Not applicable
Solubility(ies)
Solubility (water) Negligible in water. Partially soluble in toluene and xylene.
Partition coefficient (n-octanol/water) Not available.
Auto-ignition temperature Not applicable
Decomposition temperature > 392 °F (> 200 °C)
Viscosity Not applicable
Other information
Oxidizing properties No information available.
Percent volatile Negligible
Softening point 176 - 266 °F (80 - 130 °C)
Specific gravity 1 - 1.2
VOC Not applicable

10. Stability and reactivity

Reactivity Not available.
Chemical stability Stable under normal storage conditions.
Possibility of hazardous reactions Will not occur.
Conditions to avoid Imaging Drum: Exposure to light

Incompatible materials	Strong oxidizers
Hazardous decomposition products	Carbon monoxide and carbon dioxide.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Under normal conditions of intended use, this material is not expected to be an inhalation hazard.
Skin contact	Contact with skin may result in mild irritation.
Eye contact	Contact with eyes may result in mild irritation.
Ingestion	Ingestion is not a likely route of exposure.

Symptoms related to the physical, chemical and toxicological characteristics Not available.

Information on toxicological effects

Acute toxicity Based on available data, the classification criteria are not met.

Product	Species	Test Results
W2001A-X-XC		
Acute		
LD50		> 2000 mg/kg

Skin corrosion/irritation Based on available data, the classification criteria are not met.

Serious eye damage/eye irritation Based on available data, the classification criteria are not met.

Respiratory or skin sensitization

Respiratory sensitization Based on available data, the classification criteria are not met.

Skin sensitization Based on available data, the classification criteria are not met.

Germ cell mutagenicity Negative, does not indicate mutagenic potential (Ames Test: Salmonella typhimurium)
Based on available data, the classification criteria are not met.

Carcinogenicity Based on available data, the classification criteria are not met.

IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity Based on available data, the classification criteria are not met.

Specific target organ toxicity - single exposure Based on available data, the classification criteria are not met.

Specific target organ toxicity - repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Based on available data, the classification criteria are not met.

Further information Complete toxicity data are not available for this specific formulation
Refer to Section 2 for potential health effects and Section 4 for first aid measures.

12. Ecological information

Ecotoxicity LC50: > 100 mg/l, Fish, 96.00 Hours

Product	Species	Test Results
W2001A-X-XC		
Aquatic		
Algae	ErC50	Algae > 100 mg/l, 72 Hours
Crustacea	EC50	Crustacea > 100 mg/l, 48 Hours
Fish	LC50	Fish > 100 mg/l, 96 Hours

Persistence and degradability Not available.

Bioaccumulative potential Not available.

Mobility in soil	Not available.
Other adverse effects	Not available.

13. Disposal considerations

Disposal instructions	Do not shred toner cartridge, unless dust-explosion prevention measures are taken. Finely dispersed particles may form explosive mixtures in air. Dispose of in compliance with federal, state, and local regulations. HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit http://www.hp.com/recycle .
------------------------------	---

14. Transport information

Further information	Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.
----------------------------	--

15. Regulatory information

US federal regulations	US EPA TSCA Inventory: All chemical substances in this product comply with all rules or orders under TSCA.
-------------------------------	--

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories	Immediate Hazard - No Delayed Hazard - No Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No
--------------------------	--

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical	No
--	----

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA)	Not regulated.
---------------------------------------	----------------

US state regulations	Not Listed
-----------------------------	------------

Regulatory information	All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDSL), Australia, Japan, Philippines, South Korea, New Zealand, and China.
-------------------------------	--

16. Other information, including date of preparation or last revision

Issue date	28-Jun-2019
Version #	01
Other information	This SDS was prepared in accordance with USA OSHA Hazard Communications regulation (29 CFR 1910.1200).

Disclaimer

This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

This safety data sheet is meant to convey information about HP inks (toners) provided in HP Original ink (toner) supplies. If our Safety Data Sheet has been provided to you with a refilled, remanufactured, compatible or other non-HP Original supply please be aware that the information contained herein was not meant to convey information about such products and there could be considerable differences from information in this document and the safety information for the product you purchased. Please contact the seller of the refilled, remanufactured or compatible supplies for applicable information, including information on personal protective equipment, exposure risks and safe handling guidance. HP does not accept refilled, remanufactured or compatible supplies in our recycling programs.

Revision information

1. Product and Company Identification: Alternate Trade Names

Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
SARA	Superfund Amendments and Reauthorization Act of 1986
STEL	Short-Term Exposure Limit
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds