




TEGERA® CHEMFORCE 71000

Learn more

DOUBLE DIPPED FOR HIGH SAFETY

Double dipped chemical protection PVC glove for allround work with non-slip granulated nitrile finish and seamless lining. 0,2 mm/7,8 mil chemical protection layer. Accelerator-free and phthalate-free, oil and grease resistant. Pre-curved fingers and approved for handling foodstuffs. Soft and flexible design allowing wearers a good all-round working glove.

CHARACTERISTICS

- High level of protection
- Good fingertip sensitivity
- Flexible
- Durable
- Good grip
- Good fit
- Comfortable

FUNCTIONS

- Protection against chemicals
- Approved for handling foodstuffs
- Phthalate-free
- Latex-free
- Pre-curved fingers
- Oil and grease resistant
- Waterproof
- Soft

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Corrosive injuries, Abrasion injuries, Contact with dirt, Contact with chemicals, Contact with moisture, Contact with damp, Contact with oil

PRIMARY ENVIRONMENTS OF USE

Chemical risk environments, Environments hazardous to health, Corrosive environments, Wet environments, Moist environments, Oily and greasy environments, Dirty environments, Harsh environments

PRIMARY AREAS OF USE

Chemical technology work, Chemical work, HVAC installation, Laboratory work, Machine operating, Metalwork, Paint spraying work, Paper industry work, Petro-chemical work, Wood industry work

PRIMARY INDUSTRIES OF USE

Oil and gas extraction, Chemical and petrochemical industry, Basic metals manufacturing, Pulp and paper

TYPE OF WORK

Medium weight

CHEMICAL RESISTANCE

According to EN16523-1:2015. For details, please contact Ejendals.

SPECIFICATION

TYPE Chemical protection gloves
CATEGORY Cat. III
COLLECTION Chemforce
THICKNESS 0,2* mm (*chem-layer)
LINING MATERIAL Nylon, Seamless, Tricot
LENGTH 320 mm
DEXTERITY 5
GRIP DESIGN Granulated
COLOUR Black
PAIRS PER: BUNDLE/CARTON 6/72
AQL 1.5
DISPLAY TYPE Bulk pack
DIPPING MATERIAL Nitrile, PVC (Vinyl)
INNER MATERIAL SPECIFICATION Nylon

COMPLIANCE

CE 2777

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018
3121X

EN 407:2020 (No flame protection)
X1XXXX

EN ISO 374-5:2016

EN ISO 374-1:2016+A1:2018 Type B
JKL

NOT FOR FATTY FOOD

ANSI 4 ABR

FEATURES

Waterproof

Chemical protection

TEST ACCORDING TO EN ISO 374-1:2016

Tested chemical	J	K	L
Permeation level	2	5	2
Degradation %	-16,0	-8,0	-4,9

SIZE		ARTICLE NUMBER	EAN
7	S	71000-7	7340118314242
8	M	71000-8	7340118314259
9	L	71000-9	7340118314266
10	XL	71000-10	7340118314228
11	XXL	71000-11	7340118314235

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.