



## 024-4109

### Reach Anchor Assembly

#### FEATURES:

- Proprietary system to remotely anchor to an elevated point
- Connects to I-beams up to 12", pipes and other pre-established anchor points
- Compact, lightweight and portable
- Easy 2-stage installation to attach anchor point and raise PFAS
- Remote release using telescoping pole and attachments
- Prevent accidental disengagement with safety toggle on self-tightening jaws
- Corrosion-resistant premium grade aluminum components add strength
- Includes (1) Telescoping pole, (1) Pole head attachment, (1) Molded EVA case
- Dimensions: 27.2" x 8.9" x 6.3" (690mm x 225mm x 160mm)
- Minimum Breaking Strength: 5,000 lbs. (22 kN)
- Maximum Install Height: 20 ft. from working surface
- Working Load Limit: 1,000 lbs. (4.4 kN)

#### FALL ARREST POINT(S):

- D-ring

#### ITEM WEIGHT (Including Pole):

- 10.3 lbs. (4.7 kg)



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-141 kg)
OSHA	Up to 420 lbs. (191 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.18-2017 Type A
OSHA	1926.502, 1910.140, 1910.66

RELATED PRODUCTS	
022-4086	Reach Anchor
023-4107	Reach Anchor Pole
025-4125	Reach Anchor: Pole Head Attachment
025-9117	Reach Anchor Case

COMPONENT	MATERIAL SPECIFICATION
Extension arms	Aluminum
Shuttle	Aluminum, stainless steel
D-ring	Steel
Pulley	Nylon
Rope	Polyester
Case	Polyester, Molded EVA
Pole	Fiberglass
Head attachment	Aluminum