



G-Tek® Perfect Fit®

Seamless Knit Engineered Yarn Glove with Polyurethane Coated Grip - Touchscreen - Vend-Ready

- Seamless construction offers increased comfort and breathability
- Lightweight 18-gauge engineered blended liner provides excellent dexterity, tactile sensitivity, and cut resistance
- Polyurethane is thin, yet durable and provides excellent tactility, abrasion resistance and grip on dry surfaces
- Touchscreen compatible to allow the user to operate a touch screen phone or device without removing gloves
- Silicone free for smudge free handling
- ESD safe construction makes these gloves safe for use with static sensitive materials



Technical Data

Color	Black
Sizes Available	XS-2XL
Packaging	Vend Packed
Packed	100 Pair/Case
Case Dimensions (in)	98.30 x 5.00 x 35.00
Case Weight (lbs)	13.03
Country of Origin	China
Liner Material	Nylon
Coating	Polyurethane
Coating Color	Black
Coating Coverage	Palm & Fingers
Grip	Smooth
Gauge	18
Cuff	Knit Wrist
Construction	Coated Seamless Knit, Touchscreen Compatible, ESD Safe
Certifications	21 CFR, Silicone Free

Performance Data

ANSI Abrasion Level	3
ANSI Puncture Level	2
EN 388	221A

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
NPF21-0118N-V-6	Black	XS	883940459387	883940463360	883940463360
NPF21-0118N-V-7	Black	S	883940459394	883940463377	883940463377
NPF21-0118N-V-8	Black	M	883940459400	883940463384	883940463384
NPF21-0118N-V-9	Black	L	883940459417	883940463391	883940463391
NPF21-0118N-V-10	Black	XL	883940459424	883940463407	883940463407
NPF21-0118N-V-11	Black	2XL	883940459431	883940463414	883940463414