

# Safety Data Sheet



## 1. Identification

**Name on Label:** Wipe New Wash

**Product Name:** WIPE NEW HOSE ATTACHED 6PK WASH 30OZ

**Product Identifier:** 387553

**Recommended Use:** Automotive Wash

**Supplier:** Rust-Oleum Corporation  
11 Hawthorn Parkway  
Vernon Hills, IL 60061  
USA

**Manufacturer:** Rust-Oleum Corporation  
11 Hawthorn Parkway  
Vernon Hills, IL 60061  
USA

**Revision Date:** 5/13/2025

**Supercedes Date:** 4/1/2025

**Preparer:** Regulatory Department

**Emergency Telephone:** 24 Hour Hotline: 847-367-7700

## 2. Hazard Identification

### Classification

#### Symbol(s) of Product



#### Signal Word

Danger

#### Possible Hazards

15% of the mixture consists of ingredient(s) of unknown acute toxicity.

#### GHS Hazard Statements

Skin Sensitizer, category 1	H317	May cause an allergic skin reaction.
Serious Eye Damage, category 1	H318	Causes serious eye damage.

#### GHS Label Precautionary Statements

P261	Avoid breathing dust, fumes, gas, mists, vapours, or spray.
P272	Contaminated work clothing should not be allowed out of the workplace.
P280	Wear protective gloves, protective clothing, eye protection, and face protection.
P302+P352	IF ON SKIN: Wash with plenty of soap and water.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310	If exposed immediately call a POISON CENTER or doctor/physician.
P321	Specific treatment (see notice on this label).
P333+P313	If skin irritation or rash occurs: Get medical advice.
P501	Dispose of contents and container in accordance with local, regional and national regulations.

#### GHS SDS Precautionary Statements

Wipe New Hose Attached Car Wash 30 fl oz

P363

Wash contaminated clothing before reuse.

### 3. Composition / Information on Ingredients

#### HAZARDOUS SUBSTANCES

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt.% Range</u>	<u>GHS Symbols</u>	<u>GHS Statements</u>
Sulfonic acids, C14-16-alkane hydroxy and C14-16-alkene, sodium salts	68439-57-6	5.0-10	GHS05-GHS06	H311-315-318
D-Glucopyranose, Oligomeric, Decyl Octyl Glycosides	68515-73-1	3.0-7.0	GHS07	H319
Cocamidopropyl Betaine	61789-40-0	3.0-7.0	Not Available	Not Available
Sodium Hydroxide	1310-73-2	0.1-1.0	GHS05-GHS07	H302+H312-314
C10-16-Alkylbenzene sulfonic acid	68584-22-5	0.1-1.0	GHS07	H302+H312
5-Chloro-2-Methyl-4-Isothiazolin-3-one Mixture with 2-Methyl-4-Isothiazolin-3-one	55965-84-9	<0.1	GHS05-GHS06-GHS07	H301-310+H330-314-317

Actual concentrations of ingredients are withheld as trade secret.

### 4. First Aid Measures

**First Aid - Eye Contact:** Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed. Remove contact lenses, if present and easy to do. Continue rinsing.

**First Aid - Skin Contact:** Immediately flush skin with plenty of water for at least 15 minutes while removing clothing. Get medical attention immediately. Wash clothing separately before reuse. Wash contaminated clothing and decontaminate footwear before reuse.

**First Aid - Inhalation:** Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

**First Aid - Ingestion:** If swallowed, do not induce vomiting. If victim is conscious and alert, give 2 to 4 cupfuls of water or milk. Call a physician or poison control center immediately. Never give anything by mouth to an unconscious person. Treat symptomatically and supportively. Do not induce vomiting unless advised by a physician. Call nearest Poison Control Center or Physician immediately.

### 5. Fire-Fighting Measures

**EXTINGUISHING MEDIA:** Aqueous Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

**Unusual Fire and Explosion Hazards:** Keep containers tightly closed.

**Special Fire Fighting Procedures:** Water may be used to cool closed containers to prevent buildup of steam. If water is used, fog nozzles are preferred. Containers can rupture and release highly toxic material if exposed to heat. Substance is non-combustible but reacts with many metals to form explosive hydrogen gas.

**Special Fire and Explosion Hazard (Combustible Dust):** Not a combustible dust.

### 6. Accidental Release Measures

**Steps to Be Taken If Material Is Released or Spilled:** Avoid runoff into sewers and waterways. Provide ventilation and approach spill from upwind using proper personal protective equipment as indicated in Section 8. Contain spilled liquid with sand or earth. DO NOT use combustible materials such as sawdust. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers.

### 7. Handling and Storage

**Handling:** Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid prolonged or repeated contact with skin. Avoid contact with eyes, skin and clothing.

**Storage:** Store in a dry, well ventilated place. Keep container tightly closed when not in use.

**Advice on Safe Handling of Combustible Dust:** No Information

## 8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV-TWA	ACGIH TLV-STEL	OSHA PEL-TWA	OSHA PEL-CEILING
Sulfonic acids, C14-16-alkane hydroxy and C14-16-alkene, sodium salts	68439-57-6	10.0	N.E.	N.E.	N.E.	N.E.
D-Glucopyranose, Oligomeric, Decyl Octyl Glycosides	68515-73-1	10.0	N.E.	N.E.	N.E.	N.E.
Cocamidopropyl Betaine	61789-40-0	10.0	N.E.	N.E.	N.E.	N.E.
Sodium Hydroxide	1310-73-2	1.0	N.E.	N.E.	2 mg/m3	N.E.
C10-16-Alkylbenzene sulfonic acid	68584-22-5	1.0	N.E.	N.E.	N.E.	N.E.
5-Chloro-2-Methyl-4-Isothiazolin-3-one Mixture with 2-Methyl-4-Isothiazolin-3-one	55965-84-9	0.1	N.E.	N.E.	N.E.	N.E.

### PERSONAL PROTECTION

**Engineering Controls:** Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

**Respiratory Protection:** A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 (U.S.) and/or SOR/86-304 Part XII 12.13 and CSA Standard Z180.1 (Canada) requirements must be followed whenever workplace conditions warrant a respirator's use.

**Skin Protection:** Use impervious gloves to prevent skin contact and absorption of this material through the skin.

**Eye Protection:** Use safety eyewear designed to protect against splash of liquids.

**Other Protective Equipment:** Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

**Hygienic Practices:** Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

**Engineering Measures for Combustible Dust:** No Information

## 9. Physical and Chemical Properties

Physical State	Liquid	Decomposition Temperature, °C	N.D.
Color	Blue	pH	7.5 - 8.5
Odor	Solvent Like	Kinematic Viscosity	N.D.
Odor Threshold	N.E.	Solubility in Water	Slight
Freezing Point / Melting Point, °C	N.D.	Partition Coefficient, n-octanol/water	N.D.
Boiling Range, °C	100 - 100	Vapor Pressure	N.D.
Flammability	Does not Support Combustion	Evaporation Rate	Slower than Ether
Lower Explosion Limit, vol%	N.A.	Specific Gravity	1.033
Upper Explosion Limit, vol%	N.A.	Vapor Density	Heavier than Air
Flash Point, °C	94	Particle Characteristics	N.A.
Auto-Ignition Temperature, °C	N.D.		

(See "Other information" Section for abbreviation legend)

## 10. Stability and Reactivity

**Conditions to Avoid:** Avoid contact with metals. Avoid excess heat.

**Incompatibility:** Incompatible with strong oxidizing agents, strong acids and strong alkalies. Product slowly corrodes copper, aluminum, zinc, and galvanized surfaces.

**Hazardous Decomposition:** When heated to decomposition, it emits acrid smoke and irritating fumes.

**Hazardous Polymerization:** Will not occur under normal conditions.

**Stability:** This product is stable under normal storage conditions.

## 11. Toxicological Information

**Effects of Overexposure - Eye Contact:** Causes eye burns. Irritating, and may injure eye tissue if not removed promptly. High vapor concentrations can irritate eyes, nose and respiratory passages.

**Effects of Overexposure - Skin Contact:** Prolonged or repeated skin contact may cause irritation. Substance is corrosive. Causes severe skin burns. Causes skin irritation. Allergic reactions are possible. May cause skin sensitization, an allergic reaction, which becomes evident upon re-exposure to this material. Frequent or prolonged contact may irritate the skin and cause a skin rash (dermatitis). Severely irritating; may cause permanent skin damage.

**Effects of Overexposure - Inhalation:** High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. High vapor concentrations are irritating to the eyes, nose, throat and lungs.

**Effects of Overexposure - Ingestion:** Corrosive and may cause severe and permanent damage to mouth, throat and stomach. Harmful if swallowed.

**Effects of Overexposure - Chronic Hazards:** Prolonged or repeated skin contact may cause dermatitis.

**PRIMARY ROUTE(S) OF ENTRY:** Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

### ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
68439-57-6	Sulfonic acids, C14-16-alkane hydroxy and C14-16-alkene, sodium salts	2220 mg/kg Rat	>740 mg/kg Rabbit	N.E.
68515-73-1	D-Glucopyranose, Oligomeric, Decyl Octyl Glycosides	N.E.	>2000 mg/kg Rabbit	N.E.
61789-40-0	Cocamidopropyl Betaine	>5000 mg/kg Rat	>2000 mg/kg Rabbit	>20 mg/L
1310-73-2	Sodium Hydroxide	325 mg/kg Rat	1350 mg/kg Rabbit	N.E.
68584-22-5	C10-16-Alkylbenzene sulfonic acid	775 mg/kg Rat	2000 mg/kg Rabbit	N.E.
55965-84-9	5-Chloro-2-Methyl-4-Isothiazolin-3-one Mixture with 2-Methyl-4-Isothiazolin-3-one	53 mg/kg Rat	87.12 mg/kg Rabbit	N.E.

N.E. - Not Established

## 12. Ecological Information

**Ecological Information:** No ecotoxicity data was found for this product.

## 13. Disposal Considerations

**Disposal:** Dispose of material in accordance to local, state, and federal regulations and ordinances. RCRA Hazardous Waste: This material, when discarded or disposed of, could be a hazardous waste according to federal regulations (40 CFR 261) due to the characteristic of corrosivity (D002). Check state and local regulations for disposal requirements. Chemical additions, processing or otherwise altering this material may make the waste management information presented in this SDS incomplete, inaccurate, or otherwise inappropriate.

## 14. Transport Information

	<u>Domestic (USDOT)</u>	<u>International (IMDG)</u>	<u>Air (IATA)</u>	<u>TDG (Canada)</u>
<b>UN Number:</b>	N.A.	N.A.	N.A.	N.A.
<b>Proper Shipping Name:</b>	Not Regulated	Not Regulated	Not Regulated	Not Regulated
<b>Hazard Class:</b>	N.A.	N.A.	N.A.	N.A.
<b>Packing Group:</b>	N.A.	N.A.	N.A.	N.A.
<b>Limited Quantity:</b>	No	No	No	No

## 15. Regulatory Information

### U.S. Federal Regulations:

#### CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Respiratory or Skin Sensitization, Serious eye damage or eye irritation

#### SARA Section 313

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

No Sara 313 components exist in this product.

#### Toxic Substances Control Act

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

<u>Chemical Name</u>	<u>CAS-No.</u>
5-Chloro-2-Methyl-4-Isothiazolin-3-one Mixture with 2-Methyl-4-Isothiazolin-3-one	55965-84-9

### U.S. State Regulations:

#### California Proposition 65

**WARNING:** Cancer - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

## 16. Other Information

### HMIS RATINGS

Health: 2\*    Flammability: 1    Physical Hazard: 0    Personal Protection: X

### NFPA RATINGS

Health: 2    Flammability: 1    Instability: 0

Volatile Organic Compounds: 0.05%

SDS REVISION DATE: 5/13/2025

REASON FOR REVISION: Product Composition Changed  
 Substance and/or Product Properties Changed in  
 Section(s):  
 01 - Identification  
 09 - Physical & Chemical Properties  
 16 - Other Information  
 Revision Statement(s) Changed

**Legend:** N.A. - Not Applicable, N.D. - Not Determined, N.E. - Not Established

Rust-Oleum Corporation believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. Rust-Oleum Corporation makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.