ABB BALDOR RELIANCE

Customer information packet

CEM3211T

3HP, 1760RPM, 3PH, 60HZ, 182TC, 3628M, OPSB, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 5:30:08 PM

Specifications

Enclosure	OPSB
Frame	182TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CURUSEEV
	NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.300 A @ 460.0 V
	8.500 A @ 208.0 V
	8.600 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	4.3 a

Part Detail

Revision	A
Type	AC
Mech. spec.	36B102
Base	
Status	PRD/A
Elec. spec.	36WGZ649
Layout	36LYB102
Eff. date	01-08-2026
CD Diagram	CD0005
Poles	04
Leads	9#16
Proprietary	False
Created date	11-05-2025

Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3628M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	15.00 IN
Power Factor	78
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553LUA										
CAT.NO.	CEM3211T									
SPEC.	36B102Z649									
HP	3									
VOLTS	230/460									
AMPS	8.6/4.3									
RPM	1760									
FRAME	182TC	**HZ**	60			**PH**	3			
SF	1.15	**CODE**	K	**DES**	B	**CLASS**	F			
NEMA NOM. EFF	89.5	**PF**	78							
RATING	40C AMB-CONT									
CC	010A									
ENCL	OPSB	**SN**								
DE	6206	**ODE**	6205							
VPWM INVERTER READY	SFA 9.6/4.8									
CT30-60(2:1) VT3-60(20:1)										
USABLE AT	50HZ 3HP 190/380V 8.6/4.3A									SF1.0

AC Induction Motor Performance Data
Record # 115739
Typical performance - not guaranteed values

Winding: 36WGZ649-R001	**Type:** 3628M	**Enclosure:** OPSB

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			3	**Full Load Torque**	8.953 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			8.6/4.3	**Breakdown Torque**	35.1 LB-FT
R.P.M.			1760	**Pull-up Torque**	19.1 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	21.2 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	30.9 A
Service Factor (S.F.)			1.15	**No-load Current**	2.49 A
NEMA Nom. Eff.	89.5	**Power Factor**	78	**Line-line Res. @ 25ºC**	4.2111 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	25°C
S.F. Amps			9.6/4.8	**Temp. Rise @ S.F. Load**	30°C
				Locked-rotor Power Factor	44.1

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	32	52	66	73	78	81	76
Efficiency	82.9	88.8	90.2	90.1	89.4	88.2	89.7
Speed	1791.6	1783	1773.2	1763.4	1753.4	1742	1757
Line amperes	2.65	3.04	3.59	4.26	5.03	5.89	4.72


ABB Motors and Mechanical Inc.


WINDING # 36WGZ649

3 HP 3 PH 60 HZ 1760 RPM 460 V 3628M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=35.1 PU=19.1 LR=21.2 LRA=30.9




36LYB102
614-623 = 13.62
624-634 = 15.00
635-646 = 16.49
(635-646) ONLY
2.72
2.74
.25
2.62
.25 KEY
1.75 LONG
NAMEPLATE
Ø8.500
8.497
1.1250
1.1245
8.82
6 HOLES
.41 DIA.
4.50
.50
5.50
3.50
6.50
Ø7.86
6.81
1.69
45°
45°
9.04
4.50 +.00 -.06
4 HOLES
.50-13 TAP
Ø7.25 B.C.
LEAD HOLE
1.09 DIA.
3.75
3.75
5.75
4.31
8.63
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT DRW FROM AUTOCAD TO SWD
REV: F
VERSION: 02
REVISED: 09:53:58 11/09/2023
TDR: 000001218972
MODEL NO. 36LYB102
REF: -
BY: USALMAZ
B
BALDOR
HORZ 182-4TC OPSB 36M
36LYB102

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS