

CLAM SHELL SEALER

Model No. KF-772DH

sealersales



Video Demo

Great Value Unit - Direct Heat Spot Welding for Clam Shells

- Lightweight
- Easy to operate
- Two temperature settings
- Suited to any thickness
- Direct heat weld
- Voltage: 100-240V

The **KF-772DH Direct Heat Clamshell Sealer** features two heated serrated jaws, each measuring 3/8" wide and 10mm long. It offers two temperature settings: 410°F (210°C) and 356°F (180°C).

Designed for welding OPS, PSP, PVC, and EPS food packaging cases, this sealer is ideal for clam shells and similar poly packing containers. The handles remain cool during operation for user comfort.

Compatible with voltages ranging from 100-240V.

SPECIFICATIONS	KF-772DH
SEAL TYPE	DIRECT HEAT / CONSTANT HEAT
POWER SUPPLY	AC100V-240W 50/60HZ
WATTS	20W
TEMPERATURE SETTINGS	HIGH: 410°F/210°C LOW: 356°F/180°C
EFFECTIVE WELDING AREA	4MM X 10MM
DIMENSIONS (L x W x H)	1" X 8" X 3"
WEIGHT	10-OZ

Sample Seal

