



STAINLESS STEEL
DISHTABLES
CLEAN STRAIGHT

NEW Tile Edge Design



DTC-S60-60R Shown
 Optional Undershelf Shown

Item #: _____ Qty #: _____
 Model #: _____
 Project #: _____


Spec-Line: 14 ga. 304 Series Stainless Steel Top.
 16 ga. 304 Stainless Steel Legs Stainless Steel Legs with Welded Cross Bracing & Stainless Steel Bullet Feet.

UPGRADED! 16 ga. 304 Series Stainless Steel Top.
Standard: 16 ga. 304 Stainless Steel Legs Stainless Steel Legs with Welded Cross Bracing & Stainless Steel Bullet Feet.

Optional Stainless Steel UNDERSHELF
Die Cast LEG CLAMP
 secured to shelf eliminates unsightly nuts & bolts



10-1/2" EXTRA LARGE Bold Looking Backsplash with 2" return and tile edge



FEATURES:

Tile edge for ease of installation.
 Dishtable system consists of SOIL and CLEAN sections.
 Table is furnished with 10-1/2" splash with a 2" return.

CONSTRUCTION:

All TIG welded.
 Welded areas blended to match adjacent surfaces and to a satin finish.
 Stainless Steel Gussets welded to a stainless steel support channel.

ACCESSORIES	Model #	Qty
Faucet		
Wall Shelf		
Undershelf		

14 Gauge 304 16 Ga. Stainless Steel Legs	16 Gauge 304 Stainless Steel Legs
--	---

Nominal Size	"L"	SPEC-LINE	STANDARD	Approx. Wt.
2 Ft.	23"	DTC-S30-24L or R	DTC-S70-24L or R	35 lbs.
3 Ft.	35"	DTC-S30-36L or R	DTC-S70-36L or R	45 lbs.
4 Ft.	47"	DTC-S30-48L or R	DTC-S70-48L or R	60 lbs.
5 Ft.	59"	DTC-S30-60L or R	DTC-S70-60L or R	70 lbs.
6 Ft.	71"	DTC-S30-72L or R	DTC-S70-72L or R	85 lbs.
7 Ft.	83"	DTC-S30-84L or R	DTC-S70-84L or R	100 lbs.
8 Ft.	95"	DTC-S30-96L or R	DTC-S70-96L or R	110 lbs.
9 FT.	107"	DTC-S30-108L or R	DTC-S70-108L or R	225 lbs.
10 Ft.	119"	DTC-S30-120L or R	DTC-S70-120L or R	250 lbs.
12 Ft.	143"	DTC-S30-144L or R	DTC-S70-144L or R	260 lbs.

Nominal sizing on all dishtables for ease of installation.



Customer Service Available To Assist You 1-800-645-3166 8:30 am - 7:00 pm E.S.T.

For Orders & Customer Service:
 Email: customer@advancetabco.com or Fax: 631-242-6900


For Smart Fabrication™ Quotes:
 Email: smartfab@advancetabco.com or Fax: 631-586-2933

DIMENSIONS and SPECIFICATIONS

TOL ± .500"


ALL DIMENSIONS ARE TYPICAL

SEE DISH MACHINE COMPATIBILITY CHART TO ENSURE PROPER FIT
 Dish Machine Compatibility Chart can be found on our website at www.advancetabco.com under "Product Support"



SPEC-LINE & STANDARD		SUPER SAVER	
1 1/2"	26 1/2"	1 1/2"	26 1/2"
3"	10 1/2"	3"	10 1/2"
	44 1/2"		44 1/2"
34"		34"	
	Cross Brace		
	10"		

*CUSTOMIZE YOUR OWN SYSTEM
 by Ordering Optional Accessories from our
 PRODUCT & PRICE GUIDE*



Description	SPEC-LINE	STANDARD
Material	14 Ga. 304 Series	16 Ga. 304 Series
1 5/8" Dia. Legs	Stainless Steel	Stainless Steel
Gussets	Stainless Steel	Stainless Steel
Bullet Feet (1" adj.)	Stainless Steel	Stainless Steel
Cross Bracing	Welded	Welded

