

# Safety Data Sheet

## 1. Identification

<b>Product Information.</b>	S789 (112257-112256-112255-112258-112402)
<b>Product Name:</b>	Power Burst
<b>Recommended Use.</b>	Professional Carpet Cleaning
<b>Uses advised against.</b>	Professional Use Only
<b>Supplier.</b>	Legend Brands Prochem 15180 Josh Wilson Road Burlington, WA 98233 E-Mail: sds@legendbrands.com 800-932-3030
<b>Emergency telephone number.</b>	INFOTRAC 1-800-535-5053 (North America) +1-352-323-3500 (International)

## 2. Hazards Identification

### GHS Classification in accordance with 29 CFR 1910.1200

Acute Toxicity, Inhalation, category 4  
Serious Eye Damage, category 1  
Skin Corrosion, category 1B

### GHS Pictograms



### Signal Word

Danger

### Unknown Acute Toxicity

8.6% of the mixture consists of ingredient(s) of unknown acute toxicity

### HAZARD STATEMENTS

Causes severe skin burns and eye damage.  
Causes serious eye damage.  
Harmful if inhaled.

### Precautionary Statements - Prevention.

Do not breathe dust/fume/gas/mist/ vapors/spray.  
Wash face and hands and any exposed skin thoroughly after handling.  
Use only outdoors or in a well-ventilated area.  
Wear protective gloves, protective clothing, eye protection, face protection

### Precautionary Statements - Response.

If swallowed: Rinse mouth. Do NOT induce vomiting.  
If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.  
If inhaled: Remove person to fresh air and keep comfortable for breathing.  
If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
Immediately call a poison center or doctor.

Wash contaminated clothing before reuse.

#### **Precautionary Statements - Storage.**

Store locked up.

#### **Precautionary Statements - Disposal.**

Dispose of contents in accordance with local, regional, national, international regulations.

### **3. Composition/Information on Ingredients**

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt. %</u>
SODIUM TRIPOLYPHOSPHATE	7758-29-4	50-75
Sodium carbonate	497-19-8	10-25
2-(2-BUTOXYETHOXY)ETHANOL	112-34-5	2.5-10
Sodium Metasilicate	6834-92-0	2.5-10
ALCOHOLS, C6 -C12, ETHOXYLATED	68439-45-2	2.5-10
Tetrasodium Pyrophosphate	7722-88-5	1.0-2.5
Decyl phenoxybenzenedisulfonic	36445-71-3	1.0-2.5
ALCOHOLS, C10-16, ETHOXYLATED	68002-97-1	1.0-2.5

The exact percentage (concentration) of composition has been withheld as a trade secret.

### **4. First-aid Measures**

#### **Description of first-aid measures.**

##### **General advice.**

Call a physician if irritation develops or persists. When symptoms persist or in all cases of doubt seek medical advice.

##### **Inhalation.**

Move to fresh air.

##### **Skin contact.**

Wash off immediately with soap and plenty of water. Remove all contaminated clothes and shoes.

##### **Eye contact.**

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician. Remove contact lenses, if present.

##### **Ingestion.**

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Gently wipe or rinse the inside of the mouth with water.

##### **Symptoms.**

See Section 2.2, Label Elements and/or Section 11, Toxicological effects.

##### **Notes to physician.**

Treat symptomatically.

### **5. Fire-fighting Measures**

#### **Extinguishing media.**

##### **Suitable extinguishing media.**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

##### **Extinguishing media which shall not be used for safety reasons.**

High volume water jet.

#### **Special hazards arising from the substance or mixture.**

No information available.

#### **Advice for firefighters.**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## 6. Accidental Release Measures

### Personal precautions, protective equipment and emergency procedures.

#### **Personal precautions.**

Avoid contact with skin, eyes and clothing. Ensure adequate ventilation, especially in confined areas. Do not breathe vapors or spray mist.

#### **Advice for emergency responders.**

Use personal protection recommended in Section 8.

### Environmental precautions.

Prevent product from entering drains. See Section 12 for additional Ecological information.

### Methods and materials for containment and cleaning up.

#### **Methods for Containment.**

Prevent further leakage or spillage if safe to do so. Pick up and transfer to properly labeled containers.

#### **Methods for cleaning up.**

Use personal protective equipment as required.

### Reference to other sections.

See section 8 for more information.

## 7. Handling and Storage

### Conditions for safe storage, including any incompatibilities.

#### **Advice on safe handling.**

Handle in accordance with good industrial hygiene and safety practice.

#### **Hygiene measures.**

See section 7 for more information.

#### **Storage Conditions.**

Keep containers tightly closed in a cool, well-ventilated place.

## 8. Exposure Controls/Personal Protection

### Ingredients with Occupational Exposure Limits

<u>Chemical Name</u>	<u>ACGIH TLV-TWA</u>	<u>ACGIH-TLV STEL</u>	<u>OSHA PEL-TWA</u>	<u>OSHA PEL-CEILING</u>
2-(2-BUTOXYETHOXY)ETHANOL	10 ppm	N.E.	N.E.	N.E.

TLV = Threshold Limit Value TWA = Time Weighted Average PEL = Permissible Exposure Limit STEL = Short-Term Exposure Limit N.E. = Not Established

#### **Engineering Measures.**

Showers, eyewash stations, and ventilation systems.

#### **Personal protective equipment.**

##### **Eye/Face Protection.**

Safety glasses with side-shields.

##### **Skin and body protection.**

Wear suitable protective clothing.

##### **Respiratory protection.**

In case of insufficient ventilation wear suitable respiratory equipment.

## 9. Physical and chemical properties.

### Information on basic physical and chemical properties.

<b>Physical state</b>	Powder
<b>Appearance</b>	White powder
<b>Color</b>	White

Odor	Herbal
Odor Threshold	No Information
pH	10.9 - 11.5 @ 1% solution
Melting/freezing point., °C (°F)	No Information
Flash Point., °C (°F)	No Information
Boiling point/boiling range., °C (°F)	100 - 3,000 (212 - 5432)
Evaporation rate	No Information Available
Explosive properties.	No Information
Vapor pressure.	No information
Vapor density.	No Information
Specific Gravity. (g/cm <sup>3</sup> )	1.166
Water solubility.	Soluble
Partition coefficient.	No information
Autoignition temperature., °C	No information
Decomposition Temperature °C.	No information
Viscosity, kinematic.	No information

**Other information.**

Volatile organic compounds (VOC) content.	0%
Density, lb/gal	9.709

## 10. Stability and Reactivity

**Reactivity.**

Stable under normal conditions.

**Chemical stability.**

Stable under recommended storage conditions.

**Possibility of hazardous reactions.**

None known based on information supplied.

**Conditions to Avoid.**

None known.

**Incompatible Materials.**

None known based on information supplied.

**Hazardous Decomposition Products.**

None known.

## 11. Toxicological Information

**Information on toxicological effects.****Acute toxicity.****Product Information**

No Information

The following values are calculated based on chapter 3.1 of the GHS document.

ATEmix (oral)	7,599.2 mg/kg
ATEmix (dermal)	6,849.6 mg/kg
ATEmix (inhalation - dust/mist)	4.85 mg/l

**Component Information.**

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>LD50 Oral</u>	<u>LD50 Dermal</u>	<u>LC50 Inhalation</u>
497-19-8	Sodium carbonate	4090 mg/kg Rat	2002	0.8 mg/l Guinea pig (Dust)
112-34-5	2-(2-BUTOXYETHOXY)ETHANOL	5660 mg/kg Rat	2700 mg/kg Rabbit	N.I.
6834-92-0	Sodium Metasilicate	1153 mg/kg Rat	N.I.	N.I.
68439-45-2	ALCOHOLS, C6 -C12, ETHOXYLATED	N.I.	2500	N.I.

7722-88-5	Tetrasodium Pyrophosphate	1000 - 3000 mg/kg Rat	N.I.	N.I.
36445-71-3	Decyl phenoxybenzenedisulfonic	900 mg/kg Rat	>1000 mg/kg Rabbit	N.I.

N.I. = No Information

**Skin corrosion/irritation.**

SKIN IRRITANT.

**Eye damage/irritation.**

No Information

**Respiratory or skin sensitization.**

No Information

**Ingestion.**

No Information

**Germ cell mutagenicity.**

No Information

**Carcinogenicity.**

No Information

**Reproductive toxicity.**

No Information

**Specific target organ systemic toxicity (single exposure).**

No Information

**Specific target organ systemic toxicity (repeated exposure).**

No Information

**Aspiration hazard.**

No Information

**Primary Route(s) of Entry**

No Information

## 12. Ecological Information

**Toxicity.**

60.97% of the mixture consists of ingredient(s) of unknown aquatic toxicity

**Ecotoxicity effects.**

Chemical Name	Toxicity to algae	Toxicity to fish	Toxicity to daphnia and other aquatic invertebrates
Sodium carbonate 497-19-8	-	LC50 96 h Lepomis macrochirus 300 mg/L, LC50 96 h Pimephales promelas 310 - 1220 mg/L	EC50 48 h Daphnia magna 265 mg/L
2-(2-BUTOXYETHOXY) ETHANOL 112-34-5	EC50 96 h Desmodemus subspicatus >100 mg/L	LC50 96 h Lepomis macrochirus 1300 mg/L	EC50 48 h Daphnia magna >100 mg/L
Sodium Metasilicate 6834-92-0	-	LC50 96 h Brachydanio rerio 210 mg/L, LC50 96 h Brachydanio rerio 210 mg/L	-

**Persistence and degradability.**

No data are available on the product itself.

**Bioaccumulative potential.**

Discharge into the environment must be avoided.

<b><u>CAS-No.</u></b>	<b><u>Chemical Name</u></b>	<b><u>log POW</u></b>
112-34-5	2-(2-BUTOXYETHOXY)ETHANOL	1

**Mobility in soil.**

No information

**Other adverse effects.**

No information

## 13. Disposal Considerations

### Waste Disposal Guidance.

Disposal should be in accordance with applicable regional, national and local laws and regulations.

## 14. Transport Information

### DOT

Shipping Name: Not regulated

### IMDG

Proper Shipping Name: Not regulated

### IATA

Proper Shipping Name: Not regulated

## 15. Regulatory Information

### International Inventories:

TSCA	Complies
DSL	Complies
DSL/NDSL	Complies
EINECS/ELINCS	-
ENCS	-
IECSC	-
KECI	-
PICCS	-
AIIC	-
NZIoC	-
TCSI	
TSCA	United States Toxic Substances Control Act Section 8(b) Inventory.
DSL	Canadian Domestic Substances List.
DSL/NDSL	Canadian Domestic Substances List/Canadian Non-Domestic Substances List
EINECS/ELINCS	European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances.
ENCS	Japan Existing and New Chemical Substances.
IECSC	China Inventory of Existing Chemical Substances.
KECL	Korean Existing and Evaluated Chemical Substances.
PICCS	Philippines Inventory of Chemicals and Chemical Substances.
AIIC	Australian Inventory of Chemical Substances.
NZIoC	New Zealand Inventory of Chemicals.
TCSI	Taiwan Chemical Substance Inventory

### U.S. Federal Regulations:

#### SARA SECTION 313:

This product does not contain any chemicals that are subject to the reporting requirements of SARA 313.

#### TOXIC SUBSTANCES CONTROL ACT 12(b):

This product does not contain any chemicals that are subject to the reporting requirements of TSCA 12(b).

#### ADDITIONAL INFORMATION

Additional Information - Sxn 15: No Information

**CALIFORNIA PROPOSITION 65 CARCINOGENS****WARNING**

Warning: The following ingredients present in the product are known to the state of California to cause Cancer:

<u>Chemical Name</u>	<u>CAS-No.</u>
Titanium dioxide	13463-67-7
Ethylene oxide	75-21-8
1,4-DIOXANE	123-91-1

**CALIFORNIA PROPOSITION 65 REPRODUCTIVE TOXINS****WARNING**

Warning: The following ingredients present in the product are known to the state of California to cause birth defects, or other reproductive hazards.

<u>Chemical Name</u>	<u>CAS-No.</u>
Ethylene oxide	75-21-8

**16. Other Information**

**Revision Date:** 2/5/2025 **Supersedes Date:** 7/7/2023

**Reason for revision:** Substance and/or Product Properties Changed in Section(s):  
 01 - Product Information  
 02 - Hazards Identification  
 03 - Composition/Information on Ingredients  
 11 - Toxicological Information  
 14 - Transportation Information  
 15 - Regulatory Information  
 Substance Hazard Threshold % Changed  
 Revision Statement(s) Changed

**Datasheet produced by:** Regulatory Department

**HMIS Ratings:**

<b>Health:</b>	3	<b>Flammability:</b>	0	<b>Physical Hazard:</b>	0	<b>Personal Protection:</b>	B
----------------	---	----------------------	---	-------------------------	---	-----------------------------	---

**NFPA Ratings:**

<b>Health:</b>	3	<b>Flammability:</b>	0	<b>Instability:</b>	0	<b>Physical &amp; Chemical:</b>	-
----------------	---	----------------------	---	---------------------	---	---------------------------------	---

Legend: N.A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined, N.I. - No Information

The information provided on this SDS is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guide for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered as a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other material or in any process, unless specified in the text.