


Three-point gripper HGDD-50-A-G2

Part number: 1163045

FESTO



Data sheet

Feature	Value
Size	50
Stroke per gripper jaw	8 mm
Max. interchangeability	≤0.2 mm
Max. gripper jaw angular play ax, ay	≤0.1 deg
Max. gripper jaw backlash Sz	≤0.05 mm
Rotational symmetry	≤0.2 mm
Pneumatic gripper repetition accuracy	≤0.03 mm
Type code	HGDD
Number of gripper jaws	3
Mounting position	Any
Mode of operation	Double-acting
Gripper function	3-point
Gripping force backup	During closing
Structural design	Inclined plane Positively driven motion sequence
Position sensing	For proximity sensor
Symbol	00991895
Operating pressure	4 bar ... 8 bar
Operating pressure for sealing air	0 bar ... 0.5 bar
Max. operating frequency of pneumatic gripper	≤4 Hz
Min. opening time at 6 bar	111 ms
Min. closing time at 6 bar	87 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Degree of protection	IP65
Ambient temperature	5 °C ... 60 °C
Mass moment of inertia	15.07 kgcm ²
Maximum force on gripper jaw Fz, static	1300 N
Maximum torque on gripper jaw, Mx static	45 Nm
Maximum torque on gripper jaw, My static	30 Nm
Maximum torque on gripper jaw, Mz static	30 Nm
Relubrication interval for guidance elements	5 MioCyc
Max. mass per external gripper finger	276 g
Product weight	1495 g

Feature	Value
Type of mounting	Optionally: With through-hole and dowel pin With internal thread and dowel pin
Sealing air pneumatic connection	M5
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Cover cap material	High-alloy stainless steel
Housing material	Wrought aluminum alloy Smooth anodized
Gripper jaw material	Steel Hardened