

USB 3.0 to DVI Adapter with 1-Port USB Hub – 1920x1200

Product ID: USB32DVIEH



The USB32DVIEH USB 3.0 to DVI Adapter is TAA compliant and turns an available USB 3.0 port into a DVI output port with high resolution 1920x1200 video support. The adapter features built-in USB 3.0 pass-through, which offers a connection port in place of the USB port used for connecting the DVI adapter – an ideal workaround for Ultrabook or laptop users where only a limited number of USB ports are available.

The USB to DVI adapter functions as an external graphics card, providing a convenient way to add multi-monitor capability to a USB 3.0-enabled desktop or laptop computer (optimal performance from USB 3.0, backward compatible with USB 2.0). The included DVI to VGA adapter also allows you to use this device with a VGA display.

Leveraging the high-bandwidth (5 Gbps) SuperSpeed USB 3.0 interface, the adapter delivers smooth, high-definition content to your DVI display / projector. The adapter can be used to mirror your primary desktop, showing the same image on each display, or to extend your desktop to double your workspace and increase your productivity.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Recommended System Requirements:

CPU: Quad Core 2.4GHz or Higher (i5 recommended)

RAM: 4GB or higher

Certifications, Reports and Compatibility

Applications

- The 1-Port USB hub allows the use of another USB device without losing USB connectivity on your Ultrabook or slim laptop

- Add a secondary DVI display and extend your desktop without taking apart your computer to install a new video card
- Add multi-monitor capability to a single computer, to create engaging multimedia presentations
- Run multiple applications on different screens - check your email on one display and search the web on the other
- View large or multiple spreadsheets across multiple displays
- Use the adapter to connect your PC to your DVI-equipped projector or display for viewing family pictures and movies
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- TAA Compliant
- Supports resolutions up to 1920x1200
- Built in 1-Port USB 3.0 Hub
- SuperSpeed USB 3.0 (5 Gbps) Interface, backward compatible with USB 2.0
- Quick, easy installation
- USB-powered - No external power adapter required
- Choose between Mirrored, Extended or Primary display configurations
- Driver software supports display rotation
- Supports the use of multiple USB32DVIEH adapters on a single system (up to 5)
- DVI to VGA adapter included

Hardware

Warranty	2 Years
Displays Supported	1
AV Input	USB 3.0
AV Output	DVI
	VGA
Audio	No



Bus Type	USB 3.0
USB Pass-Through	Yes
Memory	16MB
Industry Standards	SuperSpeed USB 3.0, USB 2.0
Chipset ID	Trigger - T6-688SL

Performance

Maximum Analog Resolutions	1920x1200
Maximum Digital Resolutions	1920x1200
Supported Resolutions	<p>Widescreen(16/32 bit):</p> <p>1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720</p> <p>Standard(16/32 bit):</p> <p>1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600</p>
Wide Screen Supported	Yes
General Specifications	This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a DisplayLink or Fresco family chipset.

Connector(s)

Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
Connector B	DVI-I (29 pin)
	USB Type-A (9 pin) USB 3.0 (5 Gbps)

Software

OS Compatibility	<p>Windows 10 (32/64)</p> <p>Windows 8 / 8.1 (32/64)</p> <p>Windows 7(32/64)</p> <p>Windows Vista (32/64)</p> <p>Windows XP (32/64)</p>
------------------	---



Microsoft WHQL Certified Yes

Special Notes / Requirements

System and Cable Requirements	System Processor: Quad Core 2.4GHz (i5 recommended) System Memory: 4GB Not intended for gaming
Note	This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as DisplayLink or Fresco Logic Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources This USB video adapter is not intended for graphical intensive applications, such as gaming

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-10C to 75C (14F to 167F)
Humidity	< 85% non-condensing

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	6.3 in [16 cm]
Product Length	3.3 in [85.0 mm]
Product Width	1.9 in [49.0 mm]
Product Height	0.7 in [17.0 mm]
Weight of Product	2.7 oz [76.0 g]

Packaging



Information

Package Length	5.6 in [14.1 cm]
Package Width	8.2 in [20.8 cm]
Package Height	1.5 in [38.0 mm]
Shipping (Package) Weight	6.4 oz [182.0 g]

What's in the Box

Included in Package	USB 3.0 to DVI Adapter
	DVI to VGA adapter
	Software CD
	Manual

****Product appearance and specifications are subject to change without notice.***

