



Heavy-duty aluminum housing



Full control kit



Built-in eye bolts for
suspended ceiling installation

The **Saker Plus** is a large venue electric/motorized projection screen. Its list of standard features include Infrared and Radio Frequency remote controls, a wireless 12 volt trigger and a detachable keypad switch for manual UP/STOP/Down control. The MaxWhite™ front projection material is GREENGUARD® Gold Certified. It has a wide viewing angle and 1.1 gain reflectivity. The Saker Plus is ideal for auditoriums, gymnasiums, or any other large venue indoor environments.

Screen Material

- MaxWhite™ 1.1 Gain front projection surface
- Wide viewing angle, uniformly diffuses light in all directions
- Active 3D and 4K Ultra HD Ready
- Standard black masking borders and black backing
- Diagonal sizes include 200" and 235" in 16:9 and 4:3 format
- GREENGUARD® Gold Certified | UL 2818 for indoor air quality emissions

Control System

- Internal Radio Frequency/Infrared receivers with IR, RF remotes included
- Infrared IR "eye" extension sensor - ideal for concealed installations
- Wireless 12 volt trigger included for synchronized screen operation with the projector's power cycle
- Detachable 3-way wall switch keypad for UP/STOP/DOWN manual operation
- RJ45 port allows 3rd party control system integration

Design and Installation

- Streamlined arcuate profile aluminum heavy-duty white case
- Ring bolts included on case for suspended ceiling installation
- Plug & play, hardwire installation not required

Quality and Reliability

- Tubular motor allows swift operation with a superior weight tolerance and operational lifespan
- 2-year warranty from defects in workmanship
- 3rd year warranty offered through ENR-G program (Education, Non-Profit, Religious, and Government/Military)

Model Number	Nominal Diagonal	Viewable Height (in)	Viewable Width (in)	Screen Material	Gain	Case Color	N.W.	G.W.	Packaging Dims. LxWxH
SK200XVW2	200" (4:3)	120.0	160.0	MaxWhite™	1.1	White	109.7	142.9	182.7"x11.2"x13.2"
SK235XVW2	235" (4:3)	140.3	187.0	MaxWhite™	1.1	White	148.3	186.4	211.4"x11.2"x13.2"
SK200XHW2	200" (16:9)	98.0	174.0	MaxWhite™	1.1	White	112.1	147.1	196.7"x11.8"x13.8"
SK235XHW2	235" (16:9)	115.4	205.0	MaxWhite™	1.1	White	172.5	185.9	227.6"x11"x13.4"