



# C30ELGLASS



41" x 30" x 23.75" (H x W x D)

30 inch wide all-in-one kitchenette with 2-burner smooth-top 115V cooktop, refrigerator-freezer, sink, and storage cabinet

### Highlights:

Complete all-in-one convenience with a refrigerator-freezer, cooktop, sink, and storage compartment in just 30"

ENERGY STAR certified 2-door refrigerator-freezer included

2-burner smooth-top glass cooktop includes pre-installed cord

### Product Features:

Complete one-piece kitchenette	All-in-one kitchen is built with virtually everything you need for meal preparation
115V operation with pre-installed cords	Both the cooktop (12 amps) and refrigerator (1.3 amps) include 3-pronged cords for easy setup
2-door refrigerator-freezer included	CP34W is packaged inside the kitchenette. This 3.2 cu.ft. ENERGY STAR certified refrigerator includes adjustable glass shelves, door storage, and a freezer compartment
Storage compartment	Convenient lower cabinet with adjustable shelf lets you store dry goods
One piece stainless steel countertop	Easy-to-clean surface with a professional look
Indicator lights	Operating indicators light up to show which burner is in use
Push-to-turn knobs	Cooktop knobs require a small amount of force to turn the elements on, helping to prevent accidents
2-burner smooth-top cooktop	Includes a 5 3/4" 600W front element and 7" 900W rear element in a smooth black finish for easier cleanup and safer cooking
Sink and faucet	Stainless steel sink with ready-to-use faucet included



## C30ELGLASS Specifications:

Overview	
Height of Cabinet	41.0" (104 cm)
Width	30.0" (76 cm)
Depth	23.75" (60 cm)
Capacity	2.93 cu.ft. (83 L)
Defrost Type	Manual
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	14.0
Voltage/Frequency	115 V AC/60 Hz
Weight	108.0 lbs. (49 kg)
Shipping Weight	113.0 lbs. (51 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Kitchenette	
Refrigerator Included	CP34W
Refrigerator Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Shelf Type	Glass
Shelf Qty	1
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Full Door Shelves	2
Can Storage	Yes
Thermostat Type	Dial
Refrigerant Type	R600a
Refrigerant Amount	1.16 oz.
High Side PSI	250.0
Low Side PSI	88.0
Cooking Type	Smooth-Top Cooktop
Number of Burners	2
Cooktop Controls	Dial

