

# Radial gripper DHRS-32-A-NC

Part number: 1310165

FESTO



## Data sheet

Feature	Value
Size	32
Max. interchangeability	≤0.2 mm
Max. opening angle	180 deg
Rotational symmetry	≤0.2 mm
Pneumatic gripper repetition accuracy	≤0.1 mm
Type code	DHRS
Number of gripper jaws	2
Mounting position	Any
Mode of operation	Double-acting
Gripper function	Radial
Gripping force backup	During closing
Structural design	Positively driven motion sequence
Position sensing	For proximity sensor
Symbol	00991895
Operating pressure	4 bar ... 8 bar
Max. operating frequency of pneumatic gripper	≤3 Hz
Min. opening time at 6 bar	131 ms
Min. closing time at 6 bar	88 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	5 °C ... 60 °C
Mass moment of inertia	1.69 kgcm <sup>2</sup>
Maximum force on gripper jaw Fz, static	120 N
Maximum torque on gripper jaw, Mx static	6.2 Nm
Maximum torque on gripper jaw, My static	6.2 Nm
Maximum torque on gripper jaw, Mz static	6.2 Nm
Product weight	490 g
Type of mounting	Optionally: With internal thread and centering sleeve Via through-hole and centering sleeve
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Cover cap material	PA
Housing material	Wrought aluminum alloy Hard-anodized

Feature	Value
Gripper jaw material	High-alloy steel