


Angled gripper DHWS-16-A-NC

Part number: 1310179

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | 16 |
| Max. interchangeability | ≤0.2 mm |
| Max. opening angle | 40 deg |
| Rotational symmetry | ≤0.2 mm |
| Pneumatic gripper repetition accuracy | ≤0.04 mm |
| Type code | DHWS |
| Number of gripper jaws | 2 |
| Mounting position | Any |
| Mode of operation | Double-acting |
| Gripper function | Angle |
| Gripping force backup | During closing |
| Structural design | Lever |
| Position sensing | For proximity sensor |
| Symbol | 00991895 |
| Operating pressure | 4 bar ... 8 bar |
| Max. operating frequency of pneumatic gripper | ≤4 Hz |
| Min. opening time at 6 bar | 62 ms |
| Min. closing time at 6 bar | 36 ms |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Ambient temperature | 5 °C ... 60 °C |
| Mass moment of inertia | 0.15 kgcm ² |
| Maximum force on gripper jaw Fz, static | 50 N |
| Maximum torque on gripper jaw, Mx static | 1.6 Nm |
| Maximum torque on gripper jaw, My static | 1.6 Nm |
| Maximum torque on gripper jaw, Mz static | 1.6 Nm |
| Product weight | 114 g |
| Type of mounting | Optionally: With internal thread and centering sleeve Via through-hole and centering sleeve |
| Pneumatic connection | M3 |
| Note on materials | RoHS-compliant |
| Cover cap material | PA |
| Housing material | Wrought aluminum alloy Hard-anodized |

| Feature | Value |
|----------------------|------------------|
| Gripper jaw material | High-alloy steel |