

Stepper motor EMMS-ST-57-M-S-G2

Part number: 1370478

FESTO



Data sheet

Feature	Value
Type code	EMMS-ST
Ambient temperature	-10 °C ... 50 °C
Storage temperature	-20 °C ... 70 °C
Relative air humidity	0 - 85 %
Conforms to standard	IEC 60034
Insulation protection class	B
Thermal class according to EN 60034-1	B
Rating class according to EN 60034-1	S1
Degree of protection	IP54
Electrical connection technology	Plug
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS conformity	VDMA24364-B2-L
Certification	RCM compliance mark c UL us - Recognized (OL)
CE marking (see declaration of conformity)	As per EU EMC directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK instructions for EMC
Nominal operating voltage DC	48 V
Motor holding torque	1.4 Nm
Max. rotational speed	1940 1/min
Step angle with full step	1.8 deg
Step angle tolerance	±5%
Motor nominal current	5 A
Voltage constant, phase	25.5 mVmin
Phase winding resistance	0.25 Ohm
Winding inductance phase	0.95 mH
Rotor mass moment of inertia	0.48 kgcm ²
Total output inertia moment	0.48 kgcm ²
Product weight	1100 g
Permissible axial shaft load	10 N
Permissible radial shaft load	52 N
Brake holding torque	1 Nm