


Motor flange EAMF-A-38D-60G/H

Part number: 1190015

FESTO



Data sheet

Feature	Value
Type code	EAMF-A
Mounting position	Any
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C ... 60 °C
Product weight	265 g
Interface code, motor in	60G 60H
Interface code, coupling housing	38D
Note on materials	RoHS-compliant