


Motor flange EAMF-A-48C-80G

Part number: 1190375

FESTO



Data sheet

| Feature | Value |
|----------------------------------|------------------|
| Type code | EAMF-A |
| Mounting position | Any |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 740 g |
| Interface code, motor in | 80G |
| Interface code, coupling housing | 48C |
| Note on materials | RoHS-compliant |