



Angled gripper DHWS-10-A

Part number: 1310177

FESTO



Data sheet

Feature	Value
Size	10
Max. interchangeability	≤0.2 mm
Max. opening angle	40 deg
Rotational symmetry	≤0.2 mm
Pneumatic gripper repetition accuracy	≤0.04 mm
Type code	DHWS
Number of gripper jaws	2
Mounting position	Any
Mode of operation	Double-acting
Gripper function	Angle
Structural design	Lever
Position sensing	For Hall sensor
Symbol	00991894
Operating pressure	2 bar ... 8 bar
Max. operating frequency of pneumatic gripper	≤4 Hz
Min. opening time at 6 bar	10 ms
Min. closing time at 6 bar	22 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	5 °C ... 60 °C
Total gripping torque at 6 bar, opening	43 Ncm
Total gripping torque at 6 bar, closing	30 Ncm
Mass moment of inertia	0.03 kgcm ²
Maximum force on gripper jaw Fz, static	25 N
Maximum torque on gripper jaw, Mx static	0.6 Nm
Maximum torque on gripper jaw, My static	0.6 Nm
Maximum torque on gripper jaw, Mz static	0.6 Nm
Product weight	40 g
Type of mounting	Optionally: With internal thread and centering sleeve Via through-hole and centering sleeve
Pneumatic connection	M3
Note on materials	RoHS-compliant
Cover cap material	PA

Feature	Value
Housing material	Wrought aluminum alloy Hard-anodized
Gripper jaw material	High-alloy steel