

# Push-in L-connector NPQP-L-Q10-E-FD-P10

Part number: 133108

FESTO



## Data sheet

| Feature                                  | Value                                                          |
|------------------------------------------|----------------------------------------------------------------|
| Size                                     | Standard                                                       |
| Nominal width                            | 6.2 mm                                                         |
| Type code                                | NPQP                                                           |
| Pack size                                | 10                                                             |
| Structural design                        | Push-pull principle                                            |
| Temperature-dependent operating pressure | -0.95 bar ... 10 bar                                           |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:-:-]                  |
| Information on operating and pilot media | Operation with oil lubrication possible                        |
| Corrosion resistance class (CRC)         | 4 - Particularly high corrosion stress                         |
| For use in the food industry             | See supplementary material information                         |
| Ambient temperature                      | -20 °C ... 60 °C                                               |
| Product weight                           | 14 g                                                           |
| Pneumatic connection 1                   | for pneumatic tubing outside diameter 10 mm                    |
| Pneumatic connection 2                   | for pneumatic tubing outside diameter 10 mm                    |
| Note on materials                        | Contains paint-wetting impairment substances<br>RoHS-compliant |
| Housing material                         | PP                                                             |
| Material of tube retaining claw          | High-alloy stainless steel                                     |