

# Electric actuator EPCO-16-150-3P-ST-E

Part number: 1476419

FESTO



## Data sheet

Feature	Value
Size	16
Stroke	150 mm
Stroke reserve	0 mm
Piston rod thread	M6
Reversing backlash	100 µm
Step angle with full step	1.8 deg
Step angle tolerance	±5%
Screw diameter	8 mm
Spindle pitch	3 mm/U
Max. angle of rotation of the piston rod +/-	2 deg
Type code	EPCO
Mounting position	Any
Piston rod end	External thread
Motor type	Stepper motor
Structural design	Electric actuator with ball screw drive
Spindle type	Ball screw drive
Protection against torsion/guide	With plain-bearing guide
Rotor position sensor	Incremental encoder
Rotor position sensor interface	RS422 TTL A/B channels + zero index
Rotor position sensor measuring principle	Optical
Max. acceleration	10 m/s <sup>2</sup>
Max. speed	0.125 m/s
Repetition accuracy	±0.02 mm
Duty cycle	100%
Insulation protection class	B
Nominal operating voltage DC	24 V
Motor nominal current	1.4 A
Certification	RCM compliance mark c UL us - Recognized (OL)
CE marking (see declaration of conformity)	As per EU EMC directive
Corrosion resistance class (CRC)	1 - Low corrosion stress
Storage temperature	-20 °C ... 60 °C
Relative air humidity	0 - 85 % Non-condensing
Degree of protection	IP40

Feature	Value
Ambient temperature	0 °C ... 50 °C
Impact energy in the end positions	1.0E-4 J
Max. torque Mx	0 Nm
Max. torque My	0.6 Nm
Max. torque Mz	0.6 Nm
Max. feed force Fx	125 N
Guide value for payload, horizontal	24 kg
Guide value for payload, vertical	12 kg
Mass moment of inertia JH per meter of stroke	0.0253 kgcm <sup>2</sup>
Mass moment of inertia JL per kg of payload	0.0023 kgcm <sup>2</sup>
Mass moment of inertia JO	0.0228 kgcm <sup>2</sup>
Bending radius, fixed cable installation	≥60 mm
Moving mass at 0 mm stroke	70 g
Additional weight per 10 mm stroke	17 g
Basic weight with 0 mm stroke	615 g
Additional moving mass per 10 mm stroke	2 g
Electrical connection technology	Plug
Type of mounting	With internal thread With accessories
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Cover material	Wrought aluminum alloy Smooth anodized
Housing material	Wrought aluminum alloy Smooth anodized
Piston rod material	High-alloy stainless steel
Spindle nut material	Steel
Spindle material	Roller bearing steel
Material of cylinder barrel	Wrought aluminum alloy Smooth anodized