


# Air solenoid valve VZWD-L-M22C-M-G14-25-V-1P4-8

Part number: 1491831

**FESTO**



## Data sheet

| Feature                          | Value                                                                                                                                |
|----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Type code                        | VZWD                                                                                                                                 |
| Structural design                | Directly controlled poppet valve                                                                                                     |
| Actuation type                   | Electrical                                                                                                                           |
| Sealing principle                | Soft                                                                                                                                 |
| Mounting position                | Any                                                                                                                                  |
| Type of mounting                 | Line installation                                                                                                                    |
| Fitting connection               | G1/4                                                                                                                                 |
| Electrical connection            | Form A<br>Plug<br>as per EN 175301-803<br>Rectangular design                                                                         |
| Nominal width                    | 2.5 mm                                                                                                                               |
| Valve function                   | 2/2, closed, monostable                                                                                                              |
| Manual override                  | None                                                                                                                                 |
| Flow direction                   | Non-reversible                                                                                                                       |
| Medium                           | Compressed air as per ISO 8573-1:2010 [7:4:4]<br>Inert gas<br>Mineral oil<br>Water<br>Neutral liquids<br>Other flow media on request |
| Nominal pressure of fitting PN   | 50                                                                                                                                   |
| Differential pressure            | 0 bar                                                                                                                                |
| Coil characteristics             | 24 V DC: 6.8 W                                                                                                                       |
| Insulation class                 | H                                                                                                                                    |
| Permissible voltage fluctuations | +/- 10 %                                                                                                                             |
| Duty cycle                       | 100%                                                                                                                                 |
| Reset method                     | Mechanical spring                                                                                                                    |
| Type of control                  | Direct                                                                                                                               |
| Symbol                           | 00992979                                                                                                                             |
| Medium pressure                  | 0 bar ... 8 bar                                                                                                                      |
| Max. viscosity                   | 22 mm²/s                                                                                                                             |
| Temperature of medium            | -10 °C ... 80 °C                                                                                                                     |

| Feature                          | Value                                                          |
|----------------------------------|----------------------------------------------------------------|
| Ambient temperature              | -10 °C ... 35 °C                                               |
| Leak rate to EN 12266-1          | A                                                              |
| Flow rate Kv                     | 0.16 m³/h                                                      |
| Standard nominal flow rate       | 170 l/min                                                      |
| On switching time                | 25 ms                                                          |
| Switching time off               | 10 ms                                                          |
| Note on materials                | Contains paint-wetting impairment substances<br>RoHS-compliant |
| Housing material                 | Brass                                                          |
| Material number of housing       | CW614N                                                         |
| Seals material                   | FPM                                                            |
| Product weight                   | 350 g                                                          |
| Degree of protection             | IP65                                                           |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress                                       |