

# Parallel kit EAMM-U-110-D60-60H-120-S1

Part number: 1530621

FESTO



## Data sheet

Feature	Value
Size	110
Type code	EAMM-U
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	5000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP65
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	799 kgmm <sup>2</sup>
No-load driving torque	0.3 Nm
Transferable torque	25 Nm
Product weight	5270 g
Note on materials	RoHS-compliant