


Compact air cylinder ADVULQ-50-50-P-A

Part number: 156728

FESTO



Data sheet

Feature	Value
Stroke	50 mm
Piston diameter	50 mm
Type code	ADVULQ
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Double-acting
Piston rod end	Internal thread
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Symbol	00991217
Variants	Piston rod at one end
Protection against torsion/guide	Square piston rod
Operating pressure	0.8 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	0.64 J
Theoretical force at 6 bar, retracting	1057 N
Theoretical force at 6 bar, advancing	1178 N
Moving mass at 0 mm stroke	112 g
Additional weight per 10 mm stroke	72 g
Basic weight with 0 mm stroke	560 g
Additional moving mass per 10 mm stroke	16 g
Type of mounting	Optionally: With through-hole With accessories
Pneumatic connection	G1/8
Flange screws material	Steel, galvanized
Cover material	Wrought aluminum alloy
Material of dynamic seals	NBR TPE-U(PU)
Piston rod material	High-alloy steel
Material of cylinder barrel	Wrought aluminum alloy