

# Compact air cylinder AEVUZ-16-25-P-A

Part number: 157215

FESTO



## Data sheet

| Feature                                  | Value                                                              |
|------------------------------------------|--------------------------------------------------------------------|
| Stroke                                   | 25 mm                                                              |
| Piston diameter                          | 16 mm                                                              |
| Type code                                | AEVUZ                                                              |
| Cushioning                               | Elastic cushioning rings/pads at both ends                         |
| Mounting position                        | Any                                                                |
| Mode of operation                        | Single-acting<br>Pulling                                           |
| Piston rod end                           | Internal thread                                                    |
| Structural design                        | Piston<br>Piston rod                                               |
| Position sensing                         | For proximity sensor                                               |
| Symbol                                   | 00991204                                                           |
| Variants                                 | Piston rod at one end                                              |
| Operating pressure                       | 1.3 bar ... 10 bar                                                 |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                      |
| Ambient temperature                      | -20 °C ... 80 °C                                                   |
| Impact energy in the end positions       | 0.1 J                                                              |
| Theoretical force at 6 bar, advancing    | 81 N                                                               |
| Moving mass at 0 mm stroke               | 12 g                                                               |
| Additional weight per 10 mm stroke       | 15 g                                                               |
| Basic weight with 0 mm stroke            | 89 g                                                               |
| Additional moving mass per 10 mm stroke  | 4 g                                                                |
| Type of mounting                         | Optionally:<br>With through-hole<br>With accessories               |
| Pneumatic connection                     | M5                                                                 |
| Flange screws material                   | High-alloy stainless steel                                         |
| Cover material                           | Wrought aluminum alloy                                             |
| Material of dynamic seals                | NBR<br>TPE-U(PU)                                                   |
| Piston rod material                      | High-alloy stainless steel                                         |
| Material of cylinder barrel              | Wrought aluminum alloy                                             |